



Halogen lamp ball E14 18 W 205 lm 2800K

General information

Ball-shaped halogen lamp with E14 cap, 205 lumen and power consumption of 18 watts. It spreads a warm white light with a colour temperature of 2,800 kelvin.

Specifications	
Colour Temperature:	2800 K
Diameter:	46 mm
Dimmable:	Yes
Energy Class:	D
Energy consumption:	18 kWh / 1000h
Glass Style:	Clear
Height:	80 mm
HG:	None mg Milligram
Lamp Shape:	Ball
Lamp Type:	Halogen
Life Span:	1500 h
Light Colour:	Warm White
Lumen:	205 lm
Lumen Maintenance Factor (LMF):	0.85
Power Factor:	1
Ra Value:	100
Replacement Wattage:	25 W
Socket:	E14
Starting Time:	
Switch Cycles:	6000
Voltage:	230 V
Warm Up time 60% brightness:	
Wattage:	18 W



Sales information

Order code: **HQHE14BALL001**

Product description: Halogen lamp ball E14 18 W 205 lm

2800K

Packaging: Giftbox with eurolock

Brand name: HQ



Quantity	LxWxH (mm)	Weight
1	50x50x90 115x110x265	30 gr. 360 gr. 4200 gr.
10	115x110x265	360 gr.
100	290x240x580	4200 gr.