



COB Mobile LED Floodlight 10 W 700 Lumen EU Plug

General information

Indoor & outdoor rechargeable and mobile 10 Watt LED floodlight with a highly efficient light performance of 700 lumen. The built-in powerful 4400 mAh lithium battery has an operating time of approximately 4 hours. The high-power COB (chip on board) LED light uses 70% less energy than traditional floodlights. Furthermore, the LED chip has an extremely long life span which can last over 30000 hours.

Ideal for home purpose as well as professional purposes.

| Specifications | |
|---------------------|---------|
| Beam Angle: | 120 ° |
| Colour Temperature: | 6000 K |
| Dimmable: | No |
| Energy Class: | Α |
| Height: | 220 mm |
| Lamp Type: | LED |
| Life Span: | 30000 h |
| Lumen: | 700 lm |
| Power Factor: | 0.5 |
| Ra Value: | 70 |
| Switch Cycles: | 20000 |
| Wattage: | 10 W |

Package contents

- 1x LED Floodlight
- Car Adapter
- Manual
- AC Adapter

EU plug



Sales information

Order code: KNLEDFLMB10W

Product description: COB Mobile LED Floodlight 10 W 700

Lumen EU Plug

Packaging: Giftbox Brand name: König



| Quantity | LxWxH (mm) | Weight |
|----------|----------------------------|----------|
| 1 | 175x155x250 380x270x490 | 1300 gr. |
| 6 | 380x270x490 | 8500 gr. |