Powershred[®] M-7C

Personal Shredder

Stylish Compact Home / Home Office Shredder

For 1 User

- Shreds 7 sheets per pass (70gsm) into 4x46mm cross-cut particles (Security Level P-3)
- Shreds continuously for up to 4 minutes
- Features wide 229mm paper entry
- Also shreds staples and credit cards
- Safety cut out on bin removal
- 14 litre bin with easy lift-off head and viewing window
- 1 year full warranty plus 3 years on cutters



SPECIFICATIONS

Plug Type	EU	UK
Item Number	4603101	4603201
Sheet Capacity	7	7
Security Level	P-3	P-3
Bin Capacity	14 Litres	14 Litres
Run Time	4 minutes	4 minutes
Can Shred		
Machine Dimensions (HxWxD) & Weight	387 x 320 x 186 / 3.9kg	387 x 320 x 186 / 3.9kg
Retail Barcode	043859647316	043859647330
Outer Dimensions (HxWxD) & Weight	370 x 436 x 362 / 10.9kg	370 x 436 x 362 / 10.9kg
Outer Barcode	50043859647311	50043859647335
Quantity per outer	2	2

THE WORLD'S TOUGHEST SHREDDERS"