

Every 2nd shelf construction can be easier than you think.*





*At least that is what we think.

Because the planning and installation of shelves is child's play with us. And thus, you have more space and order in all private living and usage rooms with just a few maneuvers. Choose from two practical systems:



SYSTEM CLASSIC: THE RIGHT THING FOR EVERY ROOM.

With the System CLASSIC, you can easily make space in tight rooms o under roof slopes.



SYSTEM EASY: SAVE DRILL HOLES AND MEASURING.

Vith the System EASY, all omponents are aligned along a oprights on the wall rails. Thus, space can be made quicker.

Two systems, unlimited combination and material variations.

This is how easy it is:

With System CLASSIC and System EASY, you can simply make your individual shelf. The best thing: Everything is done in just two steps.



Fix uprights or wall rail




Connect accessories



The right thing for everything.



OFFSET OR PARALLEL FLOORS? Choose: Uprights in a 1 or 2 slotted.




A LOT OR A LITTLE DISTANCE?

Determine the distance between the shelf boards: Either with hole spacing in the raster 50 or raster 32.



NO DRILL HOLES AND MEASURING!

Very simple: With the EASY system, all components are set along a base-board on the wall rails.



UNLIMITED ACCESSORIES:

Wall rails or uprights on the wall? Then you have to hang it up! Our accessories fulfill all wishes.

WALL SHELVES

CLASSIC always fits! Our original leaves no wishes unfulfilled with its diverse combination options. Just select your desired shelf board distance and decide for the offset or parallel hanging of shelf boards.

CLASSIC 50	UPRIGHTS AND BRACKETS			
	Single slotted WALL UPRIGHT	Pack unit, Ordering unit	Dimensions H	Colour selection
	 The single slotted wall upright is the tried and tested starter unit. Combined with the double slotted wall upright it can be used for instance as a lateral end element for wall-mounted shelving units. The wall upright can be assembled together with brackets and with book ends. 	PU: 2, OU: 10 PU PU: 2, OU: 5 PU PU: 1, OU: 10 PU	5.7" 19.7" 39.4" 59.1" 78.7"	White Black White aluminium
	Double slotted WALL UPRIGHT	Pack unit, Ordering unit	Dimensions H	Colour selection
	 The double slotted wall uprights allow shelves and baskets to be positioned together on the same level. The double slotted wall upright can be assembled together with all CLASSIC 50 brackets. 	PU: 2, OU: 10 PU PU: 2, OU: 5 PU PU: 1, OU: 10 PU	19.7" 39.4" 59.1" 78.7"	White Black White aluminium
	Single slotted WALL PLATE	Pack unit, Ordering unit	Dimensions H x D	Colour selection
	Wall plates are the alternative to wall uprights and cantilever brackets.Screws and wall plugs are included in the delivery.	PU: 2, OU: 10 PU	2.8" x 1.3"	White Black White aluminium

CLASSIC 50	UPRIGHTS AND BRACKETS				
	PRO-BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 Safety brackets with 2 lugs and shelf support locking system. Can be assembled with all CLASSIC 50 wall uprights, steel shelf, wire mesh shelf and with wooden and glass shelves in conjunction with single-sided clip-on holder, double-sided clip-on holder and in addition, for glass shelves, suction pad. 	PU: 1 OU: 20 PU	5.9" 7.9" 9.8" 11.8" 13.8" 15.7" 19.7"	132 lbs	White Black White aluminium
	U-BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
go de la companya de	 Can be mounted with double slotted wall upright. Can be used with wooden and glass shelves in conjunction with singlesided insert holder for U-bracket, double-sided insert holder for U-bracket and, for glass shelves, with suction pad. 	PU: 1 OU: 20 PU	6.7" 8.7" 10.6" 14.6" 18.5"	110 lbs	White Black White aluminium
	TWIN WIRE SHELF BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 Can be used with TWIN wire shelf. Can be assembled with all double slotted CLASSIC 50 and CLASSIC 32 uprights. 	PU: 1 OU: 10 PU	12.6" 16.5"	66 lbs	White White aluminium
	ANGLE BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 Using a left-hand and a righthand version of the bracket creates an attractive appearance for the end of the shelving unit. The angle bracket is suitable for supporting wooden shelves. The bracket is fitted with two lugs. 	PU: 2 OU: 10 PU in pairs	7.1" 9.1" 11.0" 13.0" 15.0"	121 lbs	White Black White aluminium
	ANGLE BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	Angle bracket with three lugs.	PU: 2 OU: 10 PU in pairs	18.9"	143 lbs	White Black White aluminium

CLASSIC 50	UPRIGHTS AND BRACKETS				
	WOODEN SHELF BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 The wooden shelf bracket is suitable for wooden shelves from 0.7" to 0.9" in thickness. The wooden shelf bracket can be assembled with all CLASSIC 50 wall uprights. Incl. Spax-screws for the mounting of the wooden shelves. 	PU: 2 OU: 10 PU in pairs	4.7"	121 lbs	White White aluminium
	CLOTHES HANGING SYSTEM	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 With two lugs, for assembly with all wall uprights. Can be used in conjunction with clothes rail and end cap to create a cloakroom or for in-cupboard storage. 	PU: 1 OU: 10 PU	9.8" 13.0"	66 lbs	White White aluminium
CLASSIC 32	UPRIGHTS AND BRACKETS				
		Pack unit,	Dimensions		Colour
	WALL UPRIGHT	Ordering unit	H		selection
	 WALL UPRIGHT The double slotted wall uprights permit shelves, baskets etc. to be positioned on the same level. Can be assembled with all brackets for double slotted CLASSIC 32 uprights. 				
	 The double slotted wall uprights permit shelves, baskets etc. to be positioned on the same level. Can be assembled with all brackets for double slotted 	Ordering unit PU: 1	8.7" 17.7" 37.4" 55.1" 81.1"	Max. load	selection White Black

CLASSIC 32	UPRIGHTS AND BRACKETS				
	U-BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 Can be mounted with double slotted wall upright. Can be used with wooden and glass shelves in conjunction with insert holder for U-bracket and, for glass shelves, with suction pad. 	PU: 1 OU: 10 PU	6.7" 8.7" 10.6" 12.6" 14.6" 18.5" 22.4"	110 lbs	White Black White aluminium
	TWIN WIRE SHELF BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 Can be used with TWIN wire shelf. Can be assembled with all double slotted CLASSIC 32 and CLASSIC 50 uprights. 	PU: 1 OU: 10 PU	12.6" 16.5"	66 lbs	White White aluminium
	CLOTHES HANGING SYSTEM	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 With three lugs, for assembly with all wall uprights. Can be used in conjunction with clothes rail and end cap as a coat rack or on the inside of cabinets. 	PU: 1 OU: 10 PU	13.0"	66 lbs	White White aluminium
EASY 50	UPRIGHTS AND BRACKETS				
	WALL RAIL	Pack unit, Ordering unit	Dimensions W	Max. load	Colour selection
	Horizontal mounting on the wall.Basic element for suspension of the hang track.Can be assembled with hang track.	PU: 1 OU: 4 PU	40.0" 80.0"	330 lbs 660 lbs	White White aluminium
	HANG TRACK	Pack unit, Ordering unit	Dimensions H		Colour selection
	 For suspension in the basic element wall rail. The hang track can be suspended with any optional spacing in the wall rail. Simple alignment along the wall rail. This eliminates the need for multiple screwing of individual uprights. Uncomplicated, fast adjustment to variable shelf grid dimensions. Horizontal and vertical shelf support locking system. 	PU: 1 OU: 10 PU	47.2" 78.7"		White White aluminium

EASY 50	UPRIGHTS AND BRACKETS				
	BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	■ Bracket for wire mesh shelf.	PU: 1 OU: 20 PU	15.7"	132 lbs	White White aluminium
	CLOTHES HANGING SYSTEM	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	Can be used in conjunction with clothes rail as a coatrack and cabinet mounting system and end cap.	PU: 1 OU: 10 PU	9.8" 13.0"	66 lbs	White White aluminium
	WOODEN SHELF BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 For pushing in wooden shelves from 0.7" to 0.9". Incl. Spax-screws for the mounting of the wooden shelves. 	PU: 2 OU: 10 PU in pairs	4.7"	121 lbs	White White aluminium
EASY 32	UPRIGHTS AND BRACKETS				
EASY 32	UPRIGHTS AND BRACKETS WALL RAIL	Pack unit, Ordering unit	Dimensions W	Max. Ioad	Colour selection
EASY 32					selection White White aluminium
EASY 32	WALL RAIL Horizontal mounting on the wall. Basic element for suspension of the hang track.	Ordering unit PU: 1	W 40.0"	load 330 lbs	selection White

EASY 32	UPRIGHTS AND BRACKETS				
	BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	■ Bracket for wire mesh shelf.	PU: 1 OU: 20 PU	15.7"	77 lbs	White White aluminium
	CLOTHES HANGING SYSTEM	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	Can be used in conjunction with clothes rail as a coatrack and cabinet mounting system and end cap.	PU: 1 OU: 10 PU	13.0"	66 lbs	White White aluminium
	WOODEN SHELF BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 For pushing in wooden shelves from 0.7" to 0.9". Incl. Spax-screws for the mounting of the wooden shelves. 	PU: 2 OU: 10 PU in pairs	4.7"	121 lbs	White White aluminium
DESIGN	UPRIGHTS AND BRACKETS				
	WALL UPRIGHT	Pack unit, Ordering unit	Dimensions H		Colour selection
	 Elegant design element to create a modern ambience in any living area. The wall upright can be assembled with design bracket. 	PU: 1 OU: 10 PU	5.7" 19.7" 39.4" 59.1" 78.7"		White White aluminium
	BRACKET	Pack unit, Ordering unit	Dimensions D	Max. load	Colour selection
	 The design matches semicircular upright. Fitted with two lugs, the bracket can also be assembled with all CLASSIC 50 wall uprights and steel shelves, wire mesh shelf, as well as wooden and glass shelves. 	PU: 1 OU: 10 PU	5.9" 7.9" 9.8" 11.8" 13.8" 15.7"	121 lbs	White White aluminium

ACCESSORIES	STEEL SHELVES				
	STEEL SHELF	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
(32,50)	 The steel shelves can be simply inserted in the pro-brackets without the need for tools. Their washable surfacae makes them ideally suited for wideranging applications. 	PU: 2 OU: 10 PU in pairs	31.5" x 7.9" 31.5" x 9.8" 31.5" x 11.8" 31.5" x 13.8"	55 lbs 66 lbs 66 lbs 66 lbs	White White aluminium
	HINGED SHELF	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
200	 Further development of the steel shelf with a special feature: The fold-out brackets on both sides are already integrated. The hinged shelf can be assembled using single or double slotted CLASSIC 50 uprights. Can be assembled directly with hang track. To incline the hinged shelf by 20 degrees, adapter is required. 	PU: 2 OU: 1 PU in pairs	31.5" x 11.8"	44 lbs	White White aluminium
	ADAPTER for HINGED SHELF	Pack unit, Ordering unit		Max. load	Colour selection
20 05	 This adapter allows the hinged shelf to be inclined by 20 degrees. For this, first the adapter must be connected to the upright and then the hinged shelf inserted in the adapter 	PU: 2 OU: 10 PU in pairs		66 lbs	White White aluminium
	FALTFACHBODEN	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
32	 The hinged shelf is a further development of the known steel shelf with a special feature: The fold-out brackets on both sides are already integrated. The hinged shelf can be extended at will using the double slotted CLASSIC 32 wall uprights. Can be assembled directly with hang track. To incline the hinged shelf by 20 degrees, adapter is required. 	PU: 2 OU: 1 PU in pairs	31.5" x 11.8"	44 lbs	White White aluminium
	ADAPTER for HINGED SHELF	Pack unit, Ordering unit		Max. load	Colour selection
32)	 This adapter allows the hinged shelf to be inclined by 20 degrees. For this, first the adapter must be connected to the upright and then the hinged shelf inserted in the adapter 	PU: 4 OU: 10 PU in pairs		66 lbs	White aluminium

ACCESSORIES	WIRE SHELVES				
	TWIN WIRE SHELF	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
(32/50)	 Assembly of the TWIN wire shelves is only possible with the special wire shelf bracket. To ensure adequate stability over the 70.9" length, three wire shelf brackets must be used. This will prevent the shelf from bending in the middle. The wire shelf is firmly connected to the bracket by being clicked into place, so preventing any possibility of slippage. The raised rear and front edges of the wire shelf provide a drop protection. 	PU: 1 OU: 8 PU PU: 1 OU: 4 PU	31.5" x 11.8" 31.5" x 15.7" 35.4" x 11.8" 35.4" x 15.7" 70.9" x 11.8" 70.9" x 15.7"	88 lbs 88 lbs 88 lbs 110 lbs 44 lbs 55 lbs	White White aluminium
	WIRE MESH SHELF	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
(32/50)	 The wire grid shelf offers wide application scope, for example as a shoe rack. The wire shelf can be shortened to any optional length. 	PU: 1 OU: 5 PU	31.5" x 15.7"	44 lbs	White White aluminium
	WIRE BASKET	Pack unit, Ordering unit	Dimensions W x H x D	Max. load	Colour selection
(32 50)	The wire basket, which is supplied inclusive of two brackets, creates space for all types of storage and can be assembled with both CLASSIC 50 and CLASSIC 32 rails by simply inserting into position.	PU: 1 OU: 10 PU	31.5" x 4.7" x 13.8"	40 lbs	White White aluminium
	Telescopic WIRE BASKET	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
(32 50)	 Simple insertion into the hang track using integrated brackets. Includes drawer extension for easy access. 	PU: 1 OU: 2 PU	31.5" x 13.8"		White aluminium
	BOTTLE RACK	Pack unit, Ordering unit	Dimensions W x D	Max. load	Colour selection
(32 50)	 The rack is particularly suited for space-saving storage of bottles and is supplied inclusive of two brackets. The bottle rack can be assembled with all the wall uprights independently of the grid size. 	PU: 1 OU: 10 PU	31.5" x 11.8"	40 lbs	White White aluminium

ACCESSORIES	WOODEN SHELVES			
	SHELF large	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	The shelves can be simply suspended in the hang track using shelf bracket.	PU: 1 OU: 1 PU	31.1" x 0.9" x 14.6"	White Tobacco
	SHELF small	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	■ Matching shelf for use with small drawer element.	PU: 1 OU: 1 PU	15.4" x 0.9" x 14.6"	White Tobacco
	CORNER SHELF	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	For fastening the corner shelf, it is advisable to mount an additional hang track and an additional wooden shelf bracket!	PU: 1 OU: 1 PU	21.7" x 0.9" x 14.6"	White Tobacco
	BASIC STANDARD	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	■ Decor-coated with rounded edge on one side.	PU: 1 OU: 1 PU	23.6" x 0.7" x 7.9" 31.5" x 0.7" x 7.9" 47.2" x 0.7" x 7.9" 23.6" x 0.7" x 11.8" 31.5" x 0.7" x 11.8" 47.2" x 0.7" x 11.8"	White Beech Tobacco
	DELUXE CORNER	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	Solid wood.	PU: 1 OU: 1 PU	9.8" x 0.7" x 9.8" 13.8" x 0.7" x 13.8"	Pine White Spruce

ACCESSORIES	GLASS SHELVES			
	VARIO STANDARD	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	Standard glass shelf with two different surface finishes.	PU: 1 OU: 1 PU	15.7" x 0.2" x 5.9" 23.6" x 0.2" x 5.9" 23.6" x 0.2" x 7.9" 35.4" x 0.2" x 7.9"	Clear Satinized
	VARIO CONVEX	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
		PU: 1 OU: 1 PU	23.6" x 0.2" x 3.9"/7.9"	Clear Satinized
	VARIO CORNER	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
		PU: 1 OU: 1 PU	9.8" x 0.2" x 9.8"	Clear Satinized
	VARIO UNO	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
		PU: 1 OU: 1 PU	15.7" x 0.2" x 5.9" 23.6" x 0.2" x 5.9"	Clear Satinized

All glass floors tempered safety glass.

ACCESSORIES	CELLARS, GARAGES, LAUNDRY ROOMS			
	SUPPORT RAIL	Pack unit, Ordering unit	Dimensions W	Colour selection
(32,50)	 Hooks are positioned on the support rail. The support rails can be suspended in the hang track side by side or in staggered formation. 	PU: 1 OU: 1 PU	31.5"	White aluminium
	HOOK for SUPPORT RAIL	Pack unit, Ordering unit	Dimensions W x H, Diameter	Colour selection
	The hook is placed on support rail and can be used for a variety of applications.	PU: 1 OU: 1 PU	2.2" x 3.5", Ø 0.3"	White aluminium
	HOOK for SUPPORT RAIL	Pack unit, Ordering unit	Dimensions W x H, Diameter	Colour selection
	The large hook is also positioned on support rail. Its length permits several implements to be suspended in a row.	PU: 1 OU: 10 PU	7.5" x 5.5", Ø 0.3"	White aluminium
	CLOTHES RAIL	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50)	By mounting in the clothes rail bracket, a fully functional cupboard and wardrobe element is created.	PU: 1 OU: 1 PU	31.5" x 0.8" x 1.4" 39.4" x 0.8" x 1.4"	Chrome
	END CAP for CLOTHES RAIL	Pack unit, Ordering unit	Dimensions H x D	Colour selection
	 Attractive end element for clothes rails. The end caps also prevent hangers from slipping off the rail. 	PU: 1 OU: 1 PU	1.4" x 0.8"	Plastic

ACCESSORIES	CELLARS, GARAGES, LAUNDRY ROOMS			
	TROUSER HANGER	Pack unit, Ordering unit	Dimensions W x D	Colour selection
(32/50)	For 9 pairs of trousers.Simple suspension in the hang track.	PU: 1 OU: 1 PU	31.5" x 11.8"	White aluminium
	WIRE MESH SHELF HOOK	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
	The hook is connected to the TWIN wire shelf and is suitable for storage of brooms, shovels and other tools with handles.	PU: 1 OU: 1 PU	3.5" x 3.7" x 3.5"	White aluminium
ACCESSORIES	HOME OFFICES, STUDIOS			
	BOOK END	Pack unit, Ordering unit	Dimensions W x D	Colour selection
20 \$	This book end can be assembled with all CLASSIC 50 wall uprights by simply plugging into place.	PU: 1 OU: 20 PU PU: 4 OU: 10 PU	5.6" x 4.6"	White Black White aluminium
	BOOK END	Pack unit, Ordering unit	Dimensions W x D	Colour selection
(32 50)	This book end is assembled with a double slotted wall upright and fits both the CLASSIC 50 and the CLASSIC 32 system.	PU: 1 OU: 10 PU	3.1" x 9.8"	White White aluminium
	BOOK END	Pack unit, Ordering unit	Dimensions W x D	Colour selection
	This book end also fits into even the smallest shelf and is clamped between the book and the shelf.	PU: 4 OU: 10 PU PU: 1 OU: 20 PU	4.7" x 5.1"	White Black White aluminium

ACCESSORIES	HOME OFFICES, STUDIOS			
	BABYLON BOOK END	Pack unit, Ordering unit	Dimensions W x D	Colour selection
	■ This book end is pushed onto wooden shelves with a thickness between 0.6" and 0.9" from the front.	PU: 2 OU: 6 PU	5.9" x 5.9"	White White aluminium
	BOOK END	Pack unit, Ordering unit	Dimensions W x D	Colour selection
	This book end can be assembled with all CLASSIC 32 wall uprights by simply plugging into place.	PU: 2 OU: 6 PU	5.6" x 4.6"	White Black White aluminium
ACCESSORIES	ASSEMBLY MATERIAL			
	SCREWS AND WALL PLUGS	Pack unit, Ordering unit	Dimensions D, Diameter	Colour selection
	 The screws and wall plugs are suitable for mounting wall uprights on concrete walls. The screw heads can be covered using the provided coloured trim caps depending on the colour of the wall upright. 	PU: 18 OU: 10 PU	1.4", Ø 0.2" 2.4", Ø 0.2"	Galvanised
	SCREWS for U-BRACKETS	Pack unit, Ordering unit	Dimensions D, Diameter	Colour selection
32 50	This screw set is used to fasten wooden shelving to U-brackets.	PU: 40 OU: 10 PU	1.2", Ø 0.1" 1.9", Ø 0.1"	Galvanised
	WALL MOUNTING SET	Pack unit, Ordering unit		
4 x 4 x 12 x	For concrete walls.	PU: 1 OU: 10 PU		

ACCESSORIES	ASSEMBLY MATERIAL			
	CLIP-ON HOLDER for PRO-BRACKETS	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50) = = = = = = = = = = = = = = = = = = =	 1-sided. Made of stainless steel. For supporting wooden and glass shelves. Independent of grid usable. 	PU: 12 OU: 10 PU	0.8" x 0.4" x 0.5"	Stainless steel
	CLIP-ON HOLDER for PRO-BRACKETS	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50) = = = = = = = = = = = = = = = = = = =	 2-sided. Made of stainless steel. For supporting wooden and glass shelves. Independent of grid usable. 	PU: 2 OU: 10 PU	1.8" x 0.4" x 0.6"	Stainless steel
	SUCTION PADS	Pack unit, Ordering unit	Dimensions Diameter	Colour selection
	Suction pads can be inserted into insert holders, clip-on holders and into various brackets, and permit the slip-free positioning of wooden and glass shelves.	PU: 20 OU: 10 PU	Ø 0.5"	Transparent
	TWIN SHELF CONNECTOR	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50)	Usable with the U-brackets.Incl. screws for connection with the U-bracket.	PU: 2 OU: 10 PU	2.2" x 0.6" x 0.8"	Galvanised

ACCESSORIES	ASSEMBLY MATERIAL			
	INSERT HOLDERS for U-BRACKETS	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
33/50	 1-sided. For supporting wooden and glass shelves made of stainless steel, can be assembled with bracket. 	PU: 12 OU: 10 PU	0.9" x 0.4" x 0.7"	Stainless steel
	INSERT HOLDERS for U-BRACKETS	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50)	 2-sided. Made of stainless steel. For supporting wooden and glass shelves made of stainless steel, can be assembled with bracket. 	PU: 12 OU: 10 PU	1.2" x 0.4" x 0.9"	Stainless steel
	INSERT HOLDERS for U-BRACKETS	Pack unit, Ordering unit	Dimensions W x H x D	Colour selection
(32 50)	 2-sided. For supporting wooden and glass shelves, can be assembled with bracket. 	PU: 2 OU: 10 PU	1.6" x 0.4" x 0.7"	Plastic



ELEMENT SYSTEM. More than just wall shelves.

As one of the leading producers for order, shelf and storage systems for the private sector, we convince through functionality, stability and capacity. Our complete assortment, along with all information about our products and company ELEMENT SYSTEM can be found under

www.create-your-space.com

RTS-RIEGERTEAM.DE Art. no. 31500-1201

DIY ELEMENT SYSTEM GmbH
Stettiner Straße 1
89616 Rottenacker
Germany
Phone +49 7393 55-0
Fax +49 7393 55-184
www.element-system.com
info@element-system.com