



DREMEL

2005 Product and Accessories Catalog



For more information contact the Dremel Experts at: 1-800-437-3635 U.S.A. / 1-888-285-3476 CANADA or online at: www.dremel.com

DREMEL

Introduction

Introduction

Corded	4-5	-5 Dremel® High Speed Rotary Tools			
Rotary Tools	6-8	Dremel® 400 Series XPR™ Rotary Tool			
	9	Digital High Speed			
	10-11	MultiPro Variable Speed			
	12	MultiPro Two Speed and Single Speed			
		mann to the opeca and enight opeca			
Cordless	13	Alkaline Cordless Kits			
Rotary Tools	14-15	10.8V Lithium-Ion Cordless			
,	16-17	MultiPro Cordless Tools			
	10 17	mann to continue to the contin			
Attachments	18	FlexLite™ Attachment			
Attachments	19	XPR™ Attachments			
	20	Plunge Router and Grout Removal Attachments			
	21	Cutting Kits			
	22	Workstation Attachment			
	22	Right Angle and Tool Holder Attachments			
	23	Sharpening and DREMELite™ Attachments			
	24	Flex Shaft Attachments			
	24-25	Miscellaneous Attachments			
	25	Router Table and Mini Saw Attachments			
	26-27	Carving / Engraving Accessories			
Accessories	28	Routing Accessories			
	28-29	Grinding Accessories			
	30-31	Cutting Accessories			
	32-33	Cleaning / Polishing Accessories			
	34-35	Sanding Accessories			
		Miscellaneous Accessories			
	36				
	37-39	Accessory Kits and Sets			
	40-41	18" Variable Speed Scroll Station			
Scroll Saws	42-43	16" Variable Speed Scroll Saw			
	44	Scroll Saw Blades			
	-9-4	JOION JUW DIQUES			
	45	VersaTip™ Multipurpose Tool and Accessories			
Other Tools	46-47	Contour Sander and Accessories			
	48	Engraver			
	70	g			

Customer Support

Answering questions for consumers about our tools is accomplished by a well-prepared staff known as the Dremel Experts. With over 450 total years of combined work experience, the Dremel Experts are ready to serve you.

Call 1-800-437-3635 USA. 1-888-285-3476 CANADA.



What is a Dremel High Speed Rotary Tool?

The Dremel rotary tool is lightweight, compact and versatile, which makes it very "friendly". This tool works differently from any other tool you've ever owned. With more than 150 available accessories, you can use it to cut, sand, shape, drill, buff, grind, polish, rout, etch, clean and more. You'll find hundreds of uses for the tool around the house.



Just How Does the Rotary Tool Work?

The rotary tool doesn't work like other tools that rely on brute force to muscle through jobs. The Dremel rotary tool uses speed. Very high speed! It actually spins at rates up to 35,000 rpm. In fact, at 35,000 rpm a Dremel rotary tool with a high-speed cutting bit can make an incredible 4,000 cuts a second! It's what we call "The Dremel Speed Advantage!" The speed does all the work. You just guide the tool.



The Tool that Performs When Other Tools Won't.

We talk to Dremel tool owners all the time. A comment we hear fairly often is "If you can't figure out another way to get a job done, you'll find a way to do it with a Dremel rotary tool". It's an amazing performer! Check out the Dremel Owners Club on our web site at www.dremel.com for some unusual and fantastic uses people have found for their Dremel rotary tools.



It's the Right Tool for Detail Work.

With the new XPR[™] Planer, who needs to remove a door from its hinges to fix a stuck door? With a drywall bit, who needs a keyhole saw to make a hole for an electrical outlet? You get the picture. Obviously, a Dremel rotary tool won't replace all your other tools. (It makes a lousy hammer.) But for a lot of jobs that you only rarely tackle, the Dremel rotary tool makes a great alternative solution. That's why a lot of people tell us the first thing they think when faced with any job around the house is "How can I use my Dremel tool here?"

Corded Rotary Tools

DREMEL400 XPR

- Maximum performance across all speeds 5,000 35,000 RPM.
- Increased performance for new XPR attachments.
- Speed dial settings for ideal control and precision.
- Lock-out collet button feature for quick accessory changes.
- A must have for those serious about tools.

DIGITAL VARIABLE SPEED

- 5,000-35,000 RPM
- Digital technology for controlled speed setting and performance.
- LCD readout for accurate speed setting.
- Delivers precision and control.

MultiPro[®]

VARIABLE SPEED

- The original Dremel tool.
- 5,000-35,000 RPM
- Provides improved ergonomics, precision and control.
- Ideal for a wide range of special and do-it-yourself projects using various speed ranges for added versatility.

MultiPro°

TWO SPEED

- 15,000 and 35,000 RPM
- Ideal for multiple applications on a variety of materials.
- Replaceable motor brushes help extend tool life.

MultiPro®

SINGLE SPEED

- 35,000 RPM
- Ideal for grinding, sanding, carving and cutting.
- Can be used with external speed control.



Motor: 120V, 50-60 Hz, AC, 1.15 Amps. Power Cord: 10' (3,0m)



Motor: 120V, 50-60 Hz, AC, 1.15 Amps. **Power Cord:** 6' (1,8m)





Power Cord: 6' (1.8m)

4 5

Motor: 120V, 50-60 Hz, AC, 1.15 Amps.

DREMEL400 XPR

Precision Control

Ball bearing design for smooth performance.

Maximum Versatility

Works with ALL existing Dremel attachments and accessories plus new XPR attachments.

Easy to Handle

Ergonomic styling for comfort and control.

Lock-Out Collet Button

For quick accessory changes.



On/Off Switch

Positioned up front for easy access

NEW!

Consistent Speeds

Set dial to your desired speeds from 5,000 through 35,000 RPM – no other AC power tool is faster.



Replaceable motor brushes for hours of high performance use.

Increased Performance

DREMELLOOKER

2.0 Amp motor for more performance than ever before.

400 Series XPRTM Kit – Model 400-3/51



Contents

- 400 Series XPR™ Rotary Tool
- XPR™ Storage Case
- Flex Shaft Attachment
- Lawn Mower and Garden Tool Sharpener
- Circle Cutter
- 51 Assorted Accessories
- Quick Start Book
- Quick Change Collet Nut
- Wrench

Deluxe Storage Case

Organizes accessories and attachments better than ever before. New accessory kits snap right into the case for more flexibility than ever!



New XPR™ Attachments

Designed exclusively to utilize the increased power and performance of the XPR Rotary Tool. (See p. 19)





Kit Accessories

150 Drill E	Bit 414	1 Small felt wheel	430 Coarse 1/4" sanding drum
401 Mand	rel 420	HD Emery cut-off wheel (20)	431 Coarse 1/4" sanding band
402 Mand	rel 42°	Polishing Compound	432 Fine 1/2" sanding band
191 High:	speed cutter 422	2 Felt Buff Cone	438 Fine 1/4" sanding band
403 Bristle	e Brush 42	5 Emery wheel	541 Aluminum oxide wheel
407 Coars	e 1/2" sanding drum 42	Fiberglass cut-off wheel	561 Multipurpose Cutting Bit
408 Coars	e 1/2" sanding band 42	3 Carbon Steel Brush	932 Aluminum oxide stone
411 Coars	e sand discs (10) 42 ^o	P Large felt wheel	

400 Series XPRTM Kit - Model 400-3/71



Contents

- 400 Series XPR™ Rotary Tool
- XPR™ Deluxe Storage Case
- XPR™ Planer
- Flex Shaft Attachment
- Circle Cutter
- 71 Assorted Accessories
- Quick Start Book
- Quick Change Collet Nut
- Wrench

Kit Accessories

150 E	Drill Bit	414 Small felt wheel (2)	432 Fine 1/2" sanding band (2)
401 N	Mandrel	420 HD Emery cut-off wheel (20)	438 Fine 1/4" sanding band (2)
402 N	Mandrel	421 Polishing Compound	540 1-1/4" Cut-off wheel bulk (2)
109 E	Engraving cutter	422 Felt Buff Cone	541 Aluminum oxide wheel
191 F	High speed cutter	425 Emery wheel (2)	561 Multipurpose Cutting Bit
403 E	Bristle brush	426 Fiberglass cut-off wheel	932 Aluminum oxide stone
404 E	Bristle brush	428 Carbon Steel Brush	953 Aluminum oxide stone
407 (Coarse 1/2" sanding drum	429 Large felt wheel (2)	8193 Aluminum oxide stone
408 (Coarse 1/2" sanding band (2)	430 Coarse 1/4" sanding drum	84922 Silicon carbide stone
411 (Coarse sand discs (15)	431 Coarse 1/4" sanding band (2)	85602 Silicon carbide stone

400 Series XPRTM Kit – Model 400-6/90




Contents

- 400 Series XPR™ Rotary Tool
- XPR™ Deluxe Storage Case
- XPR™ MultiSaw
- XPR™ Planer
- Flex Shaft Attachment
- FlexLite™
- Cutting Guide
- Circle Cutter
- 90 Assorted Accessories
- Quick Start Book
- Quick Change Collet Nut
- Wrench

Kit Accessories

150 Drill Bit	414 Small felt wheel (5)	438 Fine 1/4" sanding band (3)
401 Mandrel	420 HD Emery cut-off wheel (20)	540 1-1/4" Cut-off wheel bulk (3)
402 Mandrel	421 Polishing Compound	541 Aluminum oxide wheel
109 Engraving cutter	422 Felt Buff Cone	561 Multipurpose Cutting Bit
191 High speed cutter	425 Emery wheel (4)	932 Aluminum oxide stone
194 High speed cutter	426 Fiberglass cut-off wheel (2)	952 Aluminum oxide stone
403 Bristle Brush	428 Carbon Steel Brush	953 Aluminum oxide stone
404 Bristle brush	429 Large felt wheel (2)	8193 Aluminum oxide stone
407 Coarse 1/2" sanding drum	430 Coarse 1/4" sanding drum	84922 Silicon carbide stone
408 Coarse 1/2" sanding band (3)	431 Coarse 1/4" sanding band (3)	85422 Silicon carbide stone
411 Coarse sand discs (20)	432 Fine 1/2" sanding band (3)	85602 Silicon carbide stone

Digital High Speed Rotary Tool – Model 398



Digital LCD readout. Provides accurate speed readouts in 1,000 RPM increments.

"Soft Start". Allows the tool to come up to a selected speed gradually.

Separate on/off and variable speed buttons.

Provides convenient speed adjustments and maintains selected speed, even when tool is switched off.



Variable speeds (5,000-35,000 RPM). Provides maximum control & precision.

Replaceable motor brushes. Longer tool life.



Ergonomic design.
Balanced, easy to handle and comfortable to use.

Unique fan design. Maximizes airflow for cool motor performance.

Ball bearing construction. Smooth and quiet operation.



Digital High Speed Rotary Tool Kit - Model 3981-01

Contents

- Digital High Speed Rotary Tool
- Small Window Case
- Dremel Chuck
- 50 Assorted Accessories
- Quick Start Book
- Wrench

eei	d Rotary Tool Kit	– Model	<i>3981-0</i> 2
	Kit Accessories		

	t Accessories	
106	Engraving cutter	420 Heavy duty cut-off wheel (10)
150	Drill bit	425 Emery wheel
191	High speed cutter	426 Fiberglass cut-off wheel (2)
401	Mandrel	429 Felt wheel
402	Mandrel	430 Coarse 1/4" sanding drum
403	Bristle brush	431 Coarse sanding band (3)
407	Coarse 1/2" sanding drum	432 Fine sanding band (3)
408	Coarse sanding band (2)	438 Fine sanding band (2)
409	Emery cut-off wheels (2)	932 Aluminum oxide stone
411	Coarse sand discs (10)	8193 Aluminum oxide stone
414	Small felt wheels (2)	84922 Silicon carbide stone
415	Dressing stone	

Corded Rotary Tools

MultiPro High Speed Rotary Tool

- The original Dremel tool.
- 5.000-35.000 RPM.
- Provides improved ergonomics, precision and control.

• Ideal for the widest range of special and do-it-yourself projects using various speed ranges for added versatility.

Comfort Grip Housing

Anti-slip comfort grip housing provides better control, easier handling.

High Speed

(5,000-35,000 RPM) . . . speed does the work.

Universal Motor with **Ball Bearings**

Ball Bearings help keep motor running cool under load.

Click & Set On/Off Switch

DREMEL

. . . match the speed to the job.

Replaceable **Motor Brushes**

Corded Rotary Tools

... 5 times longer motor life.

MultiPro Rotary Tool Kit - Model 395

Kit Accessories Contents

150 Drill Bit

401 Mandrel

402 Mandrel

407 Coarse 1/2" sanding drum

409 Emery cut-off wheels (2)

414 Small felt wheels (2)

425 Emery wheel

8193 Aluminum oxide stone

- MultiPro Variable Speed Rotary Tool
 - Wrench

Quick Start Book

10 Assorted Accessories



MultiPro Rotary Tool Kit – Model 3962-02

Contents

- MultiPro Variable Speed Rotary Tool
- Small Window Case
- Dremel Chuck
- 75 Assorted Accessories

Quick Start Book

- Quick Change Collet Nut
- Wrench

Kit Accessories

- 150 Drill Bit
- 191 High speed cutter
- 401 Mandrel
- 402 Mandrel
- 407 Coarse 1/2" sanding drum
- 408 Coarse 1/2" sanding band (3)
- 409 Emery cut-off wheel (5)
- 411 Coarse sanding discs (36)
- 414 Small felt wheel (4)
- 420 Heavy duty emery
- cut-off wheel (3)
- 425 Emery wheel (2)
- 426 Fiberglass cut-off wheel
- 429 Large felt wheel (4)
- 430 Coarse 1/4" sanding drum
- 431 Coarse 1/4" sanding band (3)
- 432 Fine 1/2" sanding band (3)
- 438 Fine 1/4" sanding band (3) 541 Aluminum oxide wheel
- 8193 Aluminum oxide stone

DREME

Two Speed MultiPro Kit - Model 2850-02

• Ideal for multiple applications on a variety of materials.

MultiPro Two Speed

Small Window Case

• 40 Assorted Accessories • Wrench

Rotary Tool

Contents Kit Accessories

130	DI III DIL
401	Mandrel
402	Mandrel
407	Coarse 1/2" sanding drum
408	Coarse 1/2" sanding band (3)
409	Emery cut-off wheel (5)
411	Coarse sanding disc (5)
414	Small felt wheel (4)

420 HD Emery cut-off wheel (2)

150 Drill hit

425 Emery wheel (2) 426 Fiberglass cut-off wheel 429 Large felt wheel (4) 430 Coarse 1/4" sanding drum 431 Coarse 1/4" sanding band (2) 432 Fine 1/2" sanding band (2) 438 Fine 1/4" sanding band (3) 541 Aluminum oxide wheel

8193 Aluminum oxide stone



Quick Change

Quick Start Book

Collet Nut

Single Speed MultiPro Tool Kit – Model 275-02

• Ideal for sanding, carving and drilling.

Contents

- MultiPro Single Speed Rotary Tool
- Quick Change Collet Nut
- 10 Assorted Accessories
- Quick Start Book
- Wrench

Kit Accessories

150 Drill bit

401 Mandrel

402 Mandrel

407 Coarse 1/2" sanding drum

408 Coarse 1/2" sanding band

414 Small felt wheel

420 HD Emery cut-off wheel (2)

425 Emery wheel

429 Large felt wheel



Alkaline Cordless Kits

- 6.0 volts of power and two speeds for light duty precision jobs.
- 6,000 / 12,000 RPM
- Kits use 4 AA batteries (not included).

Golf Cleaning Kit – Model 760-01*

- Cleans clubs in seconds.
- Case easily attaches to your golf bag.
- Cleans club faces and grooves for improved ball control and accuracy.

Contents

Kit Accessories

 Alkaline 2 Speed Cordless Rotary Tool

Carrying Bag

 Quick Change Collet Nut

Wrench

403 Bristle Brush

535 Brass Brush



- · Quickly, easily, and safely trim your pet's nails in minutes.
- No more painful nail clipping.

Contents

Kit Accessories

 Alkaline 2 Speed Cordless Rotary Tool

Model 761-01*

 Quick Change Collet Nut

Wrench

430 Coarse 1/4" sanding drum

438 Fine sanding band (2)



Cordless Manicure Kit -Model 762-01*

- Maintain your nails at home with the convenience of a cordless manicure tool.
- Includes everything needed to create beautiful salon style results.

Contents

Alkaline 2 Speed

Cordless Rotary Tool

 Quick Change Collet Nut

Wrench

Kit Accessories

430 Coarse 1/4" sanding drum 438 Fine sanding band (2)

414 Small felt wheels (2)

84922 Silicon carbide stone

401 Mandrel

*In Canada: Golf Kit 760-35, Pet Kit 761-35, Manicure kit 762-35





Cordless Rotary Tools

DREMEL LITHIUM-ION) COROLESS

Higher Speeds

5,000-35,000 RPM, Corded performance in a cordless tool.

Variable Speeds

Handle a greater range of applications with more precision.

Increased Versatility

Over 150 attachments and accessories available.

Soft Grip

Designed for superior control and balance.

Small and Lightweight

For easier handling and less fatique.

Battery Fuel Gauge

Know when it's time to recharge.

High Capacity 10.8V Lithium-Ion Battery Pack

Cordless Rotary Tools

For longer run-times.

The Power and Freedom

10.8V Lithium-Ion Cordless Rotary Tool Kit - Model 8000-01*







Contents

- 10.8V Lithium-Ion Cordless Rotary Tool
- Heavy Duty Storage Case
- Quick Change Collet Nut
- 3-Hour Charger
- 60 Assorted Accessories
- Quick Start Book
- Wrench

Kit Accessories

- 150 Drill Bit
- 401 Mandrel
- 402 Mandrel
- 109 Engraving cutter
- 191 High speed cutter
- 407 Coarse 1/2" sanding drum
- 408 Coarse 1/2" sanding band (4)
- 409 Emery cut-off wheel (15)
- 411 Coarse sand discs (10)
- 414 Small felt wheel (5)
- 420 HD Emery cut-off wheel (2)
- 425 Emery wheel (2)
- 429 Large felt wheel (3)
- 430 Coarse 1/4" sanding drum
- 431 Coarse 1/4" sanding band (2)
- 432 Fine 1/2" sanding band (3)
- 438 Fine 1/4" sanding band (3)
- 541 Aluminum oxide wheel
- 932 Aluminum oxide stone
- 8193 Aluminum oxide stone
- 84922 Silicon carbide stone

to Tackle Any Project, Anywhere!

10.8V Lithium-Ion Cordless Rotary Tool Accessories



Lithium-Ion Battery Pack - Model 855-01



Lithium-Ion 3-Hour Charger - Model 856-01

Why Lithium-Ion Cordless?

50% More Power†. Handle the tough jobs!

100%

75%

50%

25%

0%

Lithium-

lon

40% More Speed[†]. Highest speed available in cordless rotary tools!

BATTERY CHARGE AFTER 4

MONTHS STORAGE

0%

Standard

Always Ready. When in storage, battery holds a charge 6 times longer than standard NiCd batteries.

No Memory Effects. Standard batteries must be drained before recharging. Lithium-Ion

batteries can be recharged at any time without ever damaging the original charge capacity or run time!

† Compared to previous cordless model

*In Canada: 10.8V Lithium-Ion Cordless Kit 8000-35

7.2V MultiPro Cordless Kit – Model 7700-02

- Two speed 10,000 20,000 RPM.
- 7.2 volts of power. . . goes anywhere.

Motor	7.2V DC (7,2 V)
2-Speed	10,000/ 20,000 RPM
Collet Capacity	1/32-1/8" (0,79 mm-3,18 mm)
Weight With Battery	12oz. (340 g)



Contents

- 7.2 Two Speed Cordless MultiPro
- Quick Change Collet Nut
- Portable Storage Bag
- Accessory Organizer
- 3-Hour Charger
- 50 Assorted Accessories
- Quick Start Book
- Wrench



Unique knurled collet nut. Fast accessory change; no wrench needed.

Removable battery packs. Continuous use to finish your projects.

Light and Compact.Easy to handle and fun to use - anywhere!

Two Speeds. For better control and accuracy.

758 3-Hour Charger. Quick battery recharge with LED light. Light indicates battery is correctly placed into the charger for proper charging.

Kit Accessories

- 150 Drill
- 401 Mandrel
- 402 Mandrel
- 407 Coarse 1/2" sanding drum
- 408 Coarse sanding band (3)
- 409 Emery cut-off wheel (15)
- 414 Small felt wheel (4)
- 420 HD Emery cut-off wheel (2)
- 425 Emery wheel (4)
- 429 Large felt wheel (3)
- 430 Coarse 1/4" sanding drum
- 431 Coarse sanding band (2)
- 432 Fine sanding band (4)
- 438 Fine sanding band (3)
- 540 1-1/4" Cut-off wheel (3)
- 541 Aluminum oxide wheel
- 84922 Silicon carbide stone

MINI**MITE**® *Cordless Kit – Model 750-02*

Take it anywhere. 4.8 volts of power for light duty precision jobs.

Motor	4.8V DC (4,8 V)
2-Speed	6,500/ 13,000 RPM
Collet Capacity	1/32-1/8" (0,79 mm-3,18 mm)
Weight With Battery	9oz. (255 g)



Contents

- 4.8 Two Speed MINIMITE
- 3-Hour Charger
- Quick Change Collet Nut
- 5 Assorted Accessories
- Wrench

Kit Accessories

- 401 Mandrel
- 407 Coarse 1/2" Sanding Drum
- 414 Small felt wheel
- 432 Fine sanding band
- 84922 Silicon carbide stone



Light and Compact.Easy to handle and fun to use - anywhere!

Unique knurled collet nut. Fast accessory change; no wrench needed.



Removable battery packs. Continuous use to finish your projects.

Two Speeds. For better control and accuracy.



756-01 3-Hour Charger. Quick battery recharge with LED light. Light indicates battery is correctly placed into the charger for proper charging.

7700-01 Accessories



7.2V Battery Pack – Model 757-01

3-Hour Battery Charger – Model 758-01

7700 Accessories



7.2V Battery Pack – Model 757





3-Hour Battery Charger – Model 758

750-02 Accessories



4.8V Battery Pack – Model 755-01



3-Hour Battery Charger – Model 756-01

750 Accessories




4.8V Battery Pack – Model 755





3-Hour Battery Charger – Model 756

16



Use this chart to find out which attachments work with your tool, or use the mini charts included with the attachments' descriptions. Adapters may be needed.

☆ Adapter required. Phone the Dremel Experts at 1-800-437-3635 for free adapter.

FlexLite™ – Model FI.400

PL400

FL400

Lights up your work area!

- High intensity LED light.
- Easy to use twist on/off switch.
- Flexible arm for easy positioning.
- Attaches to: 400 Series XPR™ Rotary Tool, 400 Series XPR™ Storage System, 335 Plunge Router, 1800 Scroll Station, and 220 Workstation.
- Includes detachable bench clip.



Attachments

XPR™ MultiSaw – Model MS400

Goes where ordinary saws can't. Like having a jig saw, reciprocating saw, and scroll saw in one compact attachment.



- Universal blade holder uses standard "U" and "T" shank jigsaw blades.
- 3/8" blade stroke for fast and controlled scroll and straight line cutting.
- Pivot foot provides easier control in a variety of materials and shapes.
- Includes one wood cutting blade for straight and curved cutting.
- For use only with the 400 Series XPR™ rotary tool.



285 275 800 780 770 750

XPR™ Planer – Model PL400

Refinish furniture, fix stuck doors and cabinets, chamfer sharp edges, fit wood flooring and more.








- High-speed steel, precision-ground blade lasts up to 500 linear feet.
- 2-1/4" planing width removes approximately 1/64" with each pass.
- Features a 90 and 45 degree edge guide.
- For use only with the 400 Series XPR™ rotary tool.

TOOLS NOT INCLUDED WITH ATTACHMENTS

Attachments



Plunge Router Attachment - Model 335

Converts your corded Rotary Tool into a plunge router.



- Clear base.
- Two depth stops.
- Includes edge guide and circle guide.
- Rout circles, parallel to edge, signs and inlay work and decorative edges.



Routs decorative edges.



Routs accurate circles.

400 398 395 285 275 800 780 770

Grout Removal Attachment – Model 568

For use on wall and floor grout!

- Multiple slide depth adjustment
- 30° angle for controlled cutting
- Guides 180° apart to keep bit centered between tiles
- · Easy screw on mounting
- · Excellent cutting visibility
- Includes 1/16" Grout Removal Bit Model 569. Made of solid carbide, the bit will remove both wall and floor grout.



 Also available: Model 570 1/8" Grout Removal Bit (Not included with 568)





Cutting Kits

Provide controlled cutting in a variety of materials.

- Allows for sturdy controlled cuts with maximum visibility.
- Easy depth adjustment. Set to the correct cutting depth for the material you are working on.
- Multi position depth adjustment
- 2 Easy screw on mounting
- 3 Open arch offers excellent cutting visibility





Attachments

Multipurpose Cutting Kit – Model 565

Includes cutting guide, 2 drywall cutting bits for cutting drywall for electrical boxes & air vents, and 1 multipurpose cutting bit for making cuts in ceiling tile, wood, plastic, fiberglass, drywall, laminate and vinyl siding.



Tile Cutting Kit - Model 566

Includes cutting guide and (1) tile cutting bit for shaping ceramic wall tile around fixtures or plumbing pipes.

Not for use on ceramic floor tile.



TOOLS NOT INCLUDED WITH ATTACHMENTS

Attachments

DREMEL WORK STATION

Model 220

Functions as an articulating drill press that rotates 90°, rotary tool holder, and flex-shaft tool stand.

- Detents click the tool in place in 15° increments from vertical to horizontal.
- "Crow's Nest" provides on-board storage for Dremel accessories.
- Durable, die-cast aluminum base.



400 398 395 285 275 800 780 770 750

Available February 2005

man (400	398	395	285	275	800	780	770	750
		•	•	•	•		•		

Tool Holder and Base – Model 2217

- Firmly holds rotary tools in any position.
- Control workpiece (hands free) for better results.



395 285 275 800 780 770 750

Right Angle Attachment – Model 575

Enhances the versatility of your Dremel rotary tool by allowing you to get into hard-to-reach areas.

- Ball bearings and spiral bevel gears provide smooth and cool operation
- Coupling system allows you to orient the attachment on your tool in 12 different directions
- Quick connect system easily attaches to your rotary tool in place of the housing cap, no wrenches required
- Compact, durable design for those "hard-toreach" places



 400
 398
 395
 285
 275
 800
 780
 770
 750

 •
 •
 •
 •
 •
 •
 •
 •
 •

Lawn Mower and Garden Tool Sharpener – Model 675

The fastest, easiest, safest way to sharpen your lawn mower blade and other garden tools.

- Guide provides optimum sharpening angle.
- Sharpens most rotary lawn mower blades.
- Easy to install and use.
- Long-wearing ABS plastic material.
- · Comfortable ergonomic design.
- Includes grinding stone, #932 (see p.29).



Attachments

400 398 395 285 275 800 780 770 75

Chain Saw Sharpening Attachment – Model 1453

Easily sharpen the dullest of chains.



Contents

- Sharpening attachment
- 3 Sharpening Stones Nos. 453, 454 and 455. (see p. 28)
- Gauge
- 2 Spacers
- Wrench
- Instruction manual



DREMELite™ – Model 677

The new attachment that lights your way!

- Provides visibility in dimly lit areas and increases light on detailed projects.
- Easy to attach, no confusing wires or connections.
- Two extremely long lasting and durable LED lights.
- Uses a magnet threaded onto the tool's output shaft to provide a clever and simple power source.



TOOLS NOT INCLUDED WITH ATTACHMENTS

Attachments

400 398 395 285 275 800 780 770 750

Flex Shaft Attachment -Model 225

Ideal for hard to reach places and fine detail work.

- · Quick connect attach system.
- 36" long cable with new 5" bend radius provides more flexibility.
- · Comfort grip hand piece.
- Integrated shaft lock button.
- Holds up to 1/8" shank.
- · Works with collet system and Dremel chuck.



400 398 395 285 275 800 780 770 750

Shaper/Router Table -Model 231

400 398 395 285 275 800 780 770 750

Converts your corded Rotary Tool into a bench mounted wood shaper.

- · Features an adjustable fence and large 8" x 6" worktable.
- Slot, groove, sand and trim edges.



Flex Shaft Tool Holder - Model 2222

Conveniently suspends any Dremel Rotary Tool above your workbench.

- Perfect for use with the Flex-Shaft attachment.
- Clamps to workbenches up to 1-3/4" thick, and adjusts in height from 12" to 42".
- · Store extra bits on base.





Mini Saw Attachment – Model 670

Works great on wood and all wood-like materials.

- Quick connect system attaches to your rotary tool in seconds.
- Make clean, straight perpendicular cuts up to 1/4" thick.
- · Clear housing provides better visibility.
- Lower guard retracts when not in use to ensure safety.
- Includes blade 546 shown below.



Attachments

Rip/Crosscut Blade - Model 546

- · Long-lasting steel blade.
- 1-1/4" diameter, 48 teeth.
- One blade per package.
- · For use with Mini Saw Attachment only.

Miscellaneous Attachments



Foot Speed Control - Model 221

- Pressure sensitive pedal provides speed control.
- Variable speed from 0 to full RPM.
- 6 Amp. capacity.
- Use only with single speed rotary tools 275 and 732.



D-Vise -Model 2214

- Vise swivels 360° and tilts 180° in all directions.
- Padded jaws open to 2-1/2".



Deluxe Window Storage Case - Model 2610999673

Accessories not included.



Tool Storage Case - Model 15009



Wrench -Model 90962

 For ease of changing bits

TOOLS NOT INCLUDED WITH ATTACHMENTS

24

Carving/Engraving

HIGH SPEED CUTTERS High speed cutters can be used for shaping, hollowing, grooving, slotting, making tapered holes in soft metals, plastics and woods. No. 199 cutter can be used to make small slits.








ENGRAVING CUTTERS Quality cutters for detail engraving, carving, routing in wood, fiberglass, plastic and soft metals.





DIAMOND WHEEL POINTS For fine detail work, engraving, carving, touch-up and finishing. Use on wood, jade, ceramic, glass, hardened steel, semi precious stones and other hard materials. Bits are covered with diamond particles.







Fast cutting sharp teeth for greater material removal. Use on fiberglass, wood, plastic, epoxy, rubber, laminates, particle board and ceramic tile.







TUNGSTEN CARBIDE CUTTERS Use for shaping, smoothing and material removal. Use on hardened steel, stainless steel, cast iron, nonferrous metals, fired ceramics, plastics, hardwoods and other hard materials. Not for use with floor tile.





Routing

Grinding/Sharpening (Continued)

Accessories

ROUTER BITS For routing, inlaying, and mortising in wood and other soft materials. Use with Dremel No. 330 Router Attachment, No. 335 Plunge Router Attachment, and No. 231 Shaper/Router Table. Made of high speed steel.





Grinding/Sharpening

SILICON CARBIDE GRINDING STONES (BLUE / GREEN)

Designed to work well on stone, glass, ceramics, porcelain and non-ferrous metals.





CHAIN SAW SHARPENING STONES Precision ground for quick, easy sharpening of chain saw blades.

Each package contains 2 stones.









ALUMINUM OXIDE GRINDING STONES (ORANGE / BROWN) Use on metals, castings, welded joints, rivets and rust. Ideal


for sharpening, de-burring and general purpose grinding of most materials.








ALUMINUM OXIDE ABRASIVE WHEEL Perfect for cleaning, de-burring, removing rust, and polishing of most metals, including stainless steel.




ALUMINUM OXIDE GRINDING WHEEL Use for de-burring, rust removal and general purpose

grinding.



ABRASIVE POINTS Abrasive points are great for finishing work

and light de-burring. They can be used for paint and rust removal without





Use 409.

420, 426, 456 and

540 with Mandrel 402

Cutting

560

1/16"

1,6 mm

1/8"

DRYWALL, MULTIPURPOSE, TILE AND GROUT ACCESSORIES

Drywall Cutting Bit – Model 560*

Gives you fast clean cuts in drywall.

Multipurpose Cutting Bit – Model 561*

Cuts hardwood up to 3/8" and softwood up to 5/8". Also cuts plastic, fiberglass, drywall, laminate, aluminum & vinyl siding.

Tile Cutting Bit – Model 562*

Cuts ceramic wall tile, cement board, and plaster. (Not for use on floor tile.)

Carbide Grout Removal Bits – Model 569 and Model 570[†]

Ideal for replacing wall and floor grout or removing grout to replace broken tiles.

*Use with cutting guide (page 21)

† Use with grout removal guide (page 20)

RIP/CROSSCUT BLADE - Model 546

For use with Mini Saw Attachment #670 only (page 22). Thickness .023" (0,6 mm)

DIAMOND WHEEL - Model 545

Great for cutting, sawing and carving of hard materials such as marble, concrete, brick, porcelain, ceramics, hard epoxy, soft and hard wood.

Mandrel #402 is included.

Thickness .023" (0,6 mm)

545



Do not run in excess of 20,000 RPM.

CUT-OFF WHEELS

1/8"


3.2 mm

For slicing and cutting metal, wood and plastic. Cut-Off Wheels make it easy to cut or slot bolts, screws, sheet metal, thin wood and plastic. The cut-off wheel cuts only along its edge. Do not attempt to sand or cut curved holes with them.



FIBERGLASS REINFORCED CUT-OFF WHEELS





456 package includes 10 Cut-Off Wheels and a washer set. Washer set only used with 456. Mandrel #402 is sold separately.

12 per pack

CUTTING/SHAPING WHEEL Model 542 (CARBIDE)

For cutting and shaping on soft and hard woods, fiberglass, plastics and laminates.

Do not use on metal.

Mandrel included.


Thickness .070" (1,8 mm)



Cleaning/Polishing

RUBBER POLISHING POINTS - Blue points for finishing and polishing all ferrous metals. Removes small burrs and scratch marks left by grinding and sanding, and cleans and defines grooves. Also effective on many stones and ceramics.







Felt 3/8" dia.



POLISHING ACCESSORIES

Cloth 1" dia.

Ideal for polishing metals and plastics. Using polishing compound No. 421 with wheels produces a high luster.



Felt 1/2" dia. 6 per pack









Use 425

Mandrel

with

402





Emery Impregnated





POLISHING COMPOUND - Model 421

Use with felt or cloth accessories to polish metals and plastics. Compound will remove a dull oxidized film and/or light surface imperfections. A solid compound.



POLISHING WHEEL - Model 520

Use for light stock removal and high luster polishing of metals and hard plastics. The wheel is impregnated with a silicon carbide abrasive and lubricant, eliminating the need for polishing compound.





ABRASIVE BRUSH - Model 538

Dremel's strongest and longest lasting brush. Extra-thick nylon bristles are coated with an abrasive grit for material removal on the toughest jobs. Use for de-burring metal or wood and for removing rust and paint.



Do not run brush in excess of 20,000 RPM.



1/2"



silverware, jewelry and other precious metals: can use with polishing compound.





3/4"







3,2 mm Versatile brush for removing rust and corrosion, polish metal surfaces. De-burr and blend surface junctures, clean electrical components.



3/4" 19,1 mm

428

1/2" 12,7 mm

1/8"

443

STAINLESS STEEL 3,2 mm BRUSHES

Stainless steel brushes do not cause "after-rust" when used on corrosive-resistant materials like pewter, aluminum and stainless steel



530 3/4" 19,1 mm

535

1/2" 12,7 mm

531


1/8" **BRASS BRUSHES**

532

536 537

3,2 mm Brass brushes are nonsparking and softer than steel. They will not scratch soft metals like gold,

copper, brass.





Sanding

Accessories

SANDING BANDS

For rough shaping and smoothing wood and fiberglass; removing rust from metal surfaces; shaping rubber surfaces. Sander bands are easily replaceable on drums, and are available in packages of 6 each.











FLAPWHEELS Flapwheels grind and polish flat or contoured surfaces. They are used most effectively as a finishing sander after heavier surface sanding and material removal is

ППТПП 1/8 3,2 mm







60 GRIT **120 GRIT** 6 per pack 6 per pack 431 438 1/2 Inch Diameter **60 GRIT 120 GRIT** 6 per pack 6 per pack 408 432



Buffs are a great finishing accessory for cleaning and light sanding. They work effectively on metal, wood, aluminum and plastics. Coarse and medium buff included, Coming April 2005, 512 Fine Abrasive Buff.



CARBIDE SANDING BAND

The carbide grit surface is extremely durable and the edges of the band will stay crisp and sharp. Use on a variety of materials including woods, fiberglass, laminates, plastic, and leather. Drum sander mandrel included.





SANDING DISCS

For rough shaping and smoothing wood and fiberglass; removing rust from metal surfaces; shaping rubber surfaces.

> Coarse 180 grit. - 411 Medium 220 grit. - 412

Fine 240 grit. - 413





36 pieces per pack



Use 411, 412 and 413 with Mandrel 402

CARBIDE SHAPING WHEEL

A powerful shaping tool that quickly and efficiently removes material. Easily creates compound curves and works on a variety of materials including woods, fiberglass, laminates, plastic, and leather. Mandrel included.





DREMEL CHUCK - Model 4486

This chuck allows you to quickly and easily change accessories on Dremel rotary tools without changing collets. Accepts accessories with 1/32" - 1/8" shanks. Use with rotary tool models 275, 285, 395, 398, 400, 750, 770, 780, and 800. Also use with Dremel attachments 212, 225, 575, and 961.

Miscellaneous



QUICK CHANGE COLLET NUT KIT -**Model 4485**

Includes Collet Nut and 4 Collets. For use with all rotary tools except models 1, 2 & 260, 270, 280 series 1 or earlier.

Collets also available separately.



DRILL BIT SET - Model 628

	x	1/32" 0,8 mm
	I	3/64" 1,2 mm
	Ι	1/16" 1,6 mm
15.15.15	Ι	5/64" 2,0 mm
184.84	Ι	3/32" 2,4 mm
THE STATE OF THE S	Ι	7/64" 2,8 mm
	Ι	1/8" 3.2 mm





BRAD POINT DRILL BIT SET -Model 631

Titanium coated brad points stay on center and begin drilling immediately. For use on wood.



1/8-IN. DRILL -Model 150*

1/32-IN. DRILL -Model 660 4 pc. per pack. Use with 483 Collet.

3/64-IN. DRILL -Model 661 4 pc. per pack. Use with 482 Collet.

DRESSING STONE - Model 415*


Clean grinding wheels. Shape or reshape for desired applications.



25.4 mm

9,5 mm

MANDRELS



May be used with 429.

402 - Use with 409, 411, 412, 413, 420, 423, 425, 426, 429, 456, 511, 540 and 541

CARBON MOTOR BRUSHES



BRUSH	TOOLS	TYPE
90826*	260	
90827*	270, 280, 370 & 380	
90828*	232 & 332	
90929*	275, 285 & 395	1 & 2
90930	275, 285, 395 & 595	3,4 & 5
90930	6000	1 & 2
90931	398	
90935	732	
90936	Advantage 9000	

*Available as service part only.

Mini Accessory Kits





- Application and material usage information included
- XPR storage case compatible
- Removable organizer tray




CLEANING / POLISHING SET - Model 684-01

Polish a variety of materials to a high luster, clean those tough-to-reach areas, plus a whole lot more!



Pieces












CUTTING / CARVING / SANDING SET -Model 685-01


Collet #481 or Dremel Chuck #4486 needed for use with engraving cutter #107.



Pieces









Accessories

Mini Accessory Kits

SANDING / GRINDING SET - Model 686-01


Sharpen lawn tools, remove rust, sand down a sticking door, and engrave on glass, plus a whole lot more!



DREMEL









GENERAL PURPOSE SET - Model 687-01 Everything you need to cut, carve, sand, grind,

clean, and polish, plus a



Pieces





whole lot more!










CUT-OFF WHEEL SET - Model 688-01


Reslot a screw, cut conduit, sheet metal, rusted hose clamps, plus a whole lot more!



Pieces










HIGH SPEED CUTTER SET - Model 691

Use on soft metals, plastics and wood to shape, groove and carve. Use a light touch and let the speed of the rotary tool do the work.



Pieces



ROUTER BIT SET - Model 692

For routing, inlaying and mortising in wood and other soft materials. Use with #330 Router Attachment, #335 Plunge Router Attachment, and #231 Shaper/Router Table.



Pieces



TUNGSTEN CARBIDE CUTTER

SET - Model 693 Use for shaping, smoothing and removing material on hardened steel, stainless steel, fiberglass, ceramics, cast iron and wood.






DIAMOND POINT SET - Model 694

Use for engraving, carving, finishing and other fine detail work on a variety of materials including wood, glass, ceramic and hardened steel.





SUPER ACCESSORY KIT - Model 697 This versatile and re-usable accessory kit includes everything you need to cut, grind, sand, polish, drill, sharpen, clean and more.
















18" Variable Speed Scroll Station™ – Model 1800



Smooth Cast-iron Table

Finish An extra-smooth finish and sturdy support to provide effortless work piece manipulation

Top Handle

Accepts pin-end and plain-end saw blades **Blade Storage**

Convenient blade storage drawer keeps blades at your fingertips



Top-mounted Controls Up-front controls for easy access

Contents

- 18" Variable Speed Scroll Station™
- 5" Sanding Disc
- Scroll Saw Blade Starter Pack (12 Blade Assortment)

Motor	1.6 A, 120V, 60Hz 1/6HP	Blade Stroke	3/4" (19,1 mm)
Speed	500-1,700 SPM (CPM)	Cutting Capacity	1-3/4" at 0° 1" at 45°
Blade	5" (12,7 cm)	Net Weight	53 lbs. 24,0 kg




Scroll Saws

Power Take-Off Port

Powers a 5" sanding disc (included) and Dremel Flex Shaft model 225 (sold separately)

Tool-less Blade Holder

No tools needed for fast and easy pin or plain-end blade changes InfiniteCut™ Blade Holder Rotates 90° for infinite



Detents lock into place every 15° up to 45° to the left and at 5° to the right with a positive stop at 0° to quickly and easily square the table

Flexible LED Light

Allows movement of the light where needed for improved visibility

Flexible Dust Blower

Adjustable, multidirectional blower keeps the cutting line clear for greater visibility

18" Variable Speed Scroll Station™ Accessories




MAGNIFIER -Model 18505 Zoom in on projects where detail is critical.

SCROLL

SAW STAND -

Model 18500-01 Painted finish resists rusting and leg pads keep stand from slipping. For model 1800 only.



16" Variable Speed Scroll Saw - Model 1680



Contents

- 16" Variable Speed Scroll Saw
- 12 Blade Assortment

Light. An attached 25 watt light to improve visibility during use.

Motor	1.4 A, 120V, 60Hz 1/6HP	Blade Stroke	3/4" (19,1 mm)
Speed	500-1,600 SPM (CPM)	Cutting Capacity	2" at 0° 1" at 45°
Blade	5" (12,7 cm)	Net Weight	40 lbs. 18.15 kg



Variable Speed. Speeds of 500 - 1,600 strokes per minute to cut a variety of materials.

Top-Mounted Controls. Upfront controls for easy access.

Dust Blower. An adjustable, multidirectional blower to keep the cutting line clear.

Tool-less Blade Holder. No tools needed for fast and easy pin or plain-end blade changes.



Smooth Table Finish. An extra smooth finish to provide effortless workpiece manipulation.

Cast Iron Table. To evenly support your workpiece.

SCROLL SAW STAND - Model 16500-01 Painted finish resists rusting and leg pads keep stand from slipping. For models 1671, 1672, 1680 and 1695.




Blade Holder Storage. Handy storage to keep extra blades at your fingertips.



Two-Way Table Tilt. Tilts 45° both left and right for two-way bevel cutting.

Table Angle Detents. Angle indentations every 15° for consistent bevel cutting, with an indent at 0° to quickly and easily square the table.



Variable Speed Scroll Saw Blades

	Universal Number	Width	Thickness	Teeth per inch
PIN-END BLADES Eas cutting in hard and soft			aw. For tig	ht radius
411	7	.110"	.018"	15

16411	7	.110"	.018"	15
16412	7	.110"	.018"	10
16413	2/0	.070"	.010"	18.5

PLAIN-END BLADES Allow for extremely tight radius cutting and intricate cuts in wood, plastic, and fibrous materials. 5 per pack.

16446	5	.038"	.016"	12.5
16453	12	.062"	.024"	9.5

METAL PIERCING BLADES Cut precious and non-ferrous metals. Must be used at slow speed. Perform best when lubricated with bees wax. 5 per pack.

16483	5	.033"	.016"	36

REVERSE TOOTH BLADES Provides a smooth, splinter free finish. Leaves a clean, sharp edge on both the top and bottom of your wood piece. 12 per pack.

16431	2R	.029"	.012"	20F/14R
16432	5R	.038"	.016"	12.5F/14R

Universal Number	Kerf	Teeth per inch

SPIRAL BLADES Cut in all directions without turning the work piece. 5 per pack.

16463	2	.034"036"	41

CARBIDE COATED BLADES - **60 Grit** Tungsten carbide coated blades shape and cut ceramic wall tiles. Also for cutting thin wood. Cut in any direction without turning your workpiece. Not for use on floor tiles. 1 per pack.

VersaTip™ Multipurpose Tool – Model 1550

Multipurpose tool for wood burning, soldering, hot knife cutting of styrofoam and plastics, cutting and fusing rope.

Max. Tip 1,050° F (565°C)


Volts 110-120V, AC

Watts 30

Tool Length 7-3/8" (187,3 mm)

Contents

- VersaTip™ Tool
- 5 Tips (470, 471, 473, 474 & 499)
- Tool Stand
- Handy Tip Storage Tube





Maximum tip temperature 1,050° F. Safely burn faster and darker.

6 Different design tips. Replaceable and interchangeable for maximum versatility.



Short shaft length.
Excellent control of tip.
Ergonomic, stay cool
design. Maximum user
comfort and control.

Versatile tool stand.
Convenient for storage and protects work surface.



Soldering Tip -

Model 470



Grading Tip – Model 472



Script Tip – Model 473



Fine Cutting Tip – Model 474






Other Tools

Contour Sander

Has the power and precision needed to get even the toughest sanding jobs done quickly and easily.







Sands Flat and Contoured Surfaces

Wide selection of accessories. A variety of sandpaper, contour shapes and detail pads sand a range of curved, angled shapes and larger surfaces to eliminate hand sanding.



4,000-10,000 variable strokes per minute. Variable speed gives you all the power and control to complete a variety of sanding tasks.

Long-lasting reusable sanding tubes. Sanding tubes slip easily over all contours, can be rotated 360° and are cloth backed for longer life.

Exclusive quick change accessory release. Quickly change from contour to detail pad without extra keys or wrenches.

Longer tool life. Cool-running ball bearing construction and easily replaceable motor brushes help sander perform longer and operate more efficiently.



Tool Weight	1.75 lbs. (793,8g)
Volts	120 V AC
Amps.	1.15 (1,15)
Power Cord	10' (3 m)
Strokes per Minute	4,000-10,000
Stroke Length	.060" (1,5 mm)

Contour Sander Kit – Model 6000-01

Contents

- Variable Speed Contour Sander
- 10 Sanding Contours
- 3 Sanding Tubes
- Detail Sanding Pad
- 3 Sheets of Detail Pad Sandpaper
- Dremel Tool Bag



Sanding contours included in kit 6000-01

1/8" 1/2" 1/8" 1/4" 1/2" Flat 30° 3,2 mm 6,4 mm 12,7 mm 3,2 mm 6,4 mm 12,7 mm 6023 6030 6019 6021 6025 6029

Contour Accessories

SANDING TUBES

6050 - 5 piece 80 grit

6052 - 5 piece 120 grit

6054 - 5 piece 220 grit

6055 - Assortment

1 piece 80 grit2 piece 120 grit

- 2 piece 220 grit



Other Tools

SHUTTER EXTENSION PAD – Model 6046





DETAIL PAD SANDPAPER

6060 - 5 piece 80 grit

6065 - Assortment

6061 - 5 piece 120 grit

1 piece 80 grit2 piece 120 grit

6062 - 5 piece 220 grit

- 2 piece 220 grit



Engraver – Model 290-01

Identify and personalize your valuables. Use for decorative engraving.

• Engraves metal, glass, wood, plastic, and ceramics.



Contents

- Engraver Tool
- Carbide Point (9924)
- Letter/ number template

Motor	115V, AC/115 V, 60 Hz, .2 Amps./0,2 A
Strokes	7,200/SPM
Tool Weight	12 oz. (340g)



Light and compact design. Comfortable use for precision engraving performance.



Stroke adjustment dial. Regulates engraving depth from fine lines to deep grooves.



Replaceable carbide and diamond points.
Engrave on soft or hard materials.



Carbide Point – Model 9924 (Normal applications)



Diamond Point – Model 9929 (For continuous use)