

ANTISTATIC 2200 SERVICE-SET

The tool set for mobile use at electrostatically endangered components



2200 **BERNSTEIN** SERVICE-SET ANTISTATIC with tool set

2201 Case with zip fastener, without tools

2220 **BERNSTEIN** SERVICE-SET ANTISTATIC with tool set in **conductive** case

2221 Conductive case with zip fastener, without tools

Description:

Elegant, black zipper case, with wine red lining and transparent pockets for 12 tools and a foldable antistatic workbench pad with accessories. Art. 2220 complete made from conductive black imitation leather

Outside dimensions: 320 x 250 x 50 mm (when closed)

Weight with tools: approx. 0.950 kg

Tool set:

No.	Description of individual tools
2-620	PLCC extractor
3-601-13	Side cutters , 120 mm, for hard wire up to 0.4 mm Ø, for soft wire up to 1.0 mm Ø, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard
3-632-13	Flat nose pliers , 120 mm, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard
3-633-13	Snipe nose pliers , 120 mm, steel-polished, box joint, double leaf spring, with conductive black hand-guard
4-601	Screwdriver 50 x 0.8 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-605	Screwdriver 60 x 2.0 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-606	Screwdriver 60 x 2.5 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-621	Cross-recess screwdriver size 000 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip

No.	Description of individual tools
4-622	Cross-recess screwdriver size 00 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-623	Cross-recess screwdriver size 0 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
5-191	Tweezers , 120 mm, made from conductive plastic material, reinforced with glassfibre, with straight, rounded tips
5-192	Tweezers , 120 mm, made from conductive plastic material, reinforced with glassfibre, with straight, 3 mm flat-hand tips
9-354	ESD handling set , consisting of: foldable, green workbench pad (surface resistance according to DIN 53482: approx. 10 ⁸ ohm), 500 x 400 x 0.35 mm, contact bracelet 9-342, earth wire 2500 mm long with 1 Mohm safety resistor