

# Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.



The right tool at a glance, thanks to the printed screw symbol on the handle end.



## For slotted screws.



320N

SoftFinish® electric slotted screwdriver.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380. Manufactured acc. to IEC 60900:2012.

Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	⌀	↔	⊖	↔	↔	↔
00819	2.0	60	0.4	164	23	10
00820	2.5	75	0.4	179	23	10
00821	3.0	100	0.5	204	23	10
00822	3.5	100	0.6	204	23	10
00823	4.0	100	0.8	211	30	10
00824	4.5•	125	1.0	236	30	10
00825	4.5•	175	1.0	286	30	5
31863	4.5•	200	1.0	311	30	10
00826	5.5	125	1.0	243	36	10
00827	5.5•	175	1.0	293	36	5
00828	6.0•	150	1.2	268	36	10
00829	6.5	150	1.2	268	36	10
00830	8.0	175	1.2	299	41	10
00831	8.0	175	1.6	299	41	10
00832	10.0	200	1.6	324	41	10

• Additional dimension. Non-DIN size.



### Wiha SoftFinish® electric.

- Safety when working with live equipment up to 1,000 V AC and 1,500 V DC
- Each screwdriver is individually tested in a water bath at 10,000 volts according to IEC 60900:2012
- Awarded the GS symbol for tested safety
- Multi-component SoftFinish® handle provides maximum user comfort

Applications on live equipment are subject to very special requirements. The focus is on absolute user safety and Wiha demonstrates this with a wealth of details.

The high quality blade insulation is moulded directly onto the blade and therefore guarantees safety when working on live equipment up to 1,500 V DC / 1,000 V AC. To maintain this safety, each screwdriver of the SoftFinish® electric series is individually tested in a water bath at 10,000 Volts according to IEC 60900:2012.

The roll-off protection and the special handle geometry offer optimum handling and electrical safety, even in critical applications.



**Safety Notice:**

When working with VDE tools, observe the national safety and accident prevention regulations!



**Slotted/ Phillips and slotted/ Pozidriv sets.**



1000 V  
IEC 60900:2012

**320N K6** SoftFinish® electric slotted/ Phillips screwdriver set, 6 pcs.  
Individually tested protective insulation  
1,000 V AC, VDE and GS tested.

- Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.
- Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Standards: Manufactured acc. to IEC 60900:2012.
- Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	Series				
00833	320N K6				1
⓪	320N	3.0x100	4.0x100	5.5x125	6.5x150
⊕	321N	PH1x80	PH2x100		

**Slotted/Phillips- and nut driver set.**



1000 V  
IEC 60900:2012

**320N K7** SoftFinish® electric slotted/ Phillips screwdriver set, 7 pcs.  
Individually tested protective insulation  
1,000 V AC, VDE and GS tested.

- Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.
- Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Standards: Manufactured acc. to IEC 60900:2012.
- Application: For all work on or around electrical components up to 1,000 V AC.

with  
voltage tester

Order-No.	Series				
00834	320N K7				1
⓪	320N	2.5x75	4.0x100	5.5x125	6.5x150
⊕	321N	PH1x80	PH2x100		
⓪	255-11L	3.0x60			



1000 V  
IEC 60900:2012

**320N ZK6 SO** SoftFinish® electric slotted/ Pozidriv screwdriver set, 6 pcs.  
Individually tested protective insulation 1,000 V AC, VDE and GS tested.

- Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.
- Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Standards: Manufactured acc. to IEC 60900:2012.
- Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	Series				
25477	320N ZK6 SO				1
⓪	320N	2.5x75	3.5x100	4.5x125	5.5x125
⊕	324	PZ1x80	PZ2x100		



1000 V  
IEC 60900:2012

**322 K5** SoftFinish® electric hex nut driver set, 5 pcs.  
Individually tested protective insulation  
1,000 V AC, VDE and GS tested.

- Blade: Chrome-vanadium steel, through hardened, black-finish. Insulation moulded directly onto blade. Deep drawn socket.
- Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
- Standards: Manufactured acc. to IEC 60900:2012.
- Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	Series				
29466	322 K5				1
⓪	322	5.5x125	7x125	8x125	10x125
		13x125			