

# Wiha SoftFinish®.

The convenient expert for dry applications.



product  
design  
award

1997



*The right tool at a glance, thanks to the printed screw symbol on the handle end.*

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum through forces in dry working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



*The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.*

*Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.*



*Blade with hex bolster for wrenches to use on particularly tight screws.*



## Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

# Wiha SoftFinish®.

The convenient expert for dry applications.

## Sets with round blades.



**302 HK6 SO** SoftFinish® slotted/ Phillips screwdriver set, 6 pcs.  
Round blades.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Particularly suitable for dry applications.

Order-No.	Series					
07152	302 HK6 SO					1
⓪	302	3.5x100	4.5x125	5.5x150	6.5x150	
⊕	311	PH1x80	PH2x100			

## Sets with round blades.



**302 HK6 01** SoftFinish® slotted/ Phillips/ Pozidriv screwdriver set, 6 pcs.  
Round blades.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Particularly suitable for dry applications.

Order-No.	Series				
26113	302 HK6 01				1
⓪	302	4.0x100	5.5x125	6.5x150	
⊕	311	PH1x80	PH2x100		
⊕	313	PZ2x100			



**302 ZK6 SO** SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs.  
Round blades.

Order-No.	Series					
07153	302 ZK6 SO					1
⓪	302	3.5x100	4.5x125	5.5x150	6.5x150	
⊕	313	PZ1x80	PZ2x100			



**311 K6** SoftFinish® Phillips/Pozidriv screwdriver set, 6 pcs.  
Round blades.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Particularly suitable for dry applications.

Order-No.	Series				
26146	311 K6				1
⊕	311	PH1x80	PH2x100	PH3x150	
⊕	313	PZ1x80	PZ2x100	PZ3x150	