


Sheets and accessories



Perforated sheets

Color	Thickness	Dim. a	Dim. b	Packaging	Min.OU	Width	Length	EAN / item no.
1 Round hole sheet in anodized aluminium								
silver	0.7 mm	1.5 mm		sealed	5 pcs.	250mm	500 mm	4001116373640
silver	0.7 mm	1.5 mm		sealed	5 pcs.	120 mm	1000 mm	4001116373602
silver	0.7 mm	1.5 mm		sealed	5 pcs.	200 mm	1000 mm	4001116373619
silver	0.7 mm	1.5 mm		sealed	5 pcs.	300 mm	1000 mm	4001116373626
silver	0.7 mm	1.5 mm		sealed	5 pcs.	600 mm	1000 mm	4001116373633
silver	0,7 mm	1,5 mm		loose	1 pc.	1000mm	2000 mm	4001116373695
silver	0.7 mm	4.0 mm		sealed	5 pcs.	250 mm	500 mm	4001116374142
silver	0.7 mm	4.0 mm		sealed	5 pcs.	120 mm	1000 mm	4001116374104
silver	0.7 mm	4.0 mm		sealed	5 pcs.	200 mm	1000 mm	4001116374111
silver	0.7 mm	4.0 mm		sealed	5 pcs.	300 mm	1000 mm	4001116374128
silver	0.7 mm	4.0 mm		sealed	5 pcs.	600 mm	1000 mm	4001116374135
2 Round hole sheet in uncoated aluminium								
uncoated	1.5 mm	4.5 mm	15.0 mm	sealed	5 pcs.	250 mm	500 mm	4001116378041
uncoated	1.5 mm	4.5 mm	15.0 mm	sealed	5 pcs.	120 mm	1000 mm	4001116378003
uncoated	1.5 mm	4.5 mm	15.0 mm	sealed	5 pcs.	200 mm	1000 mm	4001116378010
uncoated	1.5 mm	4.5 mm	15.0 mm	sealed	5 pcs.	300 mm	1000 mm	4001116378027
uncoated	1.5 mm	4.5 mm	15.0 mm	sealed	5 pcs.	600 mm	1000 mm	4001116378034
uncoated	1,5 mm	4,5 mm	15,0 mm	loose	5 pcs.	1000mm	2000 mm	4001116378096
2 Round hole sheet in galvanized steel								
galvanized	1.5 mm	4.5 mm	15.0 mm	loose	5 pcs.	250 mm	500 mm	4001116378546
galvanized	1.5 mm	4.5 mm	15.0 mm	loose	5 pcs.	120 mm	1000 mm	4001116378508
galvanized	1.5 mm	4.5 mm	15.0 mm	loose	5 pcs.	200 mm	1000 mm	4001116378515
galvanized	1.5 mm	4.5 mm	15.0 mm	loose	5 pcs.	300 mm	1000 mm	4001116378522
galvanized	1.5 mm	4.5 mm	15.0 mm	loose	5 pcs.	600 mm	1000 mm	4001116378539
galvanized	1,5 mm	4,5 mm	15,0 mm	loose	5 pcs.	1000mm	2000 mm	4001116378591

Hardware catalogue - 99005 024 - 71708 - 0705