

Wiha SYSTEM 6.

The space-saving all-rounder.



Are you looking for a versatile and space-saving system for your toolbox or for use on the road?

Then our **SYSTEM 6** exchange tools with 6 mm reversible blades and suitable handles are exactly the right solution for you. Just select the right variations for your application among the wide choice of handles and reversible blades or simply decide for one of the **SYSTEM 6** sets.


- The starter sets with tough roll-up bag are already equipped with the most common reversible blades, but also offer room for a maximum of 11 further reversible blades.
- The extensive professional sets are the perfect solution if you need a professional universal set in a rigid box.
- The practical roll-up bag sets are especially handy and space-saving.

The Wiha **SYSTEM 6** reversible blade systems are high quality products with industrial quality that fulfill maximum demands thanks to first class materials and manufacturing. The 150 mm long reversible blades are manufactured from chrome-vanadium molybdenum steel and are through hardened. The various handles are particularly ergonomically designed and guaranteeing optimal power transmission.

With the Wiha **SYSTEM 6** series you always have the right tool on hand for a wide range of applications - ideal for industry, trade and the ambitious handymen.



The Wiha SYSTEM 6 range is the compact all-rounder for different applications.



Thanks to the ClickStop ball clamp in each telescopic handle, 24 different visible blade lengths can be set between 42 and 114 mm in 3 mm increments.



Wiha SYSTEM 6.

- Versatile reversible blade system in industrial quality
- Expandable individual tool system
- Ergonomic handles for almost every application
- Blades of high-quality, tough yet elastic chrome-vanadium-molybdenum steel, through hardened
- Titanium silver surface for high corrosion protection

Wiha SYSTEM 6.

The space-saving all-rounder.

SYSTEM 6 Starter sets.



281 T6 SYSTEM 6 reversible blades set, 6 pcs.

Slotted/ Phillips/ hex/ ball end hex.

Blade: High quality CVM steel, through hardened.
Titanium silver, laser tip sizes.

Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle.
ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Versatile and space-saving, it fits in every toolbox.

Extra: Robust roll-up pouches allows space-saving storage of tools.

Order-No.	Series	
27715	281 T6	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
① ①	284	3.5 - 4.5 4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
⦿ ⦿	284	5 - 5

SYSTEM 6 sets.



281 T11 SYSTEM 6 reversible blades set, 11 pcs.

Slotted/ Phillips/ Pozidriv/ TORX®/ hex/ ball end hex.

Blade: High quality CVM steel, through hardened.
Titanium silver, laser tip sizes.

Blade length is adjustable from 42 - 114 mm.

Handle: SYSTEM 6 SoftFinish®-telescopic handle.
ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Extra: Robust roll-up pouches allows space-saving storage of tools.

Order-No.	Series	
03591	281 T11	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
① ①	284	4.0 - 6.0 5.5 - 6.5
⊕ ⊕	284	PH1 - PH2
⦿ ⦿	284	PZ1 - PZ2
⦿ ⦿	284	T10 - T15 T20 - T25 T30 - T40
⦿ ⦿	284	4 - 4 5 - 5 6 - 6



281 T6 01 SYSTEM 6 reversible blades set, 6 pcs.

Blade: High quality CVM steel, through hardened.
Titanium silver, laser tip sizes.

Blade length is adjustable from 42 - 114 mm.


Handle: SYSTEM 6 SoftFinish®-telescopic handle.
ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Versatile and space-saving, it fits in every toolbox.

Extra: Robust roll-up pouches allows space-saving storage of tools.

Order-No.	Series	
32298	281 T6 01	1
	284	SYSTEM 6 SoftFinish®-telescopic handle
① ①	284	4.0 - 6.0
⊕ ⊕	284	PH1 - PH2
⦿ ⦿	284	PZ1 - PZ2
⦿ ⦿	284	T10 - T15 T20 - T25

Wiha Info



Suitable for every use:
the blades can be quickly combined,
extended and interchanged.