



Slotted, Phillips 7-pcs.

260P

| | |
|-----------|---|
| Order-No. | |
| 42991 | 1 |
| | 1,5 x 40 / 2,0 x 40 / 2,5 x 50 / 3,0 x 50 |
| | PH00 x 40 / PH0 x 50 / PH1 x 60 |

Slotted, Phillips, 6 pcs. with holder

260P

| | |
|-----------|---|
| Order-No. | |
| 42990 | 1 |
| | 1,5 x 40 / 2,0 x 40 / 2,5 x 50 / 3,0 x 50 |
| | PH00 x 40 / PH0 x 50 |

TORX® MagicSpring®, 6 pcs. with holder

267PR

| | |
|-----------|---|
| Order-No. | |
| 42998 | 1 |
| | T6 x 40 / T7 x 40 / T8 x 40 / T9 x 50 / T10 x 50 / T15 x 60 |

TORX®, 6 pcs. with holder

267P

| | |
|-----------|--|
| Order-No. | |
| 42996 | 1 |
| | T7 x 40 / T8 x 40 / T9 x 50 / T10 x 50 / T15 x 60 / T20 x 60 |

TORX®, 6 pcs. with holder

267P

| | |
|-----------|---|
| Order-No. | |
| 42997 | 1 |
| | T4 x 40 / T5 x 40 / T6 x 40 / T7 x 40 / T8 x 40 / T9 x 50 |

Hexagonal ball end, 6 pcs. with holder

264P

| | |
|-----------|--|
| Order-No. | |
| 42993 | 1 |
| | 0,9 (0,035") x 40 |
| | 1,3 (0,05") x 40 / 1,5 x 50 / 2,0 x 50 / 2,5 x 60 / 3,0 x 60 |

Hex, 6 pcs. with holder

263P

| | |
|-----------|--|
| Order-No. | |
| 42992 | 1 |
| | 0,9 (0,035") x 40 / 1,3 (0,05") x 40 / 1,5 x 50 / 2,0 (5/64") x 50 / 2,5 x 60 / 3,0 x 60 |

Hexagon nut driver 6-pcs. with holder

265P

| | |
|-----------|---|
| Order-No. | |
| 42994 | 1 |
| | 2,5 x 60 / 3,0 x 60 / 3,5 x 60 / 4,0 x 60 / 5 x 60 / 5,5 x 60 |

**INFOBOX:
PicoFinish**



Wiha PicoFinish precision screwdriver

- The comfortable precision screwdriver for fine and delicate fastenings.
- The smooth-running turn-cap enables fast turning.
- Imprint with the screw symbol and sizes eases recognition.