Wiha SYSTEM 4.

Ideal for precision work.



Colour-coded ChromTop® tips for maximum clarity.

Due to its versatility and quality the Wiha **SYSTEM 4** is a reversible blade system that convinces every user.

Either for slotted, Phillips, TORX[®] or hex screws, the wide product range provides the right model for every application.

All reversible blades are made of high-quality CVM-steel, through hardened and chrome-plated, which provides an extra long service-life. The Wiha ChromTop® tips guarantee a perfect fit every time. Just choose from the SYSTEM 4 products for the relevant tool. Following handles are offered. • The ergonomic **SoftFinish**®

telescopic handle. • The dissipative SoftFinish® telescopic ESD handle.

Each with adjustable blade lengths from 18 – 90 mm.


We offer SYSTEM 4 sets in compact roll-up pouches, rigid metal and easy access plastic boxes.



Convincing variety and quality. SYSTEM 4 – a real multi-tasker.



- Versatile reversible precision blade system
- Sets in compact roll-up pouches, rigid metalor easy access plastic-boxes
- Ergonomic handles for almost every application
- Colour-coded blades made of high-quality, tough chromevanadium-molybdenum steel, through hardened, chrome-plated
- Wiha ChromTop[®] tips ensure a perfect fit every time



The ClickStop ball clamp in each telescopic handle allows 24 different visible blade lengths between 18 and 90 mm in 3 mm increments.



Wiha SYSTEM 4.

Ideal for precision work.

SYSTEM 4 reversible blades.

SYSTEM 4 reversible blades.

SYSTEM 4 nut driver.

0

1.8

through hardened, chrome-plated.

For hex nuts.

For hex nuts.

Ο

1.5



269

Blade:

SYSTEM 4 TORX® reversible blade. High quality chrome-vanadium-molybdenum steel,

through hardened, chrome-plated. Colour-coded Wiha ChromTop® tips.

Order-No.	۲	۲	$\overline{\longrightarrow}$	- 1	—
26122	T1	T2	120	4.0	5
26123	Т3	T4	120	4.0	5
26124	T5	T6	120	4.0	5
00597	T6	T8	120	4.0	5
00598	T7	Т9	120	4.0	5
00599	T10	T15	120	4.0	5
00600	T15	T20	120	4.0	5









269

Blade:

Application:

Order-No.

00588

269 SYSTEM 4 combined ball end hex - hex reversible blade. High quality chrome-vanadium-molybdenum steel, through hardened, Blade: chrome-plated. Colour-coded Wiha ChromTop® tips. The ball end enables the user to work at angles up to 25° . Extra:

Order-No.	۲	۲	$\overline{\longleftrightarrow}$	• 1	-
00582	1.3	1.3	120	4.0	5
00583	1.5	1.5	120	4.0	5
00584	2	2	120	4.0	5
00585	2.5	2.5	120	4.0	5
00586	3	3	120	4.0	5
00587	4	4	120	4.0	5

5 00589 2 2.5 125 4.0 00590 3 125 4.0 5 -5 00591 3.2 125 4.0 -3.5 5 00592 125 4.0 -5 00593 4 125 4.0 _ 00594 4.5 125 4.0 5 -5 00595 5 125 4.0 -00596 5.5 5 125 4.0

125


High quality chrome-vanadium-molybdenum steel,

4.0

5

U759 00 SYSTEM 4 bit holder. Suitable for C 4 (4 mm) bits. Blade: Chrome-vanadium steel, through hardened, electro-plated.

Order-No.	0			⊉⊐	—
09195	4.0	135	4.0	9	1



120 **wiha** 🕑