


## 480-600V breaker lockout

Perfect for locking out oversized and irregularly shaped switches.

- Self adhesive backed rails are permanently installed onto an electrical panel simply clean panel surface and adhere – no drilling required!
- Red blocking bar indicates locked "off
- Green blocking bar indicates locked "on
- 1 padlock can be applied



Breaker Blocker Components - 090893 Blocking Bar Holder 051265

Order Reference	Description	Colour	Length (mm)	Height (mm)	Max. Shackle Diameter (mm)	Min. Shackle Clearance (mm)	Max. Switch Width (mm)	Quantity
090891**	480-600V Breaker Lockout Kit*		-	20.32	6.50	20.00	150.00	1
051264	Breaker Blocker Components - 101 mm Yellow Mounting Rails	<ul> <li>Yellow</li> </ul>	101.60	20.32	-	-	-	2
090893	Breaker Blocker Components - 190 mm Green Blocking Bar	<ul> <li>Green</li> </ul>	190.00	-	-	-	-	5
090892	Breaker Blocker Components - 190 mm Red Blocking Bar	Red	190.00	-	-	-	-	5
051265	Breaker Blocker Components - Blocking Bar Holder	<ul> <li>Yellow</li> </ul>	150.00	20.32	-	-	-	5

\*Kit includes: 2 Yellow mounting rails, 1 red blocking bar, 1 green blocking bar and 3 alcohol wipes. \*\*This product meets the ATEX Equipment Directive.



## Universal multi-pole breaker lockout

Universal multi-pole lockout works with most two or three pole breakers utilising a tie-bar.

- Compatible with GE, ITE, Sylvania, Challenger, Bryan, Westinghouse, General Switch Co. ...
- Use thumbscrews to clamp lockout securely over tie-bar, then insert lock to prevent clamp from being loosened
- Made of durable Polypropylene & Moulded Glass-filled Nylon
- 1 padlock can be applied

Quick and easy to apply
1 padlock can be applied.

Description

Order


805814

Reference

Order Reference	Description	Max. Shackle Diameter (mm)	Min. Shackle Clearance (mm)	Packaging
066320	Universal Multi-Pole Breaker Lockout	7.00	20.00	6
066321*	Universal Multi-Pole Breaker Lockout	7.00	20.00	1

\*This product meets the ATEX Equipment Directive.







bradyeurope.com/tds

## Single pole circuit breaker lockout

Economy Multi-Pole Breaker Lockout

Economy multi-pole breaker lockout Economical solution designed to fit multi-pole breakers!

Quick and easy – just snap in place and apply a lock!

- Designed for breakers that have holes in the switch tongue
- Dual cavities accommodate different size switch tongues

## 1 padlock can be applied

Order Max. Shackle Min. Shackle Width Depth Diameter (mm) Clearance (mm) Quantity Reference Description (mm) (mm) 065387\* Single Pole Circuit Breaker Lockout 7.00 20.00 54.50 8.40 1 065688 Single Pole Circuit Breaker Lockout 7.00 20.00 54.50 8.40 6

Max. Shackle

7 00

Diameter (mm)

Min. Shackle

20.00

Clearance (mm)

Quantity

1

\*This product meets the ATEX Equipment Directive.