




























3M™ EPX™ Applicators and Nozzles

		Replacement Plunger Orders							Nozzle Length (Inches)		Static Mixing Nozzle Options	
		43 mL (2:3)	45 mL (10:1)	48.5 mL (1:1)	50 mL (2:1)	200 mL (2:1 & 1:1)	400 mL (2:1 & 1:1)	3.6	6.2			
3M™ Scotch-Weld™ EPX™ Plus II Applicator*  Stock #: 7100148764 UPC: 00-063806-01001-7 *Includes 1:1, 2:1 and 10:1 plunger.	1:1/2:1 Shared Plunger Stock #: 7010415317 UPC: 00-063806-01000-0		✓	✓				3.6	6.2	3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Green, 48.5mL/50mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1	
			✓	✓						3M™ EPX™ Mixing Nozzle Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5	
	2:1 Plunger Used only for 2216 epoxy Stock #: 7010309947 UPC: 0-00-76308-86390-6	✓							3.3	5.8	3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 43mL Stock #: 7000000952 UPC: 0-00-21200-50008-4	 Bulk: 7000121587 Bulk: 0-00-21200-50009-1
	10:1 Plunger Stock #: 7010329933 UPC: 0-00-76308-86391-3		✓						3.6		3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Orange, 45mL Stock #: 7100007806 UPC: 0-00-51115-81449-0	 Bulk: 7100034272 Bulk: 0-00-51115-81467-9
3M™ EPX™ Metal Applicator  Stock #: 7000000954 UPC: 0-00-21200-21789-0	2:1 Plunger Stock #: 7000000956 UPC: 0-00-21200-82314-5	✓						3.3	5.8	3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 43mL Stock #: 7000000952 UPC: 0-00-21200-50008-4	 Bulk: 7000121587 Bulk: 0-00-21200-50009-1	
										3M™ Scotch-Weld™ EPX™ Mixing Nozzle Helical White, 43mL Stock #: 7100034271 UPC: 0-00-51115-81449-5	 Bulk: 7100034272 Bulk: 0-00-51115-81467-9	
				✓					3.6		3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Green, 43mL/48.5mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1
					✓				6.2		3M™ EPX™ Mixing Nozzle Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5
3M™ EPX™ Pneumatic Applicator 48.5/50 mL  Stock #: 7100148769 UPC: 00-063806-01006-2	N/A		✓	✓				3.6	6.2	3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Green, 43mL/48.5mL Stock #: 7100104991 UPC: 0-00-76308-86434-7	 Bulk: 7100148765 Bulk: 0-00-63806-01003-1	
				✓	✓					3M™ EPX™ Mixing Nozzle Helical White, 48.5mL/50mL Stock #: 7100148766 UPC: 00-063806-01004-8	 Bulk: 7100148756 Bulk: 00-063806-01005-5	
3M™ Scotch-Weld™ EPX™ Manual Applicator 200 mL  Stock #: 7000046632 UPC: 0-00-21200-87977-7	1:1/2:1 Shared Plunger Stock #: 7000121583 UPC: 0-00-21200-87981-4					✓	✓	5.0	7.5	3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 200mL and 400mL Stock #: 7000028616 UPC: 0-00-21200-97331-4	 Bulk: 7000121587 Bulk: 0-00-21200-50009-1	
										3M™ Scotch-Weld™ EPX™ Mixing Nozzle Helical White, 200mL and 400mL Stock #: 7000046633 UPC: 0-00-21200-87982-1	 Bulk: 7100034272 Bulk: 0-00-51115-81467-9	

3M™ EPX™ Applicators and Nozzles

	Replacement Plunger Orders	37 mL (2:1) & 43 mL (2:3)					45 mL (10:1)		50 mL (1:1)		200 mL (2:1 & 1:1)		400 mL (2:1 & 1:1)		Nozzle Length (Inches)	Static Mixing Nozzle Options
3M™ EPX™ 200, 400 mL Manual Applicator  Stock #: 7000046634 UPC: 0-00-51111-98073-6	N/A															3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 200mL and 400mL Stock #: 7000028616 UPC: 0-00-21200-97331-4 
3M™ EPX™ 490 mL Manual Applicator  Stock #: 7100015958 UPC: 0-00-51115-71115-2	N/A															3M™ Scotch-Weld™ EPX™ Mixing Nozzle Helical Orange, 490mL Stock #: 7100015959 UPC: 0-00-51115-69042-6 
3M™ Scotch-Weld™ EPX™ Pneumatic Applicator 200 mL  Stock #: 7000121584 UPC: 0-00-21200-87978-4	N/A															3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 200mL and 400mL Stock #: 7000028616 UPC: 0-00-21200-97331-4 
3M™ EPX™ 400 mL Pneumatic Applicator  Stock #: 7000148285 UPC: 0-00-21200-87979-1	N/A															3M™ Scotch-Weld™ EPX™ Mixing Nozzle Square Gold, 200mL and 400mL Stock #: 7000028616 UPC: 0-00-21200-97331-4 
3M™ EPX™ 490 mL Pneumatic Applicator  Stock #: 7100011053 UPC: 0-00-51115-69041-9	N/A															3M™ Scotch-Weld™ EPX™ Mixing Nozzle Helical Orange, 490 mL Stock #: 7100015959 UPC: 0-00-51115-69042-6 
Standard Caulk Gun	N/A															3M™ Concrete Repair 8.4 oz Cartridge Nozzles Stock #: 7000046642 UPC: 0-00-48011-53382-7 

For low volume applications and take-it-to-the-job convenience, the 3M™ EPX™ Plus II and EPX™ metal manual applicators comfortably dispense any of the 3M™ Scotch-Weld™ Duo-Pak Structural Adhesives. For higher volume applications, select the 200mL manual dispenser, or the 200mL or 400mL pneumatic dispenser. For concrete repair, there are both manual or pneumatic options.

3M™ Scotch-Weld™ One-Part Heat Cured Epoxies require a unique manual or pneumatic dispenser, such as Semco® 250, 350, 850, 950, or equivalent.