

KNIPEX-MultiCrimp

Crimping Pliers with quick changer magazine

Article-No.	EAN 4003773-			AWG	↔ mm	⚖ g		
97 33 01	066927	non-insulated open plug-type connectors; roll crimp		0.5-6.0 mm ²		20-10	250	755
		insulated terminals + plug connectors		0.5-6.0 mm ²		20-10		
		end sleeves (ferrules)		0.25-6.0 mm ²		23-10		
97 33 02	066934	non-insulated open plug-type connectors; roll crimp		0.5-6.0 mm ²		20-10	250	855
		insulated terminals + plug connectors		0.5-6.0 mm ²		20-10		
		end sleeves (ferrules)		0.25-6.0 mm ²		23-10		
		non-insulated terminals + plug connectors		0.5-10.0 mm ²		20-7		
		non-insulated butt connectors		1.5-10.0 mm ²		15-7		

All rights reserved for technical alterations.
Images partly of pilot lot; meet nearly the final product.



Your distributor



KNIPEX-Werk
C. Gustav Putsch KG
Oberkamper Strasse 13
42349 Wuppertal (Germany)
Tel.: +49 (0) 202 - 47 94-0
Fax: +49 (0) 202 - 47 74 94
info@knipex.de
www.knipex.de

L1100 019803/02/04/08/05/000/08B Printed in Germany

KNIPEX-MultiCrimp

Crimping Pliers with quick changer magazine



The all-rounder
for 5 interchangeable
crimping dies



- ▶ **One** tool for the most common crimping applications
- ▶ quick and easy exchange of the crimping dies without any additional tool
- ▶ lightweight high-quality crimping pliers for the mobile professional user

KNIPEX Quality – Made in Germany

KNIPEX-MultiCrimp

Crimping Pliers with quick changer magazine




Round magazine with belt clip: interchangeable dies are always ready to hand



The electrician travelling in mobile services needs at least 3 different crimping pliers to be prepared for crimping of the most common standard connectors. The new MultiCrimp system now offers the compact solution for the professional user: a set of optionally 3 or 5 interchangeable crimping dies in a quick changer magazine for the most common applications on the spot.



Change of crimping dies without any additional tool



97 33 01 crimping pliers with round magazine and 3 interchangeable dies for non-insulated open plug-type connectors; insulated terminals + plug connectors; end sleeves (ferrules)



97 33 02 crimping pliers with round magazine and 5 interchangeable dies for non-insulated open plug-type connectors; insulated terminals + plug connectors; end sleeves (ferrules); non-insulated terminals + plug connectors; non-insulated butt connectors



Secure attachment of the dies in the pliers by reliable locking system



Catch for exchange of crimping dies



Crimping dies are marked with a pictogram: visible in the magazine and the pliers



- ▶ set composed of pliers and quick changer magazine for current crimping applications
- ▶ very easy and quick change of crimping dies without any additional tool
- ▶ secure and dirt-proof storage of the interchangeable crimping dies in a round magazine
- ▶ repetitive, high crimping quality due to precision profiles and integral lock with very fine adjustment (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ ergonomically shaped two-colour dual component handles for one and two-hand operation

