#### LP-17R Red Long Tip Probe



Replacement test probe with 65mm insulated tip for APPA 17 pen-type multimeter. Also designed to protect against accidental contacts, 1000V, 10A.

#### ATL-4 Test Lead Set



Replacement test lead for APPA A7D. A7A, A5, and A9. Hard tips Comfortgrip, safety-shrouded, right-angle plug, 48 (1.2m),1000V, 10A, CAT. IV 600V/ CAT III 1000V

Extra strong 4mm banana tips for long life for APPA A7D, A7A, A5, and A9. Hard

tips Comfort-grip, safety-shrouded,

right-angle plug, 48 (1.2m), 1000V,

# **APPA** Accessories

#### AH-300 APPA 300 Series Holster (Yellow)



AH-109 APPA 107/109 Holster (Grey)

Easy-to Clean, nail hook holster absorbs shocks and protects meter. Lead and probe storage on back, lean or stand in best viewing position. AH-300 for 300 series DMM

#### ATL-1 Test Lead Set

ATL-2 Test Lead Set



Hard alloy tips for long life. Comfortgrip, safety-shrouded, INSULATED right-angle plug, 48"(1.2m), UL listed lead wire, 1000V, 10A, CAT III.

#### ATL-5 Test Lead Set



#### ATL-6 Test Lead Set



Replacement test lead for APPA new 60 series multimeters. Hard tips Comfortgrip, safety shrouded, right-angle plug, 48 (1.2m), 1000V, 10A, CAT. III 600V/ CAT. II 1000V.

Easy-to Clean, nail hook holster absorbs shocks and protects meter. Lead and probe storage on back, lean or stand in best viewing position. AH-109 for 107/109 DMM

#### AH-50A/50B APPA 50 Series Holster (Yellow)



Nail hook holster for meters, absorbs shocks and protects the meter from rough handing. built-in stand.AH-50A for APPA51/53. AH-50B for APPA 52/55.

#### AH-60A/60B APPA 60 Series Holster (Grey)



Easy-to-Clean, nail hook holster absorbs shocks and protects meter, built-in stand and holder. Lean or stand for best viewing position. Lead/probe storage on sid. AH-60 for APPA63/65. AH60B for APPA67.69

AH-60B AH60-A



Extra strong 4mm banana tips for long life. Comfort-grip, safetyshrouded, INSULATED right-angle

plug, 48"(1.2m),

CAT III.

UL listed lead wire,1000V, 10A,



10A, CAT. IV

600V/CAT. III 1000V.

#### ATL-3 Test Lead Set



Replacement test lead for APPA30/60/90/100/200 series, Hard tips Comfort-grip, safety-shrouded, right-angle plug, 48"(1.2m), 1000V, 10A, CAT III.

#### Specifications subject to change without notice.

#### Distrubuted by:

#### APPA TECHNOLOGY CORPORATION

9F, 119-1 Pao-Zong Rd., Shintien, Taipei, 231, TAIWAN Tel: +886-2-29178820 Fax: +886-2-29170848 E-mail: info@appatech.com · http://www.appatech.com ISO 9001 CERTIFIED

Copyright © 2005 APPA Tech., Corp. All rights reserved

#### AH-90/100 APPA90/100 Series Holster (Yellow, Grey)



Easy-to Clean, nail hook holster absorbs shocks and protects meter. Lead and probe storage on back, lean or stand in best viewing position. AH-90 for 90 series DMM AH-100 for 100 series DMM

#### AH-70 APPA 70 series holsters (Light Grey)



Easy to Clean, nail hook holster absorbs shocks and protects meter. Lead and probe storage on back, lean or stand in best viewing position.

#### AH-80 APPA 80 series holsters (Light Grey)



Easy to Clean, holster absorbs shocks and protects meter. Lead and probestorage on back.

#### AH-99II APPA 90II series holsters (Light Grey)



Easy to Clean, nail hook holster absorbs shocks and protects meter. Lead and probe storage on back, lean or stand in best viewing position.



#### AC-31/32 Carrying Case



Soft sided.zippered. Nylon fabric carrying case for APPA 31/32 current transducer or APPA 17+15, Inside pocktes are designed to carry test leads and manual, built-in belt loop.

#### AC-17 Carrying Pouch



#### Vinyl carrying case.Designed to carry a meter.test leads set. For APPA 17.

#### AC-C2 Carrying Case



Tough, double wall woven fabric, one way zipper carrying case for APPA A 39T, A11/A11R, A12 /A12R, and A18plus. Inside pockets are designed to carry test lead, and manual, built-in belt loop.

#### AC-35 Carrying Case



Soft sided, zippered, Vinyl carrying case for APPA 35N/30 clamp meter. Inside pockets are designed to carry test lead, and manual, built-in belt loop.

#### AC-M1 Carrying Case



Tough, double wall woven fabric, two way zipper carrying case for APPA 80, 90, 90II, 100 series, 76 and 25 multimeters. Inside pockets are designed to carry test lead, and manual. Convenient 5.3 (135mm) belt loop accommodates tool belts

#### AC-C3 Carrying Case



Tough, double wall woven fabric, one way zipper carrying case for APPA 35, 30, 31, 36, 33II, 36II, A10plus, A6, A8, A9, A7, A7D, A5, A2, and A3. Inside pockets are designed to carry test lead, and manual, built-in belt loop.

### AC-33 Carrying Case



AC-300 Carrying Case

Soft sided, zippered, Nylon fabric carrying case for APPA 33/37 clamp meter. Inside pockets are designed to carry test lead, and manual, built-in belt loop.

#### AC-M2 Carrying Case



Tough, double wall woven fabric, two way zipper carrying case for APPA 50, 60, 70 series multimeters. Inside pockets are designed to carry test lead, and manual. Convenient 5.3 (135mm) belt loop accommodates tool belts

#### AC-10S Superior Carrying Case



Tough, double wall woven fabric, two way zipper carrying case for APPA 10 series meters. Three seperate holders to carry an APPA 17 and two transducers, indise pocket is designed to carry test leads, bead probe and manual.

This deluxe carrying case is also versatile to carry APPA 60 series multimeter, APPA 50 series thermometer ..... etc.

#### TL-10 Safety Test Lead Set



Replacement test lead for APPA 17. Include one TC-10B, SP-17R, LP-17R and ATL-3B.

## Tough, double wall woven fabric, two

way zipper carrying case for APPA 300 series multimeter. Inside pockets are designed to carry test lead, temp. adaptor, bead probe, RS 232 cable and manual.

## AC-C1 Carrying Case



Tough, double wall woven fabric, two way zipper carrying case for APPA 39AC, 39AR, 39MR, A15/A15R, A16/A16R, and A16H/A16HR. Inside pockets are designed to carry test lead, and manual, built-in belt loop.

#### TL-10S Test Lead Interface



Connect 4mm banana plugs to standard input jacks of a multimeter. Coiled cable for convinent use, extend up to

60 (1.5m), 1000V, 10A rating.

#### TL-70 Clip Test Lead Set



For APPA 76 component tester or other meters, spring-loaded clips with serrated teeth, safety-shrouded, rightangle input, 10"(25cm), 250V, 10A. one red, one black.

#### TC-10 Alligator Clip Set



Slip-on insulated alligator clips for use with test leads probe 1000V, 10A rating. one red, one black.

#### SP-17R Red Standard Probe



Replacement test probe for APPA 17 pen-type multimeter. Also designed to protect against accidental contacts, 1000V, 10A.