

1. SHIELDING BAGS

Top quality packaging for protection and shipping of components, semiconductors and sub-assemblies sensitive to electrostatic discharge.



- Available with or without zip,
- 2 Thicknesses
- Other dimensions available on request

Technical Data

- Surface resistance: $R_{pp} < 1 \times 10^{11} \Omega$
- ESD-STM 11.11@12% HR
- Decay time: $< 0.05 \text{ sec. FTMS 101 Mtd 406}$
- Physical protection, transmitted energy: $< 50 \text{ nJ}$
- Material: shielding film

IEC
61340
Compliant
RoHS
Directive
MIL-PRF-
81705D

Shielding bags- Thickness μm (+/- 10%)

Dimensions (mm)	Dimensions (inches)	Thickness 50	Thickness 76	Thickness 76
		Without zip	Without zip	With zip
76 x 80	3 x 3	-	-	20-872-0303
76 x 102	3 x 4	20-771-0304	20-871-0304	-
76 x 127	3 x 5	20-771-0305	20-871-0305	20-872-0305
102 x 152	4 x 6	20-771-0406	20-871-0406	20-872-0406
102 x 660	4 x 26	-	20-871-0426	-
102 x 762	4 x 30	-	20-871-0430	-
127 x 203	5 x 8	20-771-0508	20-871-0508	20-872-0508
152 x 203	6 x 8	20-771-0608	20-871-0608	20-872-0608
152 x 254	6 x 10	20-771-0610	20-871-0610	20-872-0610
152 x 660	6 x 26	-	20-871-0626	-
203 x 254	8 x 10	20-771-0810	20-871-0810	20-872-0810
203 x 305	8 x 12	-	20-871-0812	20-872-0812
203 x 406	8 x 16	-	20-871-0816	-
254 x 305	10 x 12	-	20-871-1012	20-872-1012
254 x 356	10 x 14	-	20-871-1014	-
254 x 610	10 x 24	-	20-871-1024	-
254 x 660	10 x 26	-	20-871-1026	-
279 x 381	11 x 15	-	20-871-1115	-
305 x 305	12 x 12	-	-	20-872-1212
305 x 406	12 x 16	-	20-871-1216	20-872-1216
305 x 457	12 x 18	-	20-871-1218	20-872-1218
356 x 356	14 x 14	-	20-871-1414	-
356 x 457	14 x 18	-	20-871-1418	20-872-1418
381 x 457	15 x 18	-	20-871-1518	-
406 x 610	16 x 24	-	20-871-1624	-
457 x 457	18 x 18	-	20-871-1818	20-872-1818
457 x 610	18 x 24	-	20-871-1824	-
508 x 660	20 x 26	-	20-871-2026	-