





## Soldering Tips for WP 60

Model	Description	Width in mm	Diameter	PU	Order No.
<b>60-01-05</b> 	Needle shape	-	0,5 mm	1	T005 16 134 99
<b>60-01-01</b> 	Needle shape	-	1.0 mm	1	T005 16 443 99
<b>60-01-02</b> 	Chisel shape	2.4	-	1	T005 16 444 99
<b>60-01-04</b> 	Chisel shape	5.0	-	1	T005 16 446 99
<b>60-01-52</b> 	Hot air nozzle	-	4,7 mm	1	T005 16 447 99
<b>60-07U</b> 	Ejector Unit	-	-	1	T005 16 448 99
<b>60-02</b> 	Protective Cap	-	-	1	T005 16 450 99
<b>60-01-03</b> 	Round	-	2.0	1	T005 16 445 99

## Soldering Tips for Pyropen Jr.

Model	Description	Width in mm	Diameter	PU	Order No.
<b>71-01-01</b> 	Needle shape	1.0	-	1	T005 16 165 99
<b>71-01-02</b> 	Chisel shape	2.0	-	1	T005 16 166 99
<b>71-01-04</b> 	Chisel shape	5.0	-	1	T005 16 161 99
<b>71-01-03</b> 	Round	2.0	-	1	T005 16 167 99
<b>71-01-50</b>	Hot air nozzle	1.5	-	1	T005 16 168 99
<b>71-01-52</b>	Hot air nozzle	4.7	-	1	T005 16 169 99

Soldering Stations

Soldering iron and safety rest

Soldering tips and nozzles

Preheating plates

Soldering baths

Circuit board holder

Solder feeder















Hot air heating gun

Temperature measuring






Accessories



# Soldering Tips for Pyropen and Pyropen Piezo

Model	Description	Width in mm	Diameter	PU	Order No.
<b>70-01-01</b> 	Needle shape	1.0		1	T005 16 120 99
<b>70-01-05</b> 	Needle shape, extra slim	0.5		1	T005 16 124 99
<b>70-01-10</b> 	Needle shape, bent 30°	1.0		1	T005 16 129 99
<b>70-01-02</b> 	Chisel shape	3.0		1	T005 16 121 99
<b>70-01-13</b> 	Chisel shape	5.0		1	T005 16 132 99
<b>70-01-11</b> 	Chisel shape	7.0		1	T005 16 130 99
<b>70-01-03</b> 	Round	2.0		1	T005 16 122 99
<b>70-01-04</b> 	Round	3.0		1	T005 16 123 99
<b>70-01-06</b> 	Round	2.0		1	T005 16 125 99
<b>70-01-08</b> 	Round	2.0		1	T005 16 127 99
<b>70-01-50</b> 	Hot air nozzle	1.7		1	T005 16 140 99
<b>70-01-51</b> 	Hot air nozzle	3.3		1	T005 16 141 99
<b>70-01-52</b> 	Hot air nozzle	-	4.9	1	T005 16 142 99
<b>70-01-53</b> 	Hot air nozzle	-	7.0	1	T005 16 143 99



Model	Description	Width in mm	Diameter	PU	Order No.
<b>70-07TU</b> 	Flame nozzle	-	-	1	T005 16 151 99
<b>70-07SU</b> 	Soldering nozzle	-	-	1	T005 16 150 99
<b>70-01-55</b> 	Reflector attachment for heat shrinking work	18.0	6.0	1	T005 16 159 99
<b>70-01-54</b> 	Reflector attachment for heat shrinking work	22.0	8.0	1	T005 16 158 99
<b>70-03-14</b> 	PP-Barrel and nut	-	-	1	T005 16 153 99

Soldering Stations

Soldering iron and safety rest

Soldering tips and nozzles

Preheating plates

Soldering baths

Circuit board holder

Solder feeder

Hot air heating gun

Temperature measuring

Accessories