

# GETAC ZX10 FULLY RUGGED TABLET ACCESSORY SPEC BROCHURE



Getac USA  
15495 Sand Canyon Ave. Suite 350 Irvine, CA 92618 Tel : 949-681-2900  
GetacSales\_US@getac.com | [www.getac.com/us/](http://www.getac.com/us/)

**THE FULLY-RUGGED ANDROID  
FOR YOUR WORKDAY**

# CARRY BAG

## FEATURES & BENEFITS

Constructed of durable Nylon / air mesh fabric, and featuring an adjustable padded shoulder strap, this compact carry bag provides sturdy protection for your F110 tablet while giving maximum comfort. The functional pockets inside offer the optimal solution to transport the tablet and needed accessories together in one case, delivering extra convenience and go-anywhere productivity to mobile professionals.

### Product Information

Dimensions : L 340 x W 260 x D 65 mm

Weight : 760g

Main Material : Nylon, air mesh fabric

### SKU ID

GMBCX2



# STANDARD BATTERY 4990MAH

## FEATURES & BENEFITS

The hot-swappable battery can support full-shift computing with no downtime. It is a great solution for mobile professionals who require long battery life for all-day operation.

### Product Information

Battery Type : Lithium-ion Polymer

Voltage : 3.84V

Capacity : Typical 4990mAh ; Min. 4870mAh

Dimensions : L 119.5 x W 60.6 x H 8.95mm

Weight : 98g

### SKU ID

GBM1X1



# HIGH-CAPACITY BATTERY 9980MAH

## FEATURES & BENEFITS

The high-capacity battery pack extends the system run time up to two times compared to the standard battery pack, providing a great solution for mobile professionals who require extra battery life for operation longer than one day

### Product Information

Battery Type : Lithium-ion Polymer

Voltage : 3.84V

Capacity : Typical 9980mAh ; Min. 9470mAh

Dimensions : L 119.5 x W 60.6 x H 16.6mm

Weight : 170g

### SKU ID

GBM2X2



# EXTERNAL DUAL BAY MAIN BATTERY CHARGER

## FEATURES & BENEFITS

This external dual-bay main battery charger is designed to charge up to two batteries at the same time. It provides you the benefit of charging and storing the 2 main batteries together when there are limited space and power socket.

### Product Information

AC Input : 100V~240V

DC Output : 13.05V, 2.4A Max.

Number of charge bay : 2 Bay

Dimensions : L 160 x W 180 x H 72.5mm

Weight : 1.2kg

### SKU ID

GCMCEM (EU Power Cord)

GCMCUM (US Power Cord)

GCMCKM (UK Power Cord)

GCMCAM (AU Power Cord)

GCMCCM (CHN Power Cord)

GCMCTM (TW Power Cord)



# MULTI-BAY BATTERY CHARGER EIGHT BAY

## FEATURES & BENEFITS

The 8-bay multi-battery charger is designed to charge multiple battery packs simultaneously and provide users an efficient charging solution.

### Product Information

AC Input : 100V~240V AC, 4.2A 50~60Hz

DC Output : 19.5V, 16.9A

\* w / 330W AC Adapter Number of charge bays : 8 bays

Dimensions : L 465 x W 245 x H 95.3~111.3mm

Weight : 4.7 kg, not including battery packs

### SKU ID

GCECEP (EU Power Cord)

GCECUP (US Power Cord)

GCECKP (UK Power Cord)

GCECAP (AU Power Cord)

GCECCP (CHN Power Cord)



# 65W AC ADAPTER WITH POWER CORD

## FEATURES & BENEFITS

This adapter is designed to power the device and charge its internal battery from an AC power source. A country-specific power cord is included with the adapter to fit the local power outlet in your designated country.

### Product Information

Input : 100V-240V, 50~60Hz, 1.5A

Output : 19V, 3.42A, 65W

Dimensions : L 108.3 x W 46.3 x H 30mm

Weight : 250g

Input cable length : 1830mm

Output cable length. : 1500mm

### SKU ID

GAA6E5 (EU Power Cord)

GAA6U5 (US Power Cord)

GAA6K5 (UK Power Cord)

GAA6A5 (AU Power Cord)

GAA6C5 (CHN Power Cord)

GAA6T5 (TW Power Cord)



# 100W TYPE-C AC ADAPTER

## FEATURES & BENEFITS

The 100W Type-C AC adapter as an additional charging solution to charge Getac rugged tablets and laptops with inherent USB type-C ports as well as the power delivery functionality. The Type-C adapter features a reversible connector type that reduces connector damages due to misuse.

### Product Information

Input : 100V-240V  
Output : 20V, 5A, 100W  
Dimensions : L 140 x W 65 x H 25mm  
Weight : 326g Input cable  
length : 1830mm  
Output cable length : 1500mm

### SKU ID

GAT1E1 (EU Power Cord)  
GAT1U1 (US Power Cord)  
GAT1K1 (UK Power Cord)  
GAT1A1 (AU Power Cord)  
GAT1C1 (CHN Power Cord)  
GAT1T1 (TW Power Cord)





# 120W DC-DC VEHICLE ADAPTER

## FEATURES & BENEFITS

The 120W vehicle adapter comes with a choice of two types of connections: a bare wire with individual wire ends already stripped, and a cigarette lighter plug for easy connection to the cigarette lighter socket in the vehicle interior, providing a convenient way to charge and power your tablet while you are on the road.

### Product Information

Input Voltage : 11VDC~ 32VDC

Output Voltage : 19VDC

Output current : 6.32A Max.

Case Dimensions : L 131.5 x W 65.6 x H 30mm

Weight : 362g

Input cable length : 1900mm

Output cable length : 1000mm

### SKU ID

GAD2X4 (Cigarette Lighter Plug Version)

GAD2X8 (Bare Wire Version)



Cigarette Lighter Plug Version



Bare Wire Version

# MAGNETIC CAPACITIVE STYLUS & TETHER

## FEATURES & BENEFITS

This capacitive stylus is lightweight and easy to control, spring-loaded nib increasing the durability also allowing smooth and comfortable interaction with the touch screen without worrying about scratching the screen or leaving fingerprints on it. The magnetic stylus can be put into the pen holder easily. It also comes with a tether to keep it attached to the tablet.

### Product Information

Stylus Dimensions : 108.7 mm ; Ø9 mm

Tip size : 3.0 mm ; Ø2.8 mm

Color : Black

Tether Length : 304 mm

### SKU ID

GMPSXS \* MOQ : 5pcs



# SCREEN PROTECTION FILM (AG)

## FEATURES & BENEFITS

This screen protection film is cut precisely to fit the tablet and is easy to install and remove without leaving a sticky residue. With anti-glare coating, it not only protects the screen from the rigors of daily use but also helps to diffuse light on the screen and reduces glare, providing effortless readability for displayed information under common ambient lighting conditions.

### Product Information

Dimensions : L 224.6 x W 143.3 x D 0.24 mm  
Main Material: PET

### SKU ID

GMPFXS \* MOQ : 10pcs



# ROTATING HAND STRAP & KICKSTAND

## FEATURES & BENEFITS

The Rotating Hand Strap is designed to make using the tablet easier and more convenient to carry. The hand strap is adjustable to fit most hand sizes and can be rotated 360 degrees to find the ideal viewing angle while on-the-go. It also includes a built-in kickstand that allows for handsfree usage on flat surfaces, providing more on-the-job flexibility.

### Product Information

Dimensions : L 205 x W 116 x H 20mm  
Weight : 155g  
Main Material : PU

### SKU ID

GMHRXJ



# SHOULDER STRAP 2-POINT

## FEATURES & BENEFITS

This shoulder strap attaches via two holders at the back of the tablet and is adjustable to fit most body sizes for both cross-body and shoulder carry. With its durable, sturdy design, the strap not only provides a comfortable, grip-free carrying option of the tablet but also helps in avoiding accidental drops while on the move. The shoulder strap can also attach to the detachable keyboard (sold separately) via two D-rings on the built-in handle.

### Product Information

Dimensions : 38 x 1530mm  
Main Material : Polyester

### SKU ID

GMS2X8



# SHOULDER HARNESS 4-POINT

## FEATURES & BENEFITS

This shoulder harness has four snap hooks which attach to the corner rings on the tablet, and can be easily detached as well. The harness is worn in a backpack style, allowing the tablet to be carried hands-free in front of the user at a belt level for easy accessibility. It also delivers optimal support and a comfortable fit during movement, thanks to its wide soft padding and adjustable straps.

### Product Information

Dimensions : 1380 x 372mm  
Main Material : Polyester

### SKU ID

GMS4X4



# OFFICE DOCK WITH 65W AC ADAPTER

## FEATURES & BENEFITS

The Getac office dock brings out multiple I/O ports for connecting essential peripheral devices in the office environment. Through the integrated ethernet, RS232, or USB connections, users can quickly collect and synchronize field data with central offices for real-time reporting and analytics. The HDMI port also provides a convenient solution for sharing presentations or worksheets from a larger screen.

### Product Information

Dimensions : L 209.9 x W 159.7 x H 229.1mm

Weight : 790g

Docking Connector : POGO

\* w / 65W AC Adapter

I/O Interfaces : DC in Jack x 1, Audio Output x 1, Microphone x 1,  
USB 2.0 x 3, LAN x 1, HDMI x 1, RS232 Serial Port x 1, Kensington  
Lock x 1

### SKU ID

GDODE8 (EU Power Cord)

GDODU8 (US Power Cord)

GDODK8 (UK Power Cord)

GDODA8 (AU Power Cord)

GDODC8 (CHN Power Cord)

GDODT8 (TW Power Cord)

