






Cabinets - NOVASTAR Service Plus

Top covers

Order Information

					Flush top cover		Raised top cover	
					Flush	Lifting eye	Raised	Lifting eye
					 07011063	 07011071	 07011064	 07011072
					St. 1 mm, RAL 7021, incl. GND/earthing	for flush cover; M12, application and load to DIN 582	St. 1 mm, RAL 7021, incl. GND/earthing, height 31 mm, air gap 10 mm	for raised cover or fan top cover; M12, application and load to DIN 582
Cabinet dimensions					1 piece assembled	PU 4 pieces assembled	1 piece assembled	PU 4 pieces assembled
No.	Height U	Width mm	Depth mm					
1	6	357	553	500	25230-001		25230-010	
2	6	357	553	600	25230-002	27230-066	25230-011	27230-065
3	9	456	553	500	25230-001		25230-010	
4	9	456	553	600	25230-002	27230-066	25230-011	27230-065
5	12	589	553	500	25230-001		25230-010	
6	12	589	553	600	25230-002	27230-066	25230-011	27230-065
7	12	589	553	800	25230-003		25230-012	
8	16	767	553	500	25230-001		25230-010	
9	16	767	553	600	25230-002	27230-066	25230-011	27230-065
10	16	767	553	800	25230-003		25230-012	
11	20	945	553	500	25230-001		25230-010	
12	20	945	553	600	25230-002	27230-066	25230-011	27230-065
13	20	945	553	800	25230-003		25230-012	
14	25	1167	553	500	25230-001		25230-010	
15	25	1167	553	600	25230-002	27230-066	25230-011	27230-065
16	25	1167	553	800	25230-003		25230-012	
17	34	1567	553	500	25230-001		25230-010	
18	34	1567	553	600	25230-002	27230-066	25230-011	27230-065
19	34	1567	553	800	25230-003		25230-012	
20	38	1745	553	500	25230-001		25230-010	
21	38	1745	553	600	25230-002	27230-066	25230-011	27230-065
22	38	1745	553	800	25230-003		25230-012	
23	43	1967	553	500	25230-001		25230-010	
24	43	1967	553	600	25230-002	27230-066	25230-011	27230-065
25	43	1967	553	800	25230-003		25230-012	
26	47	2145	553	500	25230-001		25230-010	
27	47	2145	553	600	25230-002	27230-066	25230-011	27230-065
28	47	2145	553	800	25230-003		25230-012	

If you would like to have the individual components of your configured ServicePLUS cabinet fitted, please add the suffix **/05** to the part number



Further information www.schroff.biz/oneclick oneClick code = part number