## **SIEMENS**

## Data sheet

6GK1901-1BB10-2AA0

Product type designation

Product description

## IE FC RJ45 Plug 180 (2x2)

RJ45 data connector
IE FC RJ45 PLUG 180 2X2, RJ45 PLUG CONNECTOR
(10/100MBIT/S) W. RUGGED METAL HOUSING AND FC
CONNECTING METHOD, FOR IE FC CABLE 2X2 180 DGR CABLE
OUTLET 1 PACK = 1 PCS



Suitability for use For connection to IE FC TP cables 2x2, suitable for fast assembly with the FastConnect system

Transmission rate
Transfer rate / for Industrial Ethernet 10 Mbit/s, 100 Mbit/s

Interfaces	
Number of electrical connections	
<ul> <li>for Industrial Ethernet FC TP cables</li> </ul>	4
• for network components or terminal equipment	1
Type of electrical connection	
• for Industrial Ethernet FC TP cables	integrated cut-and-clamp contacts for 4-wire TP FC installation cable
• for network components or terminal equipment	RJ45 connector
Type of electrical connection / FastConnect	Yes

Mechanical data	
Material / of the enclosure	metal
Number of reuses	10

Design, dimensions and weight	
Type of cable outlet	180° cable outlet
Width	13.7 mm
Height	16 mm
Depth	55 mm
Net weight	35 g
Permitted ambient conditions	
Ambient temperature	
during operation	-40 +85 °C
during storage	-40 +85 °C
during transport	-40 +85 °C
Relative humidity / at 25 °C / without condensation /	95 %
during operation / maximum	
Protection class IP	IP20
Product properties, functions, components / genera	l
Product property	
● PoE capability	Yes
<ul><li>PoE+capability</li></ul>	Yes
• silicon-free	Yes
Product component	
• strain relief	Yes
Standards, specifications, approvals	
Certificate of suitability	
<ul> <li>RoHS conformity</li> </ul>	Yes
<ul><li>UL approval</li></ul>	Yes
• cULus approval	Yes
<ul> <li>Railway application in accordance with EN 50155</li> </ul>	No
Standard for structured cabling	Cat5
Further Information / Internet Links	
Internet-Link	
<ul> <li>to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
to website: Information and Download Center	http://www.siemens.com/automation/net/catalog
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
to Wobolto. Industry Offilia Support	

**last modified:** 17.07.2015