Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.











**EAN:** 4013288221162 **Size:** 115x60x40 mm

Part number:05004185001Weight:175 gArticle number:Bicycle Set 5Country of origin:CZ

Customs tariff 82079030

number:

• Short compact Stubby shape with magazine for working in tight installation spaces, including 7 stainless steel bits

- Ergonomic 2-component Kraftform handle for precise work
- Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)
- Captive and swiveling bit magazine for easy removal and safe storage of bits
- Take it easy tool finder: colour coding according to profile and size

Particularly small bit hand-holder with short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, tight, left). Includes 7 stainless steel bits, 6 of which are located in a magazine in the handle and one in the bit holder. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working. Take it easy tool finder: With size stamping and colour coding by output to help you find the required bit easily.















#### Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



#### Set contents:



#### 3840/1 TS

05071075001 1 x 5 x 25 mm 05071073001 1 x 3 x 25 mm 05071074001 1 x 4 x 25 mm 05071072001 1 x 2.5 x 25 mm



#### 3867/1 TS TORX®

05071035001 1 x TX 25 x 25 mm 05071032001 1 x TX 10 x 25 mm



## 3851/1 TS PH

05071010001 1 x PH 1 x 25 mm

# Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined

# Handle with integrated bit magazine



The handle can be opened and thus gives access to the six bits contained in the magazine.

#### Swiveling bit magazine



The swiveling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

# Ratchet function

Bit Magazine



Stubby Ratchet Screwdriver with

The ratchet mechanism is fine-toothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1


#### Stainless Steel Bits

screwdriving situations.



Wera stainless steel bits are manufactured out of stainless steel so unsightly rust can be avoided. The stainless steel bits from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

#### "Take it easy" tool finder



"Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool.

#### Web link

https://products.wera.de/en/kraftform\_kompakt\_kraftform\_kompakt\_stubby\_with\_kraftform\_bit-holding\_stubby\_screwdriver\_handle\_bicycle\_set\_5.html

### Bicycle Set 5, 7 pieces

Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



Web link

 $https://products.wera.de/en/kraftform\_kompakt\_stubby\_with\_kraftform\_bit-holding\_stubby\_screwdriver\_handle\_bicycle\_set\_5.html$