Our Autumn/Winter production innovations







	F O R		a ware
EAN:	4013288221148	Size:	115x60x40 mm
Part number:	05008885001	Weight:	177 g
Article number:	Kraftform Kompakt Stubby Magazin RA 3	Country of origin:	CZ
	U U	Customs tariff	82079030

- Short, compact Stubby shape for working in tight installation spaces, with 6 bits in the integrated magazine
- Ergonomic 2-component Kraftform handle for precise work
- Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)

number:

- · Captive and swiveling bit magazine for easy removal and safe storage of bits
- Tough viscous bits for universal use

Particularly small bitholding screwdriver with extremely short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, fixed, left). Includes 6 tough, universal bits, which are located in a magazine in the handle. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working.

https://products.wera.de/en/news_and_promotional_products_autumn_winter_2021_2022_our_autumn_winter_production_innovations_kraftform_kompakt_stubby_magazin_ra_

Our Autumn/Winter production innovations

Set contents:



 851/1 Z PH

 05072070001
 1 x PH 1 x 25 mm

 05072072001
 1 x PH 2 x 25 mm

 05072074001
 1 x PH 3 x 25 mm



800/1 Z 05072055001 05072059001 05072061001

1 x 0.6 x 4.5 x 25 mm 1 x 1 x 5.5 x 25 mm

1 x 1.2 x 6.5 x 25 mm

Compact shape



Particularly small bit hand-holder with extremely short bit mounting for hard to reach areas.



Handle with integrated bit

magazine

The handle can be opened and thus gives access to the six bits contained in the magazine.



The swiveling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

Ratchet function



The ratchet mechanism is finetoothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1

Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

https://products.wera.de/en/news_and_promotional_products_autumn_winter_2021_2022_our_autumn_winter_production_innovations_kraftform_kompakt_stubby_magazin_ra_