















EAN:

4013288194831

Size:

250x117x55 mm

Part number:

05073677001

Weight: 364 g

Article number:

Kraftform Micro 12

Electronics 1

**Customs tariff** 

Country of origin:

CZ

number:

82054000

















- Kraftform Micro screwdriver for slotted, Phillips, TORX® BO, Hex, IPR and Microstix® screws plus ejector.
- Kraftform Micro handle for fast and ergonmic working
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Kraftform Micro set in a robust pouch
- Take it easy tool finder: colour coding according to profile and size

High quality Wera Micro screwdriver set for precision mechanical work. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit. Includes practical rack for tidy storage of the screwdrivers.

https://products.wera.de/en/screwdrivers\_series\_kraftform\_micro\_kraftform\_micro\_12\_electronics\_1.html

# Kraftform Micro 12 Electronics 1 Screwdriver set for electronic applications, 12 pieces

# Series Kraftform Micro



#### Set contents:



#### 2050 PH Micro

05345290001<sup>1),2)</sup> 1 x PH 000 x 40 mm 05118019001<sup>1),2)</sup> 1 x PH 00 x 40 mm 05118026001<sup>3)</sup> 1 x PH 0 x 40 mm

Optimised for Asian PH screws
On the output side, the blade is turned to a nominal length of 10 mm.
Size 0 modificated according to JOIS 0 (Japanese Camera Industrial Standard)



#### 2067 TORX® BO Micro

05118046001 1 x TX 8 x 60 mm 05118050001 1 x TX 10 x 60 mm



# 2067 TORX PLUS® IPR Micro

05030160001 1 x 1 IPR x 40 mm



# 2035 Micro

05117997001 1 x 0.35 x 2.5 x 40 mm 05118002001 1 x 0.23 x 1.5 x 40 mm



#### 2069 Micro

05118112001 1 x 2.5 x 60 mm 05118114001 1 x 3 x 60 mm



# 2072

05118145001 1 x m x 40 mm



#### 1429


05027456001 1 x 1 x 3.5 x 50 mm

#### **Kraftform Micro Handle**




Multi-component screwdriver handle for ergonomic working.

# The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

# The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

Web link

https://products.wera.de/en/screwdrivers\_series\_kraftform\_micro\_kraftform\_micro\_12\_electronics\_1.html

Screwdriving jobs in electrical and

precision engineering applications

are often tedious and time-

consuming. We learned from users

what is important for them:

working speeds, torque, precision

- and we then focused particularly


on these issues.

# Kraftform Micro 12 Electronics 1 Screwdriver set for electronic applications, 12 pieces

# Series Kraftform Micro



# The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

#### The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

#### Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

# "Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.