

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0008520071](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)  
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [2478](#)  
 Application Power, Wire-to-Board  
 Crimp Quality Equipment Yes  
 Overview [KK® Interconnect System - Molex](#)  
 Packaging Alternative [08520072 \(Loose\)](#)  
 Product Name KK 396, KK 508  
 UPC 800753758131

**Physical**

Gender Female  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.198/g  
 Packaging Type Reel  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 2.79mm max.  
 Wire Size AWG 18, 20, 22, 24  
 Wire Size mm² N/A

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Engineering Number 2478-3-(P909)

**Reference - Drawing Numbers**

Packaging Specification [PK-2759-002-001](#)  
 Product Specification [PS-08-50-001](#)  
 Sales Drawing [SD-2478-001](#)



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/71/2019 (16 July  
 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[2478 Series](#)

**Use With**

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,  
[5239](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Extraction Tool	<a href="#">11030016</a>
-----------------	--------------------------

Terminator Die	<a href="#">11402096</a>
----------------	--------------------------

Hand Crimp Tool for	<a href="#">638279500</a>
---------------------	---------------------------

3.96mm Pitch KK

Crimp Terminals,

18-24 AWG

Mini-Mac Applicator	<a href="#">638885000</a>
---------------------	---------------------------

for KK and Trifurcon

Crimp Terminals

This document was generated on 08/09/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**