Kraftform Kompakt Stubby magazine RA 2, 6 pieces

Our Autumn/Winter production innovations













EAN: 4013288221131 Size: 115x60x40 mm

05008884001 Part number: Weight: 175 g Article number: Kraftform Kompakt Stubby Country of origin: CZ

Customs tariff

82079030

number:



• Ergonomic 2-component Kraftform handle for precise work

Magazin RA 2

- Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)
- Captive and swiveling bit magazine for easy removal and safe storage of bits
- Take it easy tool finder: colour coding according to profile and size

Particularly small bitholding screwdriver with extremely short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, fixed, left). Includes 6 tough, universal bits, which are located in a magazine in the handle. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working. Take it easy tool finder: With size stamping and colour coding by output to help you find the required bit easily.









Kraftform Kompakt Stubby magazine RA 2, 6 pieces

Our Autumn/Winter production innovations



Set contents:



851/1 BTZ PH

05056420001 1 x PH 1 x 25 mm 05056422001 1 x PH 2 x 25 mm



855/1 BTZ PZ

05056720001 1 x PZ 1 x 25 mm 05056722001 1 x PZ 2 x 25 mm



867/1 TORX® BTZ

05066126001 1 x TX 25 x 25 mm



800/1 BTZ

05056064001 1 x 0.8 x 5.5 x 25 mm

Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Handle with integrated bit magazine



The handle can be opened and thus gives access to the six bits contained in the magazine.

Swiveling bit magazine



Captive and swiveling bit magazine for easy removal and safe storage of bits

Ratchet function



The ratchet mechanism is fine-toothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1

Web link

https://products.wera.de/en/news_and_promotional_products_autumn_winter_2021_2022_our_autumn_winter_production_innovations_kraftform_kompakt_stubby_magazin_ra_

Kraftform Kompakt Stubby magazine RA 2, 6 pieces

Our Autumn/Winter production innovations

Wera BE 4 7001 REBEI

BiTorsion Bits

"Take it easy" tool finder



BiTorsion bits are absolutely premium products. They have a softer BiTorsion zone which reduces the hardness of the shaft by about 20 % in comparison to the drive tip. This means that the peak loads that cause bit breakage and premature wear are absorbed in this zone — something which enhances the service life of the bits.



"Take it easy" tool finder with colour coding according to profiles and size stamp — for simple and rapid accessing of the required