

## Kraftform Kompakt 60 RA, 17 pieces

Kraftform Kompakt Vario with Ratchet Function.



<b>EAN:</b>	4013288155290	<b>Size:</b>	190x135x55 mm
<b>Part number:</b>	05051040001	<b>Weight:</b>	560 g
<b>Article number:</b>	KK 60 RA	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- Kraftform Kompakt 60 RA with ratchet function for high working speeds
- Kraftform with anti-roll feature, multi-component with Rapidaptor technology
- Ratchet function
- Fine-pitched teeth for small return angle; switchover ring (right, fixed, left)
- Maximum torque of up to 50 Newton metres

17-piece set with bits in a length of 89 mm in a practical pouch. 1 holder 816 RA Kraftform with ratchet function: fine-toothing for a small return angle, switchover ring (right, fixed, left), maximum torque of up to 50 Newton metres. 1/4" hexagon socket head take-up and Rapidaptor technology for low-fatigue working and rapid bit change; magnetic.

### Web link

[https://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_kk\\_60\\_ra.html](https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra.html)

Wera - KK 60 RA  
05051040001 - 4013288155290


Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)


# Kraftform Kompakt 60 RA, 17 pieces


## Kraftform Kompakt Vario with Ratchet Function.





### Set contents:


 **816 RA**  
05051461001 1 x 1/4" x 142 mm

 **855/4 Z PZ**  
05060029001 1 x PZ 1 x 89 mm  
05060035001 1 x PZ 2 x 89 mm  
05060043001 1 x PZ 3 x 89 mm

 **800/4 Z**  
05059488001 1 x 1 x 5.5 x 89 mm

 **851/4 Z PH**  
05059760001 1 x PH 1 x 89 mm  
05059775001 1 x PH 2 x 89 mm  
05059795001 1 x PH 3 x 89 mm

 **867/4 Z TORX® BO**  
05060050001 1 x TX 10 x 89 mm  
05060051001 1 x TX 15 x 89 mm  
05060052001 1 x TX 20 x 89 mm  
05060053001 1 x TX 25 x 89 mm  
05060054001 1 x TX 30 x 89 mm

 **840/4 Z Hex-Plus**  
05059630001 1 x 3 x 89 mm  
05059631001 1 x 4 x 89 mm  
05059632001 1 x 5 x 89 mm  
05059633001 1 x 6 x 89 mm

### 816 RA Ratchet screwdriver




Ratchet screwdriver, fine-tooth design for minimal return angle, switchover ring (right, locked, left), maximum torque of up to 50 Newton metres, 1/4" hexagon chuck with Rapidaptor technology i.e. rapid-in, rapid-out, rapid-spin, chuck-all and single-hand function for rapid bit change, magnetic, suitable for hexagon socket insert bits as per DIN ISO 1173-C 6.3 and E 6.3 and Wera series 1 and 4

### Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

### Fine-tooth design



Fine action 44 tooth system for precision work. Great time savings when screwdriving.

### Fine adjustment work



Additionally, the lockable neutral position permits exact adjustment work without having to change the screwdriving direction every time. Lockable neutral position for fine adjustment work.

### Web link

[https://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_kk\\_60\\_ra.html](https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra.html)

Wera - KK 60 RA  
05051040001 - 4013288155290

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Changing ratchet direction



Ergonomic design of the reverse direction switch.

Chuck-all



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Web link

[https://products.wera.de/en/kraftform\\_kompakt\\_kraftform\\_kompakt\\_vario\\_with\\_ratchet\\_function\\_fine\\_tooth\\_system\\_for\\_precision\\_work\\_kk\\_60\\_ra.html](https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_vario_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra.html)

Wera - KK 60 RA  
05051040001 - 4013288155290

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)