2067 TORX® screwdriver for TORX® screws for electronic applications, TX 1 x 40 mm

Series Kraftform Micro







EAN: 4013288108593 **Size:** 137x13x13 mm

Part number:05118035001Weight:10 gArticle number:2067 TORX®Country of origin:CZ

Customs tariff 82054000

number:















- Kraftform Micro screwdriver for recessed TORX® screws
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- · Anti-roll feature and swivel cap for rapid twisting
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size

High quality Wera Micro screwdriver for precision mechanical jobs. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit. "Take it easy" tool finder with colour coding according to profiles and size stamp — for simple and rapid accessing of the required tool.

2067 TORX® screwdriver for TORX® screws for electronic applications, TX 1 x 40 mm

Series Kraftform Micro



Kraftform Micro Handle




Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.


The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone

on these issues.



Screwdriving jobs in electrical and

precision engineering applications

are often tedious and time-

consuming. We learned from users

what is important for them:

working speeds, torque, precision

- and we then focused particularly

The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

2067 TORX® screwdriver for TORX® screws for electronic applications, TX 1 x 40 mm Series Kraftform Micro



Further versions in this product family:

	\odot	A	A ▼	\varnothing	☐ Å
		mm	mm	mm	inch
05118035001	TX 1	40	97	2.0	1 9/16
05118036001	TX 2	40	97	2.0	1 9/16
05118037001	TX 3	40	97	2.0	1 9/16
05118039001	TX 4	40	97	2.5	1 9/16
05118040001	TX 5	40	97	3.0	1 9/16
05118042001	TX 6	40	97	3.0	1 9/16