2054 Screwdriver for hexagon socket screws for electronic applications, 1.5 x 60 mm

Series Kraftform Micro







EAN: 4013288032102 **Size:** 157x13x13 mm

Part number:05118066001Weight:13 gArticle number:2054 MicroCountry of origin:CZ

Customs tariff 82054000

number:

















- Kraftform Micro screwdriver for hexagon socket screws
- · Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- · Hex-Plus allows socket head screws to live longer
- Take it easy tool finder: colour coding according to profile and size

High quality Wera Micro screwdriver for precision mechanical jobs. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit. "Take it easy" tool finder with colour coding according to profiles and size stamp — for simple and rapid accessing of the required tool.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2054_micro.html

Wera - 2054 Micro 05118066001 - 4013288032102

2054 Screwdriver for hexagon socket screws for electronic applications, 1.5 x 60 mm

Series Kraftform Micro




Hex-Plus



The refined screwdriver for electronics technicians



Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision — and we then focused particularly on these issues.



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!



Multi-component screwdriver handle for ergonomic working.




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone




The fast-turning zone

"Take it easy" Tool Finder



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.



The fast-turning zone just below the rotating cap allows rapid twisting.



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2054_micro.html

Wera - 2054 Micro 05118066001 - 4013288032102

2054 Screwdriver for hexagon socket screws for electronic applications, 1.5 x 60 mm Series Kraftform Micro



Further versions in this product family:

		0		\(\rightarrow\)	\oslash	
	mm	inch	□ v mm	⊕ ਾ mm	mm	□▼ inch
05118060001	0.7	-	40	97	3.0	1 9/16
05118062001	0.9	-	40	97	3.0	1 9/16
05118064001	1.3	-	40	97	3.0	1 9/16
05118066001	1.5	-	60	97	3.0	2 3/8
05118068001	2	-	60	97	3.0	2 3/8
05118070001	2.5	-	60	97	4.0	2 3/8
05118072001	3.0	-	60	97	4.0	2 3/8
05345284001	-	0.028"	40	97	3.0	1 9/16
05345285001	-	0.035"	40	97	3.0	1 9/16
05118074001	-	0.05	40	97	3.0	1 9/16
05118076001	-	1/16	60	97	3.0	2 3/8
05118078001	-	5/64	60	97	3.0	2 3/8
05118080001	-	3/32	60	97	4.0	2 3/8
05118082001	-	7/64	60	97	4.0	2 3/8
05118075001	-	1/8	60	97	4.0	2 3/8