


1100 series stylish ABS enclosures

1101 SERIES WITH ABS LID

Aesthetically pleasing electronic enclosure with solid ABS lid. Designed for a broad range of applications.

- Lid and base moulded in ABS- UL94-V0
- Lid mounted by four self tapping screws
- Bevelled edges and curved side walls
- 1.2mm membrane keypad recesses in lid and base
- Polished finish for ease of cleaning and stylish appearance
- Deep profile for maximum internal volume
- Plastic standoffs in base for mounting of PCBs
- Excellent properties for machining
- This enclosure can easily be recycled
- 1100 series has been designed to meet the requirements of IP54



CSACST



SPECIFICATION


Materials	Lid and base high impact ABS-UL94-V0
Operating temperature	Resistant to temperatures between -5°C and 80°C
Protection class	1100 series has been designed to meet the requirements of IP54
Standard colours	Light grey similar to RAL 7047
Standard unit includes	Base and lid 4 x self tapping screws

LIGHT GREY	LENGTH	WIDTH	HEIGHT
CSACST001	90mm	50mm	35mm
CSACST002	110mm	60mm	40mm
CSACST003	125mm	75mm	50mm
CSACST004	155mm	95mm	60mm
CSACST005	190mm	115mm	75mm
CSACST006	220mm	140mm	90mm

1102 SERIES WITH TRANSPARENT LID

Electronic enclosure featuring a transparent lid, designed for applications that require visible electronics. High-impact polycarbonate smoked effect lid.

- Base moulded in ABS, UL94-V0
- Lid moulded in transparent, Polycarbonate, UL94-V0
- Lid mounted by four self tapping screws
- Bevelled edges and curved side walls
- 1.2mm membrane keypad recesses in lid and base
- Polished finish for ease of cleaning and stylish appearance
- Deep profile for maximum internal volume
- Pillars in base for mounting of PCBs
- Excellent properties for machining
- This enclosure can easily be recycled
- 1100 series has been designed to meet the requirements of IP54



CSACTT



SPECIFICATION

Materials	Lid high impact PC, UL94-V0 Base high impact ABS, UL94-V0
Operating temperature	Resistant to temperatures between -5°C and 80°C Lid resistant to temperatures up to 120°C
Protection class	IP54 1100 series has been designed to meet the requirements of IP54
Standard colours	Light grey similar to RAL 7047
Standard unit includes	Base and lid 4 x self tapping screws

LIGHT GREY	LENGTH	WIDTH	HEIGHT
CSACTT001	90mm	50mm	35mm
CSACTT002	110mm	60mm	40mm
CSACTT003	125mm	75mm	50mm
CSACTT004	155mm	95mm	60mm
CSACTT005	190mm	115mm	75mm
CSACTT006	220mm	140mm	90mm