

# Rittal – The System.

Faster – better – everywhere.

## ► Compact enclosure AX Basic enclosure AX, sheet steel – AX 1350.000

Date : Oct 4, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Compact enclosure AX Basic enclosure AX, sheet steel – AX 1350.000

created: 04.10.2021 build on [www.rittal.com/uk-en](http://www.rittal.com/uk-en)



## Product description

<b>Material:</b>	Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal
<b>Surface finish:</b>	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 66
<b>Protection category NEMA:</b>	NEMA 1, 3R, 4, 12
<b>Type rating to UL 50E:</b>	Type 1, 3R, 4, 12
<b>IK Code:</b>	IK10
<b>Supply includes:</b>	Enclosure with door(s) Gland plate(s) in enclosure base Mounting plate Perforated door strip Lock: 3 mm double-bit
<b>Basic material:</b>	Sheet steel

## Product description

<b>Dimensions:</b>	Width: 500 mm Height: 500 mm
--------------------	---------------------------------

Depth: 300 mm

<b>Material thickness:</b>	Enclosure: 1.5 mm Door: 1.5 mm Mounting plate: 2.5 mm
<b>Mounting plate:</b>	Width: 450 mm Height: 475 mm
<b>Number of doors:</b>	1
<b>Door hinged on the right, may be swapped to the left:</b>	yes
<b>Number of cam locks:</b>	2
<b>Lock version:</b>	Cam
<b>Number of locks:</b>	2
<b>Lock insert:</b>	3 mm double-bit
<b>Gland plate, size:</b>	6
<b>Gland plate, qty.:</b>	1
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	19 kg
<b>EAN:</b>	4028177813281
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC000261
<b>ETIM 6.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>Product description:</b>	AX Compact enclosure, WHD: 500x500x300 mm, sheet steel, with mounting plate, single-door, with two cam locks

## Approvals

**Approvals:** Bureau Veritas

DNV-GL  
Lloyds Register of Shipping  
UL + C-UL

---

<b>Certificates:</b>	Certificate of manufacturer according to RMRS
----------------------	---

---

<b>Declarations:</b>	Declaration of conformity
----------------------	---------------------------

---