


LaserMark LM WO 23/55 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



LM WriteOn cable markers on DIN A4 sheets are used for labelling conductors and cables up to an outside diameter of 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Easy and quick labelling with a DIN A4 laser printer or STI pen

General ordering data

Type	LM WO 23/55 WS
Order No.	1695721044
Version	LaserMark, Conductor and cable markers, 6.8 - 12 mm, 23 x 55 mm, White
GTIN (EAN)	4008190924676
Qty.	10 pc(s).

**LaserMark
LM WO 23/55 WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	55 mm	Width (inches)	2.165 inch
Height	23 mm	Height (inches)	0.906 inch
Depth	0.2 mm	Depth (inches)	0.008 inch
Net weight	10.1 g		

General data

Adhesive	Acrylate	Colour	White
Material	Polyester film	Material colour according to resistance code	9
Number of markers per packaging unit	400	Number per sheet	40
Operating temperature range	-40...150 °C	Size of labelling field	23 x 12.7 mm
Type of printing	blank	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	55 mm

Conductor and cable markers

Conductor O.D.	6.8 - 12 mm	Conductor O.D., max.	12 mm
Conductor O.D., min.	6.8 mm	Conductor cross-section, max.	50 mm ²
Conductor cross-section, min.	10 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-14-07-08
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Software	M-Print PRO configuration file

Data sheet

**LaserMark
LM WO 23/55 WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

