



Bezeichnung Configuration	L	Ident-Nr. Part-Nr.
Federleiste SMC-B, 12 pol. ohne Codierung snap-in Verriegelung (ERNI Ident-Nr.: 214345) IDC Female Connector SMC-B, 12 pol. without Coding with Locking Latches (ERNI Part-Nr.: 214345) Flachbandkabel, PVC (ERNI Ident-Nr.: 053786) Flat cable, PVC (ERNI Part-Nr.: 053786)	300mm	173801
	200mm	173800
	100mm	173799
Federleiste SMC-B, 26 pol. ohne Codierung snap-in Verriegelung (ERNI Ident-Nr.: 214346) IDC Female Connector SMC-B, 26 pol. without Coding with Locking Latches (ERNI Part-Nr.: 214346) Flachbandkabel, PVC (ERNI Ident-Nr.: 053787) Flat cable, PVC (ERNI Part-Nr.: 053787)	300mm	173798
	200mm	173797
	100mm	173796
Federleiste SMC-B, 50 pol. ohne Codierung snap-in Verriegelung (ERNI Ident-Nr.: 214347) IDC Female Connector SMC-B, 50 pol. without Coding with Locking Latches (ERNI Part-Nr.: 214347) Flachbandkabel, PVC (ERNI Ident-Nr.: 034575) Flat cable, PVC (ERNI Part-Nr.: 034575)	300mm	173795
	200mm	173794
	100mm	173793
Federleiste SMC-B, 68 pol. ohne Codierung snap-in Verriegelung (ERNI Ident-Nr.: 214348) IDC Female Connector SMC-B, 68 pol. without Coding with Locking Latches (ERNI Part-Nr.: 214348) Flachbandkabel, PVC (Ident-Nr.: 134527) Flat cable, PVC (ERNI Part-Nr.: 134527)	300mm	193890
	200mm	193889
	100mm	193888
Federleiste SMC-B, 80 pol. ohne Codierung snap-in Verriegelung (ERNI Ident-Nr.: 214349) IDC Female Connector SMC-B, 80 pol. without Coding with Locking Latches (ERNI Part-Nr.: 214349) Flachbandkabel, PVC (Ident-Nr.: 134528) Flac cable, PVC (ERNI Part-Nr.: 134528)	300mm	193893
	200mm	193892
	100mm	193891

Information:	Tolerances	 All Dimensions in mm	Scale	2:1
	All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Designation  <b>SMC-SKV</b> <b>Verdrahtungs-System</b>	
Subject to modification without prior notice. Drawing will not be updated.				
		 www.ERNI.com		1
b	17.07.2006			
Index	Date	VERSMC		

Consider protection memo from DIN 34