

**Bolt-type screw terminals  
WTW WF10/WF12 2300**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

**General ordering data**

Type	WTW WF10/WF12 2300
Order No.	<a href="#">1780920000</a>
Version	Bolt-type screw terminals, Seperation plate, grey, 2 mm
GTIN (EAN)	4032248241149
Qty.	20 pc(s).

## Bolt-type screw terminals WTW WF10/WF12 2300

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Width	2 mm	Width (inches)	0.079 inch
Height	155.8 mm	Height (inches)	6.134 inch
Depth	76.45 mm	Depth (inches)	3.01 inch
Mounting dimension - width	2 mm	Net weight	41.05 g

### Temperatures

Operating temperature range, max.	160 °C	Storage temperature, max.	40 °C
Storage temperature, min.	10 °C	Storage temperature	10 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	160 °C

### Material data

Material	Epoxy resin	Colour	grey
UL 94 flammability rating	V-0		

### System specifications

Version	End and intermediate plate
---------	----------------------------

### Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

### Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-33
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>