

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930158](#)
Status: **Active**
Overview: VersaKrimp Terminals and Splices
Description: VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19193](#)
 Crimp Quality Equipment Yes
 Overview [VersaKrimp Terminals and Splices](#)
 Product Name VersaKrimp
 Type Ring
 UPC 800753039520

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 2.743/g
 Packaging Type Adhesive Tape on Reel
 Stud Size 5/16" (M8)
 Termination Interface: Style Crimp or Compression
 Wire Size AWG 8
 Wire Size mm² 6.60-10.50

Material Info

Engineering Number D-350-56T

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
 Sales Drawing SD-19193-016-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)10043-DC (17
 Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19193 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for VersaKrimp High Temperature Nickel Plated Steel Terminals on Tape, 8 AWG	190270105
ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals And Butt Splices on Tape, 8 AWG	190270111
ATP Crimp Dies for VersaKrimp Ring	190270117

Tongue Terminals,
for Solid Copper
or Steel Wire (Anti
Rotation)

ATP Crimp Dies 190270120

for Versakrimp 8
AWG Ring Tongue

Terminals, for
Stripped Magnet or
Steel 6 AWG Wire

ATP Crimp Dies 190472000

for VersaKrimp
Copper Ring Tongue

Terminals and Butt
Splices on Tape, 8

AWG, use with Tape
Crimp Module and

ATP-201 Press

This document was generated on 03/21/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION