



EN

Datasheet

RS PRO 38mm Insulation Shackle Safety Padlocks

**Stock No. 196-3758 196-3759 196-3760 196-3761
196-3762 196-3763**

Material: nylon PA, safety insulation material.

- PA is resistant impact, UV, corrosion, heat and low temperature, Durable, lightweight, Non conductive.
- High security, reserved-for-safety cylinder, Key retaining-ensures that padlock is not left unlocked.
- Standard "Danger" label and write on properly labels included front and back.
- Color available: red, orange, yellow, green, blue, black, brown, white, black.

Weight: 83g

Key System: Key Difference

Body Size: 45mm x 38mm x 20mm


Shackle Size: 38mm height, 6mm diameter

Material: Nylon shackle and nylon body

Color: Red, orange, yellow, green, blue, black, brown, white, dark blue or OEM



SPECIFICATION

Product Description	RS code	Size
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Blue	1763758	
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Blue	1763759	
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Green	1763760	
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Orange	1763761	
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Black	1763762	
RS PRO 38mm nylon padlock, Nylon shackle, brass key, Yellow	1763763	

RS Article#	Supplier Article#	Brand	Lock Type	Shackle Diameter	Shackle Length	Body Width	Bluetooth
1963758	EP-8531 Red	RS PRO	key	6.4mm	38mm	38mm	N
1963759	EP-8531 Blue	RS PRO	key	6.4mm	38mm	38mm	N
1963760	EP-8531 Green	RS PRO	key	6.4mm	38mm	38mm	N
1963761	EP-8531 Orange	RS PRO	key	6.4mm	38mm	38mm	N
1963762	EP-8531 Black	RS PRO	key	6.4mm	38mm	38mm	N
1963763	EP-8531 Yellow	RS PRO	key	6.4mm	38mm	38mm	N

RS Article#	Keyed Alike	Indoor/Outdoor	Weather Proof	Body Material	Shackle Material	Colour	Quantity Per Package
1963758	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	red	6
1963759	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	blue	6
1963760	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	green	6
1963761	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	orange	6
1963762	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	black	6
1963763	NO	Indoor & Outdoor	Y	Nylon, brass	Nylon	yellow	6