

PRODUCT-DETAILS

RB121P-5VDC

RB121P-5VDC Interface relay R600 1c/o,A1-A2=5VDC,5-250VAC/60mA-6A



General Information

Extended Product Type	RB121P-5VDC
Product ID	1SNA645034R2300
EAN	4013614507977
Catalog Description	RB121P-5VDC Interface relay R600 1c/o,A1-A2=5VDC,5-250VAC/60mA-6A

Long Description	<p>The RB121P-5VDC is a boxed interface relay with screw terminals, which can be seamlessly snap-on mounted onto a DIN Rail. The relay is soldered into device housing, ensuring a high resistance against vibration. This relay operates with a 5 V DC rated control supply voltage and has a 1 c/o (SPDT) output with contacts rated at 250 V / 6 A. This 6mm wide boxed interface relay may be used for electrical isolation, amplification and signal matching and enables the switching of high currents on a small footprint. It has an integrated LED, which provides the visual indication of the energization of the relay coil and UL 94-V0 certified device housing, improving safety by providing high levels flame retardation. Jumper bars are available as accessories.</p>
------------------	--

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	2CDC110004C0210_05
Instructions and Manuals	15VC645000M9000

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.02 kg

Technical

Function	Boxed interface relay R600
Sub-Function	Relay with built in LED
Output	1 c/o (SPDT) contact
Output Signal	5 ... 250VAC / 60mA ... 6A
Rated Control Supply Voltage (U _s)	5 V DC
Terminal Type	Screw Terminals

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

CB Certificate	CB_DK-53188-UL
CCC Certificate	CCC_2017010303941444
CQC Certificate	CQC_2017010303941444
CSA Certificate	CSA_254821
cUR Certificate	cUR_E352056
Declaration of Conformity - CCC	CCC_2020980303000254
Declaration of Conformity - CE	1SVD982016-0001
Declaration of Conformity - UKCA	1SVD982016-1000
EAC Certificate	EAC_RU_C-FR.ME77.B.01634
Instructions and Manuals	1SVC645000M9000
LR Certificate	LR_16_20068
RoHS Information	1SVD982016-0001
UR Certificate	UR_E352056

Container Information

Package Level 1 Units	box 10 piece
Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	3472596450342

Classifications

Object Classification	K
-----------------------	---

Code	
ETIM 4	EC001437 - Switching relay
ETIM 5	EC001437 - Switching relay
ETIM 6	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
ETIM 8	EC001437 - Switching relay
eClass	V11.0 : 27371601
UNSPSC	39122331
E-Number (Finland)	2712046

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

