

3M™ Solus™ 2000 Series

The 3M™ Solus™ 2000 Series features adjustable ratchet temples that allow the wearer to customize fit—a first for our Solus lineup. Choose from several lens coating options, including 3M™ Scotchgard™ Anti-Fog, multiple lens colors and features like a removable foam gasket to create a protective eyewear solution for YOU.

Adjustable Ratchet Temples
Multiple position ratchet allows user to adjust lens for facial features and eyeglass position.

Reader Models
Models available with reading diopters +1.5, +2.0, +2.5

Polycarbonate Lenses
▶ Absorb 99.9% of UVA and UVB rays.
▶ Meet the requirements of ANSI Z87.1-2015 Standard as an Impact Rated Spectacle.

Same Protection, New IR Lens Color
Unlike green IR shade lenses, gray IR lenses provide wearers with better color recognition. (Select Models)

Removable Foam-lined Gasket
Helps limit eye exposure to dirt and debris while providing added comfort and cushioning.* (Select Models)

Choose Your Coating
▶ Scotchgard™ Anti-Fog Coating provides fog and abrasion resistance. (Select Models)
▶ Resists fogging longer than traditional anti-fog coatings, up to 25 washings with water.*
▶ Helps provide durable scratch resistance in tough work environments.

*Does not meet ANSI Z87.1 D4 dust or D5 fine dust rating. Users must determine if eyewear is suitable for the application prior to use.
**3M internal testing per EN168 test method when compared with traditional anti-fog coatings.

Available Models:

S2001SGAF-RED
Lens: Clear
Frame Color: Gray/Red

S2002SGAF-RED
Lens: Gray
Frame Color: Gray/Red

S2024AS-RED
Lens: Red Mirror
Frame Color: Gray/Red

S2001SGAF-BGR
Lens: Clear
Frame Color: Gray/Teal

S2002SGAF-BGR
Lens: Gray
Frame Color: Gray/Teal

S2003SGAF-BGR
Lens: Amber
Frame Color: Gray/Teal

S2005SGAF-BGR
Lens: Brown
Frame Color: Gray/Teal

S2007SGAF-BGR
Lens: I/O Gray
Frame Color: Gray/Teal

S2001SGAF-BGR-F
Lens: Clear
Frame Color: Gray/Teal
Foam gasket

S2001AF-BLU
S2001AS-BLU
Lens: Clear
Frame Color: Blue/Gray

READER MODELS

S2008AS-CLR
Lens: Blue Mirror
Frame Color: Clear/Blue

S2001SGAF-CLR
Lens: Clear
Frame Color: Clear/Blue

S2015AF-BLU
Lens: Clear +1.5
Frame Color: Blue/Gray

S2020AF-BLU
Lens: Clear +2.0
Frame Color: Blue/Gray

S2025AF-BLU
Lens: Clear +2.5
Frame Color: Blue/Gray

IR SHADE MODELS

S2017AS-BLK
Lens: IR 1.7 Gray
Frame Color: Black/Green

S2030AS-BLK
Lens: IR 3.0 Gray
Frame Color: Black/Green

S2050AS-BLK
Lens: IR 5.0 Gray
Frame Color: Black/Green

Ordering Information

Product I.D.	3M I.D.	Description	Frame Color	Lens Color	Coating	Units per Case	Foam Gasket
S2001SGAF-RED	70-0717-3285-6	3M™ Solus™ 2000 Series, S2001SGAF-RED, Gray/Red Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Gray/Red	Clear	SGAF AF/AS	20	-
S2002SGAF-RED	70-0717-3286-4	3M™ Solus™ 2000 Series, S2002SGAF-RED, Gray/Red Temples, Scotchgard™ Anti-Fog Coating, Gray AF-AS Lens	Gray/Red	Gray	SGAF AF/AS	20	-
S2024AS-RED	70-0717-3287-2	3M™ Solus™ 2000 Series, S2024AS-RED, Gray/Red Temples, Red Mirror Anti-Scratch Lens	Gray/Red	Red Mirror	AS	20	-
S2001SGAF-BGR	70-0717-3288-0	3M™ Solus™ 2000 Series, S2001SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Gray/Teal	Clear	SGAF AF/AS	20	-
S2002SGAF-BGR	70-0717-3289-8	3M™ Solus™ 2000 Series, S2002SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Gray AF-AS Lens	Gray/Teal	Gray	SGAF AF/AS	20	-
S2003SGAF-BGR	70-0717-3290-6	3M™ Solus™ 2000 Series, S2003SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Amber AF-AS Lens	Gray/Teal	Amber	SGAF AF/AS	20	-
S2005SGAF-BGR	70-0717-3292-2	3M™ Solus™ 2000 Series, S2005SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Brown AF-AS Lens	Gray/Teal	Brown	SGAF AF/AS	20	-
S2007SGAF-BGR	70-0717-3293-0	3M™ Solus™ 2000 Series, S2007SGAF-BGR, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, I/O Gray AF-AS Lens	Gray/Teal	I/O Gray	SGAF AF/AS	20	-
S2001S-GAF-BGR-F	70-0717-3295-5	3M™ Solus™ 2000 Series, S2001SGAF-BGR-F, Gray/Blue-Green Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens, Foam Gasket	Gray/Teal	Clear	SGAF AF/AS	20	✓
S2001AS-BLU	70-0717-3296-3	3M™ Solus™ 2000 Series, S2001AS-BLU, Blue/Gray Temples, Clear Anti-Scratch Lens	Blue/Gray	Clear	AS	20	-
S2001AF-BLU	70-0717-3297-1	3M™ Solus™ 2000 Series, S2001AF-BLU, Blue/Gray Temples, Clear AF-AS Lens	Blue/Gray	Clear	AF/AS	20	-
S2008AS-CLR	70-0717-3380-5	3M™ Solus™ 2000 Series, S2008AS-CLR, Clear/Blue Temples, Blue Mirror Anti-Scratch Lens	Clear/Blue	Blue Mirror	AS	20	-
S2001SGAF-CLR	70-0717-3398-7	3M™ Solus™ 2000 Series, S2001SGAF-CLR, Clear/Blue Temples, Scotchgard™ Anti-Fog Coating, Clear AF-AS Lens	Clear/Blue	Clear	SGAF AF/AS	20	-
Readers Models							
S2015AF-BLU	70-0717-3377-1	3M™ Solus™ 2000 Series, S2015AF-BLU, Blue/Gray Temples, Clear Reader +1.5 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +1.5	AF/AS	20	-
S2020AF-BLU	70-0717-3378-9	3M™ Solus™ 2000 Series, S2020AF-BLU, Blue/Gray Temples, Clear Reader +2.0 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +2.0	AF/AS	20	-
S2025AF-BLU	70-0717-3379-7	3M™ Solus™ 2000 Series, S2025AF-BLU, Blue/Gray Temples, Clear Reader +2.5 Anti-Fog/Anti-Scratch lens	Blue/Gray	Clear +2.5	AF/AS	20	-
IR Shade Models							
S2017AS-BLK	70-0717-3298-9	3M™ Solus™ 2000 Series, S2017AS-BLK, Black/Green Temples, IR 1.7 Gray Anti-Scratch Lens	Black/Green	IR 1.7 Gray	AS	20	-
S2030AS-BLK	70-0717-3301-1	3M™ Solus™ 2000 Series, S2030AS-BLK, Black/Green Temples, IR 3.0 Gray Anti-Scratch Lens	Black/Green	IR 3.0 Gray	AS	20	-
S2050AS-BLK	70-0717-3302-9	3M™ Solus™ 2000 Series, S2050AS-BLK, Black/Green Temples, IR 5.0 Gray Anti-Scratch Lens	Black/Green	IR 5.0 Gray	AS	20	-
Accessories							
S2000-FOAM	70-0717-3381-3	3M™ Solus™ 2000 Series, S2000-FOAM, Replacement Foam Gasket	-	-	-	10ea/bag	-

Explore more protective eyewear at [3M.com/ProtectiveEyewear](https://www.3m.com/ProtectiveEyewear).

#3MScienceofSafety

WARNING: These eye and face protection products help provide limited eye and face protection. Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death. For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read User Instructions and warnings on the package or call 3M PSD Technical Service in the USA at 800-243-4630. In Canada, call Technical Service at 800-267-4114.



Personal Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

Technical Assistance 1-800-243-4630
Customer Service 1-800-328-1667
[3M.com/ProtectiveEyewear](https://www.3m.com/ProtectiveEyewear)

3M PSD products are for occupational use only.

© 3M 2019. All rights reserved. 3M, Solus and Scotchgard are trademarks of 3M. Used under license by 3M subsidiaries and affiliates. Please recycle. Printed in USA. Issued: 11/19 14677HB70-0716-9775-2