

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2042230010](#)
Status: **Active**
Overview: [Squba Sealed Wire-to-Wire Connectors](#)
Description: [Squba Sealed Plug Assembly, 1.80mm Pitch, 10 Circuits, Single Row, No Seal Plugs](#)

Documents:

| | |
|---|---|
| 3D Model | Application Specification 2042200000-AS-000 (PDF) |
| Drawing (PDF) | Packaging Specification 2042230000-PK-000 (PDF) |
| Product Specification 2042200000-PS-000 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification 2042200000-TS-000 (PDF) | Product Literature (PDF) |

Agency Certification

UL E29179

General

| | |
|-----------------------------|--|
| Product Family | Crimp Housings |
| Series | 204223 |
| Application | Power, Signal, Wire-to-Wire |
| Datasheet Order No | 987651-7401 |
| Overview | Squba Sealed Wire-to-Wire Connectors |
| Product Literature Order No | 987651-7401 |
| Product Name | Squba |
| UPC | 191128320351 |


Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 10 |
| Circuits Detail | No Seal Plugs |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Plug |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 4.540/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 1.80mm |
| Pitch - Termination Interface | 1.80mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------------------------------|
| Application Specification | 2042200000-AS-000 |
| Packaging Specification | 2042230000-PK-000 |
| Product Specification | 2042200000-PS-000, 2042200000-TS-000 |
| Sales Drawing | 2042230000-SD-000 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204223](#) Series

Mates With

Squba Receptacle [204220](#)

Use With

Squba Male Terminal [2042261001](#)