

Data sheet | Item number: 210-133

Busbar; tin-plated; 1000 mm long; Cu 10 mm x 3 mm; white

www.wago.com/210-133



Data

Technical data

Main product function

Mounting accessories

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Electrical data

Rated current	140 A
---------------	-------

Material data










Color	white
Weight	300 g

Commercial data

Packaging type	box
Country of origin	DE
GTIN	4045454229443
Customs tariff number	74071000000

Optional accessories

Terminal blocks

	Item no.: 812-100 Ground busbar terminal block; for (10 x 3) mm busbars; 12-pole; 4 mm ² ; Push-in CAGE CLAMP®; 4,00 mm ² ; green-yellow	www.wago.com/812-100
	Item no.: 812-101 Busbar terminal block; for (10 x 3) mm busbars; 12-pole; without push-buttons; 4 mm ² ; 4,00 mm ² ; light gray	www.wago.com/812-101
	Item no.: 812-102 Busbar terminal block; for (10 x 3) mm busbars; 12-pole; without push-buttons; 4 mm ² ; 4,00 mm ² ; dark gray	www.wago.com/812-102
	Item no.: 812-103 Busbar terminal block; for (10 x 3) mm busbars; 12-pole; without push-buttons; 4 mm ² ; 4,00 mm ² ; red	www.wago.com/812-103
	Item no.: 812-104 Busbar terminal block; for (10 x 3) mm busbars; 12-pole; without push-buttons; 4 mm ² ; 4,00 mm ² ; blue	www.wago.com/812-104
	Item no.: 812-110 Ground busbar terminal block; for (10 x 3) mm busbars; 3-pole; 16 mm ² ; CAGE CLAMP®; 16,00 mm ² ; green-yellow	www.wago.com/812-110
	Item no.: 812-111 Busbar terminal block; for (10 x 3) mm busbars; 3-pole; without push-buttons; 4 mm ² ; CAGE CLAMP®; 16,00 mm ² ; light gray	www.wago.com/812-111
	Item no.: 812-112 Busbar terminal block; for (10 x 3) mm busbars; 3-pole; without push-buttons; 4 mm ² ; CAGE CLAMP®; 16,00 mm ² ; dark gray	www.wago.com/812-112
	Item no.: 812-113 Busbar terminal block; for (10 x 3) mm busbars; 3-pole; without push-buttons; 4 mm ² ; CAGE CLAMP®; 16,00 mm ² ; red	www.wago.com/812-113
	Item no.: 812-114	

Subject to changes. Please also observe the further product documentation!



Busbar terminal block; for (10 x 3) mm busbars; 3-pole; without push-buttons; 4 mm²; CAGE CLAMP®; 16,00 mm²; blue www.wago.com/812-114

N-busbar



Item no.: 209-105
Connector; silver-colored www.wago.com/209-105



Item no.: 210-281
Connector; blue www.wago.com/210-281

Shield termination



Item no.: 790-108
Shield clamping saddle; 11 mm wide; diameter of compatible conductor; 3 ... 8 mm www.wago.com/790-108



Item no.: 790-116
Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 ... 16 mm www.wago.com/790-116



Item no.: 790-124
Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 ... 24 mm www.wago.com/790-124



Item no.: 790-140
Shield clamping saddle; diameter of compatible conductor www.wago.com/790-140



Item no.: 790-208
Shield clamping saddle; 12.4 mm wide; 3 ... 8 mm www.wago.com/790-208



Item no.: 790-216
Shield clamping saddle; 21.8 mm wide; 6 ... 16 mm www.wago.com/790-216



Item no.: 790-220
Shield clamping saddle; 30 mm wide; 6 ... 20 mm www.wago.com/790-220



Item no.: 790-398
T-connector; for busbars Cu 10 mm x 3 mm; gray www.wago.com/790-398



Item no.: 791-107
Shield clamp; diameter of compatible conductor; 1.5 mm to 6.5 mm; H max. 40 mm; 10 mm wide www.wago.com/791-107



Item no.: 791-111
Shield clamp; diameter of compatible conductor; 5 mm to 11 mm; H max. 47 mm; 17 mm wide www.wago.com/791-111



Item no.: 791-117
Shield clamp; diameter of compatible conductor; 10 mm to 17 mm; H max. 63 mm; 23 mm wide www.wago.com/791-117



Item no.: 791-124
Shield clamp; diameter of compatible conductor; 16 mm to 24 mm; H max. 78 mm; 30 mm wide www.wago.com/791-124

Downloads

Documentation

Bid Text

210-133

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



210-133 X81 - Datei	19 Feb 2019	xml 2.6 kB	Download
210-133 docx - Datei	23 Nov 2018	docx 13.7 kB	Download

CAD/CAE-Data

CAD data

2D/3D Models 210-133	URL	Download
----------------------	-----	----------

CAE data

WSCAD Universe 210-133	URL	Download
------------------------	-----	----------

ZUKEN Portal 210-133	URL	Download
----------------------	-----	----------

EPLAN Data Portal 210-133	URL	Download
---------------------------	-----	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 210-133 Busbar; tin-plated; 1000 mm long; Cu 10 mm x 3 mm; white	URL	Download
--	-----	----------

Installation Notes

Subject to changes. Please also observe the further product documentation!