


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334710201](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: [MX150 Sealed Female Connector, Single Row, 2 Circuits, Keying Option A, Black](#)

Documents:

3D Model	Application Specification AS-33611-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31300-635-001 (PDF)
Product Specification PS-33471-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-001 (PDF)	



Series image - Reference only

General

Product Family	Crimp Housings
Series	33471
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA), No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	883906705213

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	6.305/g
Number of Rows	1
Packaging Type	Individual Cell
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33611-001-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33471-000-001
Sales Drawing	150-S-002-1-Z05, SD-33471-0001-001, SD-33471-021, SD-33481-0001-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[33471](#) Series

Mates With

[MX150 Sealed Single Row Male Connector 33481](#)

Use With

[MX150 Female Terminal 33012](#) , [33001](#)

[MX150 Sealed Receptacle Cavity Plug 343454001](#)
[MX150 Backshell 349490210](#) , [349490220](#)