


**Product Details for 352620 - 1**



**352620 - 1**

[Active](#)

**2mm Hard Metric PCB Mount Connectors  
(Z - PACK 2mm HM)**

[RoHS/Not ELV Compliant](#) (Find RoHS Compliant Alternates/Compliance Statement)

**Product Highlights:**

- ? Connector
- ? Connector Type = Type B, 25 Column
- ? Plug
- ? Interface Type = 2mm HM
- ? Contact Type = ACTION PIN Post

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(1\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [MALE ASSEMBLY, Z - PACK 2mm HM, TYPE B](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)
- ? [Mating Products \(1\)](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? Connector Type = Type B, 25 Column
- ? [Gender](#) = Plug
- ? [Number of Positions](#) = 148
- ? [PCB Mount Angle](#) = Vertical
- ? [Mating Polarization](#) = Without
- ? [Shielded](#) = No

**Mechanical Attachment:**

- ? [Board Mount](#) = Fixed Board
- ? [Module Length \(mm \[in\]\)](#) = 50.00 [1.968]
- ? [Crosstalk Version](#) = Standard

**Termination Related Features:**

- ? [Interface Type](#) = 2mm HM
- ? Termination End Plating = Tin -Lead over Nickel

**Body Related Features:**

- ? [Number of Rows](#) = 5+2
- ? [Grounding Contact](#) = With
- ? Rows Loaded = A, C, E, Z, F, D, B
- ? Selectively Loaded = See Print for Loaded Positions

**Contact Related Features:**

- ? Contact Type = ACTION PIN Post
- ? [Feedthrough Post Length \(mm \[in\]\)](#) = 3.71 [0.146], 13.00 [0.512], 14.50 [0.571]
- ? [CompactPCI](#) = No
- ? [Contact Mating Area Plating](#) = Gold over Nickel
- ? Contact Style = Feed through
- ? Contact Material = Phosphor Bronze

**Housing Related Features:**

- ? Housing Material = Glass -Filled Polyester
- ? Housing Color = Gray

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS not ELV compliant

**Other:**

- ? Brand = AMP