

DIN rail adapter - PTFIX-NS35



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

DIN rail adapter, length: 58.1 mm, width: 28.6 mm, height: 11 mm, color: gray



Commercial Data

Item number	3274054
Packing unit	20 pc
Minimum order quantity	20 pc
Sales Key	BE2ZWX
Product Key	BEA14Z
Catalog Page	Page 438 (C-1-2019)
GTIN	4055626377162
Weight per Piece (including packing)	4.67 g
Weight per Piece (excluding packing)	4.515 g
Customs tariff number	39269097
Country of origin	PL

DIN rail adapter - PTFIX-NS35



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Technical Data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	28.6 mm
Height	11 mm
Height NS 35/15	22.5 mm
Height NS 35/7,5	15 mm
Length	58.1 mm

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

DIN rail adapter - PTFIX-NS35



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Approvals



EAC

Approval ID: RU C-DE.AI30.B.01102



LR

Approval ID: LR2002627TA

DIN rail adapter - PTFIX-NS35



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Classifications

ECLASS

ECLASS-9.0	27370419
ECLASS-11.0	27370419
ECLASS-10.0.1	27370419

ETIM

ETIM 8.0	EC001024
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DIN rail adapter - PTFIX-NS35



3274054

<https://www.phoenixcontact.com/gb/products/3274054>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk