Torque screwdriver set TorqueVario®-S electric assorted, variably adjustable torque limit, 13-pcs. in bag (40674) 0,8-5,0 Nm



Wiha Werkzeuge GmbH Obertalstraße 3-7 78136 Schonach

E-Mail: info.de@wiha.com Tel.:+49 (0)7722 959-0



Article No.: 40674 GTIN: 4010995406745 Unit: Set

Meets your requirements: A variably settable torque covers a large application area.

Simplifies your work: All tools securely arranged in a robust, orderly bag.

Lowers your costs: The correct torque protects you from warranty claims.

Increases your safety: Wiha slimBits ensure good, protected access to deep-set screws.

Protects your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and

muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs.

Increases your efficiency: The correct torque avoids damaging material and no follow-up work is necessary.

Provides you with full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Standards: Manufactured acc. to IEC 60900.DIN EN ISO 6789.

Application: For controlled fastening on live parts up to 1 000 V AC.

| Lieferumfang | 1 x Adapter TorqueVario-S electric for slimBits (35870) 6 mm, 170 mm |
|-----------------------|--|
| | 1 x Adjusting tool for torque screwdriver with long handle (26864) 146 mm |
| | 1 x Screwdriver with bit holder SoftFinish® electric slimVario for slimBits (34577) 6 mm x 50 mm |
| | 1 x slimBit electric bit Phillips (34583) PH1 x 75 mm |
| | 1 x slimBit electric bit Phillips (34584) PH2 x 75 mm |
| | 1 x slimBit electric bit PlusMinus/Pozidriv (34589) SL/PZ1 x 75 mm |
| | 1 x slimBit electric bit PlusMinus/Pozidriv (34590) SL/PZ2 x 75 mm |
| | 1 x slimBit electric bit Pozidriv (34585) PZ1 x 75 mm |
| | 1 x slimBit electric bit Pozidriv (34586) PZ2 x 75 mm |
| | 1 x slimBit electric bit Slotted (34578) 2,5 mm x 75 mm |
| | 1 x slimBit electric bit Slotted (34581) 5,5 mm x 75 mm |
| | 1 x slimBit electric bit Slotted (41159) 3,5 mm x 75 mm |
| | 1 x Torque screwdriver TorqueVario®-S electric Variable torque limit settings (26626) 0,8-5,0 Nm, 3,8 mm |
| Nm | 0,8-5,0 Nm |
| Weight | 550 g |
| Serie | 2872 T13 |
| Anwendungsszenarien | For controlled fastening on live parts up to 1 000 V AC. |
| Customs tariff number | 82079030 |
| Product group | 40674 |