Competence XXL II electrician's tool set assorted in case 115-pcs. (42069)



Wiha Werkzeuge GmbH Obertalstraße 3-7 78136 Schonach

E-Mail: info.de@wiha.com Tel.:+49 (0)7722 959-0



Article No.: 42069

GTIN: 4010995420697

Unit: Set

Meets your requirements: Case: robust, large, stable and secure with lid brake.

Lowers your costs: The correct torque protects material from damage and ensures no additional follow-up work.

Increases your safety: Internationally award-winning VDE-insulated tools, each individually tested at 10,000 V AC and approved for use at 1,000 V AC.Gas-filled shock absorbers hold the lid in all positions and reduce the risk of injury when closing.

Protects your health: Wiha pliers require less force and reduce pressure on wrists. Ergonomic handle design makes work easier and prevents occupational illnesses. Trolley with stable in-line rollers allow easy and stress-free transportation of tools to the work area.

Increases your efficiency: A comprehensive tool assortment, always providing you with the right tool when it is needed. The design and function of the tool trays guarantee quick and easy access to tools.

Increases your flexibility: Ample space for additional tools and lots of storage for small parts and machines.

Conventional toolboxes are often not sufficiently robust, have little storage space and the tools are difficult to remove. The development of Wiha's 115-piece Electrician's Competence Case XXL II has put an end to such problems once and for all. The tool inserts in this case are designed to help you work efficiently by ensuring that all tools can be removed quickly and easily. Thanks to extensive equipment, electricians have the right utensil for every application, such as the LiftUp electric magazine bit holder, a torque screwdriver set, fully insulated screwdrivers from the Wiha Slim line or TriCut installation pliers. The large storage space in the tool case also contains a spirit level specially designed for electricians. Made of robust polypropylene, the case also features gas-filled shock absorbers, which hold the lid in different positions, preventing it from closing automatically and causing injury.

Application: Suitable for working on live parts up to 1,000 V AC. The complete kit for professional electricians out on jobs.

Lieferumfang

- 1 x Automatic crimp tool for wire-end sleeves hex crimping (41246) 210 mm
- 1 x Cable cutter Professional electric (34744) 200 mm
- 1 x Combination pliers Professional electric with DynamicJoint® and OptiGrip with extra long cutting edge (26708) 180 mm
- 1 x Crimp tool for insulated cable eyes and contacts (33841) 220 mm
- 1 x Electrician's hammer with 300 g hammer head, in blister pack (42071)
- 1 x Electrician's Longlife® folding ruler, 2 m metric, 10 segments (42068) orange
- 1 x Electrician's spirit level 40 cm (42074)
- 1 x Fine screwdriver PicoFinish electric Phillips (38880) PH0 x 60 mm
- 1 x Fine screwdriver PicoFinish electric Slotted (38876) 2,5 mm x 60 mm
- 1 x Flashlight with LED, laser and UV light in blister pack, including 3 AAA batteries (41286)
- 1 x Installation pliers TriCut Professional electric (38552) 170 mm
- 1 x L-key set in ErgoStar holder hexagonal ball Magicring® 9-pcs. in flourescent colour (41979)
- 1 x Needle nose pliers Professional electric with cutting edge curved shape, approx. 40° (26729) 200 mm
- 1 x Needle nose pliers Professional electric with cutting edge straight shape (26727) 200 mm
- 1 x Precision mechanic's diagonal cutters Classic with opening spring (36189) 125 mm
- 1 x Professional BiCut® high-performance diagonal cutters with DynamicJoint® Switchable (38191) 200 mm
- 1 x Professional electric diagonal cutters with DynamicJoint® (26741) 160 mm
- 1 x Screwdriver SoftFinish® electric Hex nut driver (00856) 5,5 mm x 125 mm
- 1 x Screwdriver SoftFinish® electric Hex nut driver (00858) 7 mm x 125 mm
- 1 x Screwdriver SoftFinish® electric Hex nut driver (00859) 8 mm x 125 mm
- 1 x Screwdriver SoftFinish® electric Hex nut driver (00861) 10 mm x 125 mm
- 1 x Screwdriver SoftFinish® electric Hex nut driver (00864) 13 mm x 125 mm

- 1 x Screwdriver SoftFinish® electric slimFix Phillips (35393) PH1 x 80 mm
- 1 x Screwdriver SoftFinish® electric slimFix Phillips (35394) PH2 x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv (36329) SL/PZ1 x 80 mm
- 1 x Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv (36330) SL/PZ2 x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix Pozidriv (35395) PZ1 x 80 mm
- 1 x Screwdriver SoftFinish® electric slimFix Pozidriv (35396) PZ2 x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix Slotted (35391) 5,5 mm x 125 mm
- 1 x Screwdriver SoftFinish® electric slimFix Slotted (35392) 6,5 mm x 150 mm
- 1 x Screwdriver SoftFinish® electric slimFix Slotted (35446) 3,5 mm x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix TORX® Tamper Resistant (with hole) (41141) T10H x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix TORX® Tamper Resistant (with hole) (41142) T15H x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix TORX® Tamper Resistant (with hole) (41143) T20H x 100 mm
- 1 x Screwdriver SoftFinish® electric slimFix TORX® Tamper Resistant (with hole) (41144) T25H x 125 mm
- 1 x Screwdriver SoftFinish® Slotted with one-piece hexagonal blade and solid steel cap (03223) 3,5 mm x 75 mm
- 1 x Screwdriver SoftFinish® Slotted with one-piece hexagonal blade and solid steel cap (03231) 12,0 mm x 200 mm
- 1 x Screwdriver with bit holder SoftFinish® electric slimVario Stubby for slimBits (41229) 6
- 1 x Screwdriver with bit magazine LiftUp electric Pozidriv, PlusMinus/Pozidriv, slotted with 6 slimBits (41234)
- 1 x Shear for electricians with crimp function in blister pack (41923) 160 mm
- 1 x slimBit electric bit Pozidriv (34586) PZ2 x 75 mm
- 1 x SoftFinish® dowel racket set with dowels Phillips with 6 mm round blade in blister pack, 5-pcs. (41289)
- 1 x Stripping tool automatic up to 16 mm² in blister pack (42062) 200 mm
- 1 x Stripping tool with self-rotating trailing blade (35969) 165 mm
- 1 x Switch cabinet key pen shape in blister pack (39076)

	1 x Voltage tester SoftFinish® single-pole, 110-250 volts Slotted transparent, with push-on clip (34745) 3,0 mm x 60 mm
	1 x Voltage tester Volt Detector non-contact, single-pole, 230-1,000 VAC (37871)
	1 x Water pump pliers Professional electric with push button adjustment (37450) 250 mm
	1 x XLSelector Y bit set, 25 mm Phillips, Pozidriv, TORX®, 31-pcs., 1/4" (41832)
Weight	19.000 g
Serie	9.500
Anwendungsszenarien	Suitable for working on live parts up to 1,000 V AC. The complete kit for professional electricians out on jobs.
Customs tariff number	82060000
Product group	42069

1 x Torque screwdriver set TorqueVario®-S electric assorted, variably

adjustable torque limit, 18-pcs. in bag (36791) 0,8-5,0 Nm