

Surge suppressor, RC element, 127 ... 240 V AC 150 ... 250 V DC for contactors Size S2



Figure similar

General technical data:		
Product brand name		SIRIUS
Product designation		surge suppressor
Size of contactor		S2
Design of the surge suppressor		RC element
Ambient temperature		
<ul style="list-style-type: none"> <li>during storage</li> </ul>	°C	-40 ... +80
<ul style="list-style-type: none"> <li>during operation</li> </ul>	°C	-25 ... +60
Control circuit/ Control:		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency		
<ul style="list-style-type: none"> <li>1 rated value</li> </ul>	Hz	50
<ul style="list-style-type: none"> <li>2 rated value</li> </ul>	Hz	60
Control supply voltage 1		
<ul style="list-style-type: none"> <li>at DC</li> </ul>		
<ul style="list-style-type: none"> <li>— Initial rated value</li> </ul>	V	150
<ul style="list-style-type: none"> <li>— Final rated value</li> </ul>	V	250






- at AC
  - at 50 Hz Initial rated value
  - at 50 Hz Final rated value
  - at 60 Hz Final rated value
  - at 60 Hz Initial rated value




V	127
V	240
V	240
V	127

#### Installation/ mounting/ dimensions:

Mounting position		any
Mounting type		clip-on
Width	mm	30
Height	mm	30
Depth	mm	14.5

#### Certificates/ approvals:

Certificate of suitability	CE / UL / CSA / CCC		
General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
 CSA	 UR	 EAC	 EG-Konf.
		<a href="#">Type Test Certificates/Test Report</a>	 ABS

Shipping Approval	other
 BUREAU VERITAS	 LRS
 RMRS	<a href="#">Confirmation</a>

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2936-1CD00>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2936-1CD00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT2936-1CD00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2936-1CD00&lang=en)





last modified:

12/22/2018