


**3M** Science.  
Applied to Life.™

# A Legend Re-born

Precision optics. An award-winning, slim profile welding helmet.  
At a winning price. Who says you can't have it all?

3M™ Speedglas™ Welding Helmet 9002NC

 **Speedglas**™



## The optics that forever changed the way welders see are now available in the helmet that changed everything...

See your welds in a new light, with more contrast and natural-looking colours.

3M™ Speedglas™ True-View Technology allows you to see your weld pool with a view that appears lighter, brighter and more realistic. Read surfaces and contours better with a view that must be seen to be believed.



Sample competitor's welding lens shade 3.



Speedglas 9002NC welding lens shade 3.

# The classic, streamlined Speedglas 9000 design

## 3M™ Speedglas™ Welding Helmet 9002NC

You asked and we listened. The award winning Speedglas 9000 welding helmet changed the game in helmet design by introducing the perfect combination of helmet shape, size, and weight still preferred by welders today!

So we've brought it back. The exact same narrow shell profile many welders love only with advanced optics, less weight, more comfort and a new look!

### Better control

An improved optical experience with Speedglas True-View allows better control over your welds.

### Exhale

Thanks to the exhaust vents built into the helmet, the build-up of carbon dioxide is reduced, keeping you more comfortable and the lens fog free.

### Freedom of movement

The classic slim, light-weight design increases your freedom of movement. Plus, the exhaust vents allow for a close-to-the-face fit.

### The best made affordable

3M™ Speedglas™ Technology and state-of-the-art auto-darkening optics at a price point within reach of every welder, from apprentices to seasoned veterans.



### Custom comfort

Ratchet mechanism and multiple adjustments for a customised fit.



#### Speedglas Welding Helmet 9002NC Specifications

**Light-weight:** 485g

**Shades:** 3 / 8, 9, 10, 11, 12

**Lens viewing area:** 55 × 107 mm

**Optical Rating:** 1/1/1 with True-View

**Welding applications:** MMAW, MIG/MAG, TIG and low amp TIG (1 Amp)

**Approvals:** Welding Protection - AS/NZS1338.1, Eye/Face Protection - AS/NZS1337.1

# Ready to order?



40 13 85



40 00 85



70 50 15

Part No	Description
40 13 85	Complete 3M™ Speedglas™ Welding Helmet 9002NC
40 00 85	Upgraded 3M™ Speedglas™ Welding lens 9002NC, suitable for all 9000 series welding helmets
70 50 15	Upgraded head harness, suitable for all 9000 series welding helmets

## Extra protection and performance



16 40 05



16 40 09



16 90 01



16 91 00



17 10 20  
17 10 21  
17 10 22  
17 10 23  
17 10 24

Part No	Description
16 40 05	Ear and neck protection in leather.
16 40 09	Head protection, black/grey flame-resistant fabric.
16 90 01	Neck protection, black/grey flame-resistant fabric.
16 91 00	Full hood black/grey flame-resistant fabric.
17 10 20	Magnifying lens 1.0
17 10 21	Magnifying lens 1.5
17 10 22	Magnifying lens 2.0
17 10 23	Magnifying lens 2.5
17 10 24	Magnifying lens 3.0