

FEATURES

- 8 piece screwdriver set containing popular sizes
- Ideal for the repair/service engineers
- Supplied in a vinyl tool roll

RS PRO Engineers Slotted Parallel; Phillips; Pozidriv Screwdriver Set 8 Piece

RS Stock No.: 459-3966



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO 8 Piece Screwdriver Set is an ideal choice for professionals and enthusiasts. Manufactured with high quality in mind, these screwdrivers are made with durable chrome-molybdenum and chrome-vanadium steel. They feature a soft-feel handle to ensure a comfortable and safe grip for precision and control over long periods of use. The 8 piece set is supplied in handy storage roll to keep your tools safe and dry when not in use.



General Specifications

Screwdriver Type	Engineers
Number of Pieces	8
Тір Туре	Slotted Parallel; Phillips; Pozidriv
Set Contents	4pc- Flare tip slotted screwdriver with Red/Black colour double injection handle Sizes 5.0x75mm 5.0x100mm 6x 150mm Chubby: 6x 40mm 4pc- Parallel tip slotted screwdriver Red/Black colour double injection handle Sizes 3.0x50mm 3z100mm 3x 150mm 5x 200mm 4pc- Pozidriv screwdriver with Red /Black colour double injection handle Sizes No.0 x 75mm No.1 x75mm No.2 x 100mm Chubby No .2 x 40mm 1pc- VDE insulated pozidriv screwdriver with Red/Black colour double injection handle Size No. 1 x80mm 5pc- Phillips screwdriver with Red/Black colour double injection handle Sizes No. 0x 50mm No. 1 x80mm 5pc- 200mm No. 1 x 75mm No. 2 x 100mm No. 3 x 150mm Chubby no.1 x 40mm (Remove the ma
Applications	consoles - Xbox/Playstation, Woodworking/carpentry, Fastening wood and metal



Mechanical Specifications

Tip Size	Slotted Parallel: 3 mm; Pozidriv: PZ0; PZ1; Phillips: PH0; PH1
Blade Material	Phillips and Pozidriv tips: Chrome Molybdenum Vanadium steel (S-2) Slotted Tips: Chrome Vanadium steel (#6155)
Handle Material	Polypropylene / TPR
Blade Finish	Satin chrome finish and Phosphate Black tip
Hardness	Phillips and Pozidriv tips: Heat treat to HRC 58-62 degrees Slotted tips: Heat treat to HRC 52-56 degrees

Approvals	
Compliance/Certifications	BS2559

