

PRODUCT-DETAILS

# UPS PowerValue 11T G2 3 kVA B

## UPS PowerValue 11T G2 3 kVA B



### General Information

Extended Product Type	UPS PowerValue 11T G2 3 kVA B
Product ID	4NWP100162R0001
EAN	7640169261923
Catalog Description	UPS PowerValue 11T G2 3 kVA B
Long Description	VFI online double conversion;2700W;9min;RS232;USB;mini COM slot

### Circular Value

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004828

### Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	No declaration needed

### Technical

Input Voltage (U <sub>in</sub> )	220 V 230 V 240 V
Input Voltage Type	AC
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Apparent Power Output	3000 V·A
Rated Output Power	2700 W
Communication Interface	USB, RS-232
Number of Phases	Primary - 1 Secondary - 1
Number of Outputs	C13 Connection 4 C19 Connection 1
Connection Type	IEC C20
Options Provided	Auto shut down function Potential free switch contact Network-management
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Number of Batteries	4

## Dimensions

Product Net Width	190 mm
Product Net Height	327 mm
Product Net Depth / Length	399 mm
Product Net Weight	22.2 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	324 mm
Package Level 1 Height	464 mm
Package Level 1 Depth / Length	500 mm
Package Level 1 Gross Weight	24.6 kg
Package Level 1 EAN	7640169261923

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408612
E-Number (Sweden)	5257249
Country of Origin	China (CN)

## Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
---------------------------------	-------------------------

Declaration of  
Conformity - CE

4NWD004828

### Popular Downloads

Data Sheet, Technical Information	4NWD003883_EN
Instructions and Manuals	4NWD003883_EN
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658

### Classifications

ETIM 7	EC000382 - UPS
ETIM 8	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

### Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 T G2 IEC 230V

