

**ENGLISH** 

# Datasheet RS PRO Partition Plate RS

Stock No: 501-746



### **Product Details**

RS PRO partition plate is suitable for use with DIN rail terminal. DIN rail mounted terminals, with universal mounting foot clips to both 'G' profile (asymmetric to BS5825:1990) and 'top hat' profile (symmetric to BS5584:1978) rails, with a range of features to suit all applications. The 2.5 to  $10 \text{mm}^2$  terminals have common end covers and partitions, there are 10 pole Jumper Bars available for cross connection and are easily fitted with markers on either side. The partition plate meets UL, CSA, NEMKO and GOST standards.

### **Features and Benefits**

- Suitable for use with DIN rail terminal
- Suits all applications
- The partition plate meets UL, CSA, NEMKO and GOST standards



## ENGLISH

### **Specifications:**

Accessory Type Partition Plate
For Use With DIN Rail Terminal
Colour Beige

Material Nylon 66

Standards Met UL, CSA Certified

Suitable terminals for RS	501746	
	1	
	RS Part	
	1	<b>a</b>

RS Part	
No	Description
815666	2.5mm din rail terminal beige
815644	2.5mm din rail terminal blue
501635	2.5mm din rail terminal brown
501730	2.5mm din rail terminal orange
501976	2.5mm din rail terminal black
501639	2.5mm din rail terminal grey
501613	2.5mm din rail terminal white
501641	2.5mm din rail terminal yellow
501821	2.5mm din rail terminal red
815666	2.5-4mm Terminal Beige
815672	2.5-4mm Terminal Blue
501720	2.5-4mm din rail terminal brown
501651	2.5-4mm din rail terminal orange
501645	2.5-4mm din rail terminal black
501803	2.5-4mm din rail terminal grey
501932	2.5-4mm din rail terminal white
501663	2.5-4mm din rail terminal yellow
501673	2.5-4mm din rail terminal red
815694	6-10mm Terminal Beige





#### Series overview and accessories:

Terminal blocks colour	RS Article
beige 10mm²	762-2521
blue 10mm²	762-2525

Accessories	RS Article
End plate AP	872-4726
Partition plate TW	501-746
Insulating cap SQIK for cross-connector	872-4739
Insulated cross-connection SQI 2 pole	762-2587
Insulated cross-connection SQI 3 pole	872-4773
Insulated cross-connection SQI 5 pole	762-2590
Insulated cross-connection SQI 10 pole	762-2593

Note: Cross connectors can be used overlapping

Fitting DIN Rails	RS Article
35mm Din Rail, slotted, 500mm	467-406
35mm Din Rail, slotted, 1000mm	467-416
35mm Din Rail, slotted, 2000mm	742-4138
35mm Din Rail, not slotted, 500mm	742-4129
35mm Din Rail, not slotted, 1000mm	467-399
35mm Din Rail, not slotted, 2000mm	467-400